

规格书编号

SPEC NO: HDFB08ARSSB5SP02

产品规格书

SPECIFICATION

CUSTOMER 客户: _____
PRODUCT 产品: _____ SAW FILTER _____
MODEL NO 型号: _____ HDFB08ARSS-B5 _____
MARKING 印字: _____ ● T 5 _____
PREPARED 编制: _____ CHECKED 审核: _____
APPROVED 批准: _____ D A T E 日期: _____ 2017-11-30 _____


客户确认 CUSTOMER RECEIVED:		
审核 CHECKED	批准 APPROVED	日期 DATE

无锡市好达电子有限公司
Shoulder Electronics Limited

1. Application

- Low-loss RF filter for mobile telephone GSM900 systems, receive path(RX).
- Usable passband 35MHz
- Impedance 50 ohm input and output
- Unbalanced to unbalanced operation
- RoHS compatible

2. DIMENSION (PKG SIZE 1.1 x 0.9mm)



Dot Marking

Unit: mm


Pin configuration

- 1. Input
- 4. Output
- 2,3,5 To be grounded

3. Maximum Rating

Items	Conditions
Operation temperature rang	-30°C ~ +85°C
Storage temperature rang	-40°C ~ +85°C
ESD voltage	ESD(MM) : 50VDC
Sensitive discharge device	ESD(HBM) : 175VDC
DC Voltage VDC	3V (25+/-2 deg.C)
Max Input Power	15dBm 2000h
Moisture Sensitivity Level	MSL 2

4. Test Circuit



5. ELECTRICAL SPECIFICATION

Table1. Electrical Specification

Temperature range for specification: T = -20~+80°C


Terminating source impedance: Zs = 50Ω


Terminating load impedance: Zl = 50Ω

Input power: 15dBm 2000h

Item	Condition (MHz)	Specification			Unit	
		Min	Typ	Max		
Insertion loss	927.4~957.6	-	1.5	2.0	dB	
	925~960	-	1.8	2.5	dB	
Amplitude Ripple	925~960	-	0.8	1.8	dB	
VSWR	925~960	Input	-	1.7	2.1	-
		Output	-	1.7	2.1	-
Absolute attenuation	45	40	60	-	dB	
	835~870	38	40	-	dB	
	880~915	35	45	-	dB	
	902.5~910	37	40	-	dB	
	1805~1875	39	52	-	dB	
	1850~1920	38	50	-	dB	
	2400~2500	35	40	-	dB	
	2685~2790	31	35	-	dB	
	2775~2880	31	35	-	dB	
	3700~3840	30	35	-	dB	
	4625~4800	28	33	-	dB	
	5550~5760	28	33	-	dB	
	5725~5875	28	33	-	dB	

6. Typical frequency response





7. ENVIRONMENTAL CHARACTERISTICS

7.1 High temperature exposure

Subject the device to +85°C for 16 hours. Then release the filter into the room conditions for 24 hours prior to the measurement. It shall fulfill the specifications in 5.

7.2 Low temperature exposure

Subject the device to -40°C for 16 hours. Then release the device into the room conditions for 24 hours prior to the measurement. It shall fulfill the specifications in 5.

7.3 Temperature cycling

Subject the device to a low temperature of -40°C for 30 minutes. Following by a high temperature of +85°C for 30 Minutes. Then release the device into the room conditions for 24 hours prior to the measurement. It shall meet the specifications in 5.


7.4 Resistance to solder heat

- 1、immerge the solder bath at 260°C for 10 sec.
- 2、 the iron at 370°C for 3 sec

7.5 Solderability

Submerge the device terminals into the solder bath at 245°C ±5°C for 5s, More than 95% area of the soldering pad must be covered with new solder. It shall meet the specifications in 5.

7.6 Reflow soldering



The specimen shall be passed through the reflow furnace with the condition shown in the above profile for 1 time.

The specimen shall be stored at standard atmospheric conditions for 1h, after which the measurement shall be made. Test board shall be 1.6 mm thick. Base material shall be glass fabric base epoxy resin.

7.7 Mechanical shock

Drop the device randomly onto the concrete floor from the height of 1m 3 times. the device shall fulfill the specifications in 5.

7.8 Vibration

Subject the device to the vibration for 1 hour each in x,y and z axes with the amplitude of 1.5 mm at 10 to 55 Hz. The device shall fulfill the specifications in 5.

8. REMARK

8.1 Static voltage

Static voltage between signal load & ground may cause deterioration & destruction of the component. Please avoid static voltage.

8.2 Ultrasonic cleaning

Ultrasonic vibration may cause deterioration & destruction of the component. Please avoid ultrasonic cleaning

8.3 Soldering

Only pad component may be solded. Please avoid soldering another part of component.

9. Packing

9.1 Dimensions

(1) Carrier Tape: Figure 1

(2) Reel: Figure 2


(3) The product shall be packed properly not to be damaged during transportation and storage.

9.2 Reeling Quantity

10000 pcs/reel ϕ 178mm

9.3 Taping Structure


(1) The tape shall be wound around the reel in the direction shown below.



(2) Label

Device Name	
Marking	
User Product Name	
Quantity	
Lot No.	

(3) Leader part and vacant position specifications.




10. TAPE SPECIFICATIONS


10.1 Tensile Strength of Carrier Tape: 4.4N/mm width

10.2 Top Cover Tape Adhesion: (See the below figure)

- (1) pull off angle: 0~15°
- (2) speed: 300mm/min.
- (3) force: 20~70g



[Figure 1] Carrier Tape Dimensions



Prior to the size of 4.0±0.1, after encryption,
modified to 2.0±0.1.

[Figure 2] 10000 pcs/reel ϕ 178mm