

ESD24VD3B

Description


ESD24VD3B is designed to protect voltage sensitive components from ESD and transient voltage events. Excellent clamping capability, low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium. Because of its small size, it is suited for use in cellular phones, MP3 players, digital cameras and many other portable applications where board space is at a premium

Features

- Ultra low leakage: nA level
- Operating voltage: 24V
- Package: SOD-323
- Low clamping voltage
- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
 Air discharge: ±15kV
 Contact discharge: ±8kV
 - IEC61000-4-4 (EFT) 40A (5/50ns)
 - IEC61000-4-5 (Lightning) 6A (8/20µs)



Functional Diagram



Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation
- Peripherals
- Pagers

Absolute Maximum Ratings(Tamb=25°C unless otherwise specified)


Parameter	Symbol	Value	Unit	
Peak Pulse Power (8/20µs)	P _{PP}	Watts		
ESD per IEC 61000-4-2 (Air)	N/	±15	KV	
ESD per IEC 61000-4-2 (Contact)	VESD	±8	KV	
Lead Soldering Temperature	Τι	260 (10 sec)	°C	
Operating Temperature Range	TJ	-55 to +150	°C	
Storage Temperature Range	T _{STJ}	-55 to +150	°C	





Electrical Characteristics (TA = 25 °C unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Reverse Stand-off Voltage	V _{RWM}				24	V
Reverse Breakdown Voltage	$V_{\scriptscriptstyle BR}$	It = 1mA	26.7			V
Reverse Leakage Current	I _R	V _R =VRWM			1	μA
Clamping Voltage	Vc	I _{₽₽} =1A, t _₽ = 8/20µs			43	V
		I _{₽₽} =6A, t _₽ = 8/20µs			52	V
Junction Capacitance	C	V _ℝ =0V, f = 1MHz			75	pF

Characteristics Curves










ACKAGE OUTLINE DIMENSIONS in millimeters (inches) :SOD323



Disclaimer

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.

Users should verify actual device performance in their specific applications.