

1A, 400V - 1000V Glass Passivated Bridge Rectifier

FEATURES

- Glass passivated junction
- Ideal for automated placement
- Reliable low cost construction utilizing molded plastic technique
- High surge current capability
- UL Recognized File # E-326854
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21

ΔD	DI	IC	ΔTI	2

- Switching mode power supply (SMPS)
- Adapters
- Lighting application


MECHANICAL DATA

- Case: ABS
- Molding compound :meets UL 94V-0 flammability rating
- Packing code with suffix "G" means green compound (halogen-free)
- Moisture sensitivity level: level 1, per J-STD-020
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- Polarity: As marked
- Weight: 0.12 g (approximately)

KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I _{F(AV)}	1	Α		
V_{RRM}	400 - 1000 V			
I _{FSM}	30	Α		
T_{JMAX}	150 °0			
Package	ABS			
Configuration	Quad			







PARAMETER	SYMBOL	ABS4-K	ABS6-K	ABS8-K	ABS10-K	UNIT
Marking code on the device		ABS4	ABS6	ABS8	ABS10	
Repetitive peak reverse voltage	V_{RRM}	400	600	800	1000	V
Reverse voltage, total rms value	V _{R(RMS)}	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	400	600	800	1000	V
Forward current On glass-epoxy	I _{F(AV)}	0.8				
Forward current On aluminum substrate		1.0				A
Surge peak forward current, 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}		3	0		Α
t value (of a surge on-state current) I ² t 3.74			A ² s			
Junction temperature	nction temperature T _J -55 to +150			°C		
Storage temperature	T _{STG} -55 to +150		°C			

1



THERMAL PERFORMANCE					
PARAMETER	SYMBOL	LIMIT	UNIT		
Junction-to-lead thermal resistance	$R_{\Theta JL}$	25	°C/W		
Junction-to-ambient thermal resistance	$R_{\Theta JA}$	80	°C/W		

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	TYP.	MAX.	UNIT
Forward voltage (1)	I _F = 0.4A, T _J = 25°C	V _F	-	0.95	V
Reverse current @ rated V _R (2)	T _J = 25°C	I _R	-	10	μA
Reverse current @ rated v _R	T _J = 125°C		-	150	μA

Notes:

- 1. Pulse test with PW=0.3 ms
- 2. Pulse test with PW=30 ms.

ORDERING INFORMATION				
PART NO.	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
ABSxx-K	RE	6	ABS	1,000 / 7" Plastic reel
(Note 1, 2)	RG	G	ABS	5,000 / 13" Paper reel

Notes:

- 1. "xx" defines voltage from 400V (ABS4-K) to 1000V (ABS10-K)
- 2. Whole series with green compound (halogen-free)

EXAMPLE P/N					
EXAMPLE P/N	PART NO.	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION	
ABS8-K REG	ABS8-K	RE	G	Green compound	



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics





Fig.4 Typical Forward Characteristics




3



CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)


Fig.5 Maximum Non-repetitive Forward Surge Current






PACKAGE OUTLINE DIMENSIONS

ABS



DIM.	Unit (mm)		Unit ((inch)
DIW.	Min.	Max.	Min.	Max.
В	4.30	4.50	0.169	0.177
С	6.25	6.65	0.246	0.262
D	0.60	0.70	0.024	0.028
Е	3.90	4.10	0.154	0.161
F	4.90	5.10	0.193	0.200
G	1.40	1.60	0.055	0.063
Н	1.35	1.45	0.053	0.057
I	0.05	0.15	0.002	0.006
J	0.30	0.70	0.012	0.028
K	0.15	0.25	0.006	0.010

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
Α	1.5	0.059
В	0.9	0.035
С	4.22	0.166
D	7.22	0.284
E	2.05	0.081
F	5.72	0.225

MARKING DIAGRAM



P/N = Marking Code ΥW = Date Code F = Factory Code



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.