# MOSFET – Power, Single, N-Channel, SO-8 FL 30 V, 44 A

### Features

- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Optimized Gate Charge to Minimize Switching Losses
- Optimized for 5 V, 12 V Gate Drives
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

# Applications

- CPU Power Delivery
- DC-DC Converters

## **MAXIMUM RATINGS** (T<sub>J</sub> = $25^{\circ}$ C unless otherwise stated)


Para	meter		Symbol	Value	Unit
Drain-to-Source Volt	age		V <sub>DSS</sub>	30	V
Gate-to-Source Volta	age		V <sub>GS</sub>	±20	V
Continuous Drain Current $R_{\theta JA}$		$T_A = 25^{\circ}C$	۱ <sub>D</sub>	15.5	А
(Note 1)		$T_A = 100^{\circ}C$		9.8	
Power Dissipation $R_{\theta JA}$ (Note 1)		$T_A = 25^{\circ}C$	PD	2.70	W
Continuous Drain		$T_A = 25^{\circ}C$	Ι <sub>D</sub>	23.4	Α
Current R <sub>θJA</sub> ≤ 10 s (Note 1)	Steady	T <sub>A</sub> = 100°C		14.8	
Power Dissipation $R_{\theta JA} \leq 10 \text{ s} \text{ (Note 1)}$		T <sub>A</sub> = 25°C	PD	6.13	W
Continuous Drain Current R <sub>0.IA</sub>	State	T <sub>A</sub> = 25°C	Ι <sub>D</sub>	9.0	Α
(Note 2)		$T_A = 100^{\circ}C$		5.7	
Power Dissipation $R_{\theta JA}$ (Note 2)		T <sub>A</sub> = 25°C	PD	0.92	W
Continuous Drain		$T_{C} = 25^{\circ}C$	Ι <sub>D</sub>	44	Α
Current R <sub>θJC</sub> (Note 1)		T <sub>C</sub> =100°C		28	
Power Dissipation $R_{\theta JC}$ (Note 1)		T <sub>C</sub> = 25°C	P <sub>D</sub>	21.6	W
Pulsed Drain Current	T <sub>A</sub> = 25°	<sup>2</sup> C, t <sub>p</sub> = 10 μs	I <sub>DM</sub>	182	A
Current Limited by Pa	ackage	T <sub>A</sub> = 25°C	I <sub>Dmax</sub>	100	А
Operating Junction an Temperature	nd Storage	•	T <sub>J</sub> , T <sub>STG</sub>	–55 to +150	°C
Source Current (Body			ا <sub>S</sub>	21	Α
Drain to Source DV/D	T		dV/d <sub>t</sub>	6.0	V/ns



# **ON Semiconductor®**

## http://onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
30 V	7.0 m $\Omega$ @ 10 V	44 A
50 V	11.2 mΩ @ 4.5 V	44 A



# ORDERING INFORMATION

= Work Week

= Lot Traceability

W ZZ

Device	Package	Shipping <sup>†</sup>
NTMFS4926NT1G	SO-8 FL (Pb-Free)	1500 / Tape & Reel
NTMFS4926NT3G	SO-8 FL (Pb-Free)	5000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

### MAXIMUM RATINGS (T<sub>J</sub> = 25°C unless otherwise stated)

Parameter	Symbol	Value	Unit
Single Pulse Drain-to-Source Avalanche Energy (T <sub>J</sub> = 25°C, V <sub>DD</sub> = 24 V, V <sub>GS</sub> = 20 V, I <sub>L</sub> = 21 A <sub>pk</sub> , L = 0.1 mH, R <sub>G</sub> = 25 $\Omega$ )	E <sub>AS</sub>	22	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)	ΤL	260	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.
Surface-mounted on FR4 board using the minimum recommended pad size.

# THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case (Drain)	$R_{ ext{ heta}JC}$	5.8	
Junction-to-Ambient - Steady State (Note 3)	$R_{\thetaJA}$	46.3	°C 14/
Junction-to-Ambient - Steady State (Note 4)	$R_{\thetaJA}$	136.2	°C/W
Junction-to-Ambient – (t $\leq$ 10 s) (Note 3)	$R_{\thetaJA}$	20.4	

Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.
Surface-mounted on FR4 board using the minimum recommended pad size.

### ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS}$ = 0 V, $I_D$ = 250 $\mu$ A		30			V
Drain-to-Source Breakdown Voltage (transient)	V <sub>(BR)DSSt</sub>	$V_{GS}$ = 0 V, I <sub>D(aval)</sub> = 8.8 A, T <sub>case</sub> =25°C, t <sub>transient</sub> = 100 ns		34			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> / T <sub>J</sub>				25		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{GS} = 0 V,$	$T_J = 25^{\circ}C$			1.0	
		V <sub>DS</sub> = 24 V	T <sub>J</sub> = 125°C			10	μΑ
Gate-to-Source Leakage Current	I <sub>GSS</sub>	$V_{DS}$ = 0 V, $V_{GS}$	= ±20 V			±100	nA

**ON CHARACTERISTICS** (Note 5)

Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D = 250 \ \mu A$		1.32	1.6	2.2	V
Negative Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>			3.8		mV/°C	
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V	I <sub>D</sub> = 30 A		5.6	7.0	
			I <sub>D</sub> = 15 A		5.6		
		V <sub>GS</sub> = 4.5 V	I <sub>D</sub> = 30 A		9.0	11.2	mΩ
			I <sub>D</sub> = 15 A		8.7		
Forward Transconductance	<b>9</b> FS	V <sub>DS</sub> = 1.5 V, I <sub>D</sub>	) = 15 A		40		S

### **CHARGES, CAPACITANCES & GATE RESISTANCE**

Input Capacitance	C <sub>ISS</sub>		1004		
Output Capacitance	C <sub>OSS</sub>	$V_{GS}$ = 0 V, f = 1 MHz, $V_{DS}$ = 15 V	390		pF
Reverse Transfer Capacitance	C <sub>RSS</sub>		119		
Capacitance	C <sub>RSS</sub> / C <sub>ISS</sub>	V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 15 V, f = 1 MHz	0.119	0.237	


5. Pulse Test: pulse width  $\leq$  300 µs, duty cycle  $\leq$  2%. 6. Switching characteristics are independent of operating junction temperatures.

# **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = $25^{\circ}$ C unless otherwise specified)


Parameter	Symbol	Test Cond	lition	Min	Тур	Max	Unit
CHARGES, CAPACITANCES & GATE	E RESISTANCE						-
Total Gate Charge	Q <sub>G(TOT)</sub>			8.7			
Threshold Gate Charge	Q <sub>G(TH)</sub>			1.4		.0	
Gate-to-Source Charge	Q <sub>GS</sub>	V <sub>GS</sub> = 4.5 V, V <sub>DS</sub> =	15 V; I <sub>D</sub> = 30 A		3.0		nC
Gate-to-Drain Charge	Q <sub>GD</sub>				3.5		
Total Gate Charge	Q <sub>G(TOT)</sub>	$V_{GS}$ = 10 V, $V_{DS}$ =	15 V; I <sub>D</sub> = 30 A		17.3		nC
SWITCHING CHARACTERISTICS (N	ote 6)						
Turn-On Delay Time	t <sub>d(ON)</sub>			8.6			
Rise Time	tr	$V_{GS}$ = 4.5 V, $V_{DS}$ = 15 V, I <sub>D</sub> = 15 A, R <sub>G</sub> = 3.0 Ω			36.9		
Turn-Off Delay Time	t <sub>d(OFF)</sub>				14.7		ns
Fall Time	t <sub>f</sub>			5.5			
Turn-On Delay Time	t <sub>d(ON)</sub>			6.6			
Rise Time	tr	$\label{eq:VGS} \begin{array}{l} V_{GS} = 10 \; V, \; V_{DS} = 15 \; V, \\ I_{D} = 15 \; A, \; R_{G} = 3.0 \; \Omega \end{array}$			31.8		
Turn-Off Delay Time	t <sub>d(OFF)</sub>				18.3		ns
Fall Time	t <sub>f</sub>	1			4.0		
DRAIN-SOURCE DIODE CHARACTE	ERISTICS						
Forward Diode Voltage	V <sub>SD</sub>	$V_{GS} = 0 V_{0}$	$T_J = 25^{\circ}C$		0.87	1.1	
		V <sub>GS</sub> = 0 V, I <sub>S</sub> = 30 A	T <sub>J</sub> = 125°C		0.76		V
Reverse Recovery Time	t <sub>RR</sub>				21.9		
Charge Time	t <sub>a</sub>	V <sub>GS</sub> = 0 V, dIS/dt	= 100 A/μs,		11.0		ns
Discharge Time	t <sub>b</sub>	V <sub>GS</sub> = 0 V, dIS/dt I <sub>S</sub> = 30	A		10.9		
Reverse Recovery Charge	Q <sub>RR</sub>	1			8.0		nC
PACKAGE PARASITIC VALUES						_	
Source Inductance	L <sub>S</sub>				1.00		nH
Drain Inductance	L <sub>D</sub>	т. т.	00		0.005		nH
Gate Inductance	L <sub>G</sub>	T <sub>A</sub> = 25	°U		1.84		nH
Gate Resistance	R <sub>G</sub>	1			1.0	2.2	Ω

Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
Switching characteristics are independent of operating junction temperatures.

# **TYPICAL CHARACTERISTICS**



# **TYPICAL CHARACTERISTICS**



# **TYPICAL CHARACTERISTICS**





Figure 13. Thermal Response

### PACKAGE DIMENSIONS



\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and IIII are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death agosciated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunit/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative