


Technical Data Sheet

1.6mm Round Subminiature Chip Phototransistor

Features

- Fast response time
- High photo sensitivity
- Small junction capacitance
- Package in 8mm tape on 7" diameter reel
- Pb free
- The product itself will remain within RoHS compliant version.



 PT26-21B/CT is a phototransistor in miniature SMD package which is molded in a black with spherical top view lens.
 The device is spectrally matched to infrared emitting diode.


Applications

- Miniature switch
- Counters and sorter
- Position sensor
- Infrared applied system
- Encoder

Device Selection Guide

Part No.	Chip	Lens Color	
	Material	Lens Color	
PT	Silicon	Black	

PT26-21B/CT




Everlight Electronics Co., Ltd. http://www.everlight.com Rev 3 Page: 1 of 8

Device No: DPT-0000116 Prepared date: 25-May-2012 Prepared by: Gao YunFei

Revision : 3 Release Date:2012-06-03 15:44:48.0



Package Dimensions



Notes: 1.All dimensions are in millimeters

2.Tolerances unless dimensions ±0.1mm

Absolute Maximum Ratings (Ta=25

Parameter	Symbol	Rating	Units	
Collector-Emitter Voltage	V_{CEO}	30	V	
Emitter-Collector-Voltage	V_{ECO}	5	V	
Collector Current	I_{C}	20	mA	
Operating Temperature	T_{opr}	-25 ~ +85		
Storage Temperature	T_{stg}	-40 ~ +100		
Soldering Temperature *1	T_{sol}	260		
Power Dissipation at(or below)	P_d	75	mW	
25 Free Air Temperature				

Notes: *1:Soldering time 5 seconds.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 3 Page: 2 of 8

Device No: DPT-0000116 Prepared date: 25-May-2012 Prepared by: Gao YunFei
Revision: 3 Release Date: 2012-06-03 15:44:48.0



Electro-Optical Characteristics (Ta=25

Parameter	Symbol	Condition	Min	Тур	Max	Unit				
Rang Of Spectral Bandwidth	0.1		730		1100	nm				
Wavelength Of Peak Sensitivity	P			840		nm				
Collector-Emitter Breakdown Voltage	BV _{CEO}	I _C =500 µ A Ee=0mW/cm ²	30			V				
Emitter-Collector Breakdown Voltage	BV _{ECO}	I_E =50 μ A Ee=0mW/cm ²	5			V				
Collector-Emitter Saturation Voltage	V _{CE(sat)}	I _C =5mA Ee=1m W/cm ²			0.4	V				
Collector Dark Current	I_{CEO}	V _{CE} =20V Ee=0mW/cm ²			50	nA				
On State Collector Current	$I_{C(ON)}$	$V_{CE}=5V$ $Ee=1mW/cm^{2}$ $p=940nm$		1.0		mA				
Rise Time	$t_{\rm r}$	V _{CE} =5V		20		μS				
Fall Time	t_{f}	I _C =1mA R _L =1000		20						

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 3 Page: 3 of 8

Device No: DPT-0000116 Prepared date: 25-May-2012 Prepared by: Gao YunFei

Release Date:2012-06-03 15:44:48.0

Revision: 3

LifecyclePhase: Expired Period: Forever Expired Period: Forever



Typical Electro-Optical Characteristics Curves

Fig.1 Collector Power Dissipation vs. Ambient Temperature




Fig.2 Spectral Sensitivity




Fig.3 Collector Current vs.





Fig.4 Collector Current vs. Collector-Emitter Voltage



Everlight Electronics Co., Ltd.

Device No: DPT-0000116

: 3 LifecyclePhase:

Revision

http://www.everlight.com

Collector Current Ic (mA)

Rev 3

Page: 4 of 8

Prepared date: 25-May-2012

Prepared by: Gao YunFei Release Date:2012-06-03 15:44:48.0

Expired Period: Forever




Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package, the LEDs should be kept at 30 or less and 90%RH or less.
 - 2.3 After opening the package: The LED's floor life is 1 year under 30 or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
 - 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.Baking treatment: 60±5 for 24 hours.
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 3 Page: 5 of 8

Device No: DPT-0000116 Prepared date: 25-May-2012 Prepared by: Gao YunFei Revision: 3 Release Date: 2012-06-03 15:44:48.0




4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350 for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.




Everlight Electronics Co., Ltd. http://www.everlight.com Rev 3 Page: 6 of 8

Device No: DPT-0000116 Prepared date: 25-May-2012 Prepared by: Gao YunFei
Revision: 3 Release Date: 2012-06-03 15:44:48.0




Package Dimensions



Note: The tolerances unless mentioned is ±0.1mm, Unit: mm

Carrier Tape Dimensions: Loaded quantity 1500 PCS per reel



Unit:mm

Everlight Electronics Co., Ltd.

Device No: DPT-0000116

Revision: 3

LifecyclePhase: 正式發行 Approved

http://www.everlight.com

Rev 3

Page: 7 of 8

Prepared date: 25-May-2012

O12 Prepared by : Gao YunFei Release Date: 2012-06-03 15:44:48.0

Expired Period: Forever



Label Form Specification



CPN: Customer's Production Number

P/N: Production Number OTY: Packing Quantity

CAT: Ranks

HUE: Peak Wavelength

REF: Reference

LOT No: Lot Number

MADE IN TAIWAN: Production Place

Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD.

Office: No. 6-8, Zhonghua Rd., Shulin Dist., New Taipei City 23860, Taiwan, R.O.C. Tel: 886-2-2685-6688 Fax: 886-2-2685-6897 http://www.everlight.com

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 3 Page: 8 of 8

Device No: DPT-0000116 Prepared date: 25-May-2012 Prepared by: Gao YunFei

Revision : 3 Release Date:2012-06-03 15:44:48.0