AMS1117

Features

- Maximum output current is 1.4A
- Range of operation input voltage: Max 30V
- Line regulation: 0.03%/V (typ.)

Applications

- Power Management for Computer Mother Board, Graphic Card
- LCD Monitor and LCD TV

- Standby current: 2mA (typ.)
- Load regulation: 0.2%/A (typ.)
- Environment Temperature: -40°C ~ 85°C
- DVD Decode Board
- ADSL Modem
- Post Regulators For Switching Supplies

General Description


AMS1117 is a series of low dropout three-terminal regulators with a dropout of 1.3V at 1A load current. AMS1117 features a very low standby current 2mA compared to 5mA of competitor.

Other than a fixed version, Vout = 1.2V, 1.8V, 2.5V, 2.85V, 3.3V, and 5V, AMS1117 has an adjustable version, which can provide an output voltage from 1.25 to 12V with only two external resistors.

AMS1117 offers thermal shut down function, to assure the stability of chip and power system. And it uses trimming technique to guarantee output voltage accuracy within 2%. Other output voltage accuracy can be customized on demand, such as 1%.


AMS1117 is available in SOT-223 package.

Typical Application




Application circuit of AMS1117 fixed version

Typical Electrical Characteristic




REV.08 1 of 7

Block Diagram



Pin Configuration



Absolute Maximum Ratings

Max Input Voltage	··30V
Max Operating Junction Temperature(Tj)	. . 150 ℃
Ambient Temperature(Ta) ·····	40°C~ 85°C
Storage Temperature(Ts)	40°C~150°C
Lead Temperature & Time	260°C 10S
Caution: Exceed these limits to damage to the device. Exposure to absolute maximum rating condit	ions may affect

Recommended Work Conditions

Thermal Information

device reliability.

Parameter	Package	Rating	Unit
Package thermal resistance	SOT-223	20	°C/W

REV.08 2 of 7



AMS1117

Electrical Characteristics

T_A=25°C, unless otherwise noted.

Symbol	Parameter	Conditions Min		Тур	Max	Unit
Vref	Reference	AMS1117 -Adj	1.225	1.25	1.275	V
	voltage	10mA≤lout≤1A , Vin=3.25V				
		-1.2V	1.176	1.2	1.224	V
		0≤lout≤1A , Vin=3.2V				
		-1.8V	1.764	1.8	1.836	V
		0≤lout≤1A , Vin=3.8V				
		-2.5V	2.45	2.5	2.55	V
Vout	Output voltage	0≤lout≤1A , Vin=4.5V				
		-2.85V	2.793	2.85	2.907	V
		0≤lout≤1A , Vin=4.85V				
		-3.3V	3.234	3.3	3.366	V
		0≤lout≤1A , Vin=5.3V				
		-5.0V	4.9	5	5.1	V
		0≤lout≤1A , Vin=7.0V				
		-1.2V		0.03	0.2	%/V
		lout=10mA, 2.7V≪Vin≪10V				
		-ADJ		0.03	0.2	%/V
		lout=10mA, 2.75V≪Vin≪12V				
		-1.8V		0.03	0.2	%/V
		lout=10mA, 3.3V≪Vin≪12V				
$\triangle Vout$	Line	-2.5V		0.03	0.2	%/V
	regulation	lout=10mA, 4.0V≪Vin≪12V				
		-2.85V		0.03	0.2	%/V
		lout=10mA, 4.35V≪Vin≪12V				
		-3.3V		0.03	0.2	%/V
		lout=10mA, 4.8V≪Vin≪12V				
		-5.0V		0.03	0.2	%/V
		lout=10mA, 6.5V≲Vin≤12V				
		-1.2V		2	8	mV
		Vin =2.7V, 10mA≤lout≤1A				
		-ADJ		2	8	mV
		Vin =2.75V, 10mA≤lout≤1A				
		-1.8V		3	12	mV
		Vin =3.3V, 10mA≤lout≤1A				

REV.08 3 of 7



AMS1117

△Vout	Load	AMS1117-2.5V	4	16	mV
regulation		Vin =4.0V, 10mA≤lout≤1A			
		-2.85V	5	20	mV
		Vin =4.35V, 10mA≤lout≤1A			
		-3.3	6	24	mV
		Vin =4.8V, 10mA≤lout≤1A			
		-5.0	9	36	mV
		Vin =6.5V, 10mA≤lout≤1A			
Vdrop	Dropout voltage	lout =100mA	1.15	1.3	V
		lout=1A	1.3	1.5	V
Imin	Minimum load	AMS1117-ADJ	2	10	mA
	current				
		AMS1117-1.2V,Vin=10V	2	5	mA
		-1.8V,Vin=12V	2	5	mA
lq	Quiescent	-2.5V,Vin=12V	2	5	mA
	Current	-2.85V,Vin=12V	2	5	mA
		-3.3V,Vin=12V	2	5	mA
		-5.0V,Vin=12V	2	5	mA
lAdj	Adjust pin	AMS1117-ADJ	55	120	uA
	current	Vin=5V,10mA≤lout≤1A			
Ichange	ladj change	AMS1117-ADJ	0.2	10	uA
		Vin=5V,10mA≤lout≤1A			
Δ V / Δ T	Temperature		±100		ppm
	coefficien		 		
Α	Thermal	SOT-223	 20		°C AA/
$_{\theta}$ 1C	resistance	301-223	20		°C/W

Note1: All test are conducted under ambient temperature 25° C and within a short period of time 20ms

Note2: Load current smaller than minimum load current of AMS1117-ADJ will lead to unstable or oscillation output.

REV.08 4 of 7

Detailed Description

AMS1117 is a series of low dropout voltage, three terminal regulators. Its application circuit is very simple: the fixed version only needs two capacitors and the adjustable version only needs two resistors and two capacitors to work. It is composed of some modules including start-up circuit, bias circuit, bandgap, thermal shutdown, power transistors and its driver circuit


The thermal shut down modules can assure chip and its application system working safety when the junction temperature is larger than 140°C.

The bandgap module provides stable reference voltage, whose temperature coefficient is compensated by careful design considerations. The temperature coefficient is under 100 ppm/°C. And the accuracy of output voltage is guaranteed by trimming technique.

Typical Application

AMS1117 has an adjustable version and six fixed versions (1.2V, 1.8V, 2.5V, 2.85V, 3.3V and 5V)


Fixed Output Voltage Version



Application circuit of AMS1117 fixed version

- Recommend using 10uF tan capacitor as bypass capacitor (C1) for all application circuit.
- Recommend using 10uF tan capacitor to assure circuit stability.

Adjustable Output Voltage Version



Application Circuit of AMS1117-ADJ

The output voltage of adjustable version follows the equation: Vout= $1.25 \times (1+R2/R1)+IAdj \times R2$. We can ignore IAdj because IAdj (about 50uA) is much less than the current of R1 (about 2~10mA).

1) To meet the minimum load current (>10mA) requirement, R1 is recommended to be 125ohm or lower. As AMS1117-ADJ can keep itself stable at load current about 2mA, R1 is not allowed to be higher than 625ohm.

REV.08 5 of 7

AMS1117

2) Using a bypass capacitor (C_{ADJ}) between the ADJ pin and ground can improve ripple rejection. This bypass capacitor prevents ripple from being amplified as the output voltage is increased. The impedance of C_{ADJ} should be less than R1 to prevent ripple from being amplified. As R1 is normally in the range of $100\Omega\sim500\Omega$, the value of C_{ADJ} should satisfy this equation: $1/(2 \pi \times f_{\text{ripple}} \times C_{\text{ADJ}}) < R1$.


Thermal Considerations

We have to take heat dissipation into great consideration when output current or differential voltage of input and output voltage is large. Because in such cases, the power dissipation consumed by AMS1117 is very large. AMS1117 series uses SOT-223 package type and its thermal resistance is about 20°C/W. And the copper area of application board can affect the total thermal resistance. If copper area is 5cm*5cm (two sides), the resistance is about 30°C/W. So the total thermal resistance is about 20°C/W + 30°C/W. We can decrease total thermal resistance by increasing copper area in application board. When there is no good heat dissipation copper are in PCB, the total thermal resistance will be as high as 120°C/W, then the power dissipation of AMS1117 could allow on itself is less than 1W. And furthermore, AMS1117 will work at junction temperature higher than 125°C under such condition and no lifetime is guaranteed.


Typical Performance Characteristics

T_A=25°C, unless otherwise noted.


Line regulation




Dropout voltage



Load regulation




Thermal performance with OTP





REV.08 6 of 7



SOT-223 PACKAGE OUTLINE DIMENSIONS







Symbol	Dimensions In	Millimeters	Dimensions	In Inches	
Symbol	Min	Max	Min	Max	
Α	1.520	1.800	0.060	0.071	
A1	0.000	0.100	0.000	0.004	
A2	1.500	1.700	0.059	0.067	
b	0.660	0.820	0.026	0.032	
С	0.250	0.350	0.010	0.014	
D	6.200	6.400	0.244	0.252	
D1	2.900	3.100	0.114	0.122	
E	3.300	3.700	0.130	0.146	
E1	6.830	7.070	0.269	0.278	
е	2.300(BSC)		2.300(BSC) 0.091		BSC)
e1	4.500	4.700	0.177	0.185	
L	0.900	1.150	0.035	0.045	
θ	0°	10°	0°	10°	

REV.08 7 of 7