











CSD17577Q5A

SLPS516-AUGUST 2014

## CSD17577Q5A 30-V N-Channel NexFET™ Power MOSFET

#### **Features**


- Low Q<sub>a</sub> and Q<sub>ad</sub>
- Low Thermal Resistance
- Avalanche Rated
- Pb Free Terminal Plating
- **RoHS Compliant**
- Halogen Free
- SON 5 mm × 6 mm Plastic Package

## 2 Applications

- Point of Load Synchronous Buck in Networking, Telecom, and Computing Systems
- Optimized for Control, and Sync FET Applications

## Description

This 30 V, 3.5 m $\Omega$ , SON 5 mm × 6 mm NexFET<sup>TM</sup> power MOSFET is designed to minimize resistance in power conversion applications.



## **Product Summary**

$T_A = 25^\circ$	С	TYPICAL VA	UNIT		
$V_{DS}$	Drain-to-Source Voltage 30				
$Q_g$	Gate Charge Total (4.5 V) 13				
$Q_{gd}$	Gate Charge Gate-to-Drain	2.8	nC		
В	Drain-to-Source On-Resistance	V <sub>GS</sub> = 4.5 V 4.8		mΩ	
R <sub>DS(on)</sub>	Drain-to-Source On-Resistance	V <sub>GS</sub> = 10 V 3.5		mΩ	
$V_{GS(th)}$	Threshold Voltage	1.4	V		

## Ordering Information<sup>(1)</sup>


Device	Qty	Media	Package	Ship
CSD17577Q5A	2500	13-Inch Reel	SON 5 × 6 mm	Tape and
CSD17577Q5AT	250	7-Inch Reel	Plastic Package	Reel

(1) For all available packages, see the orderable addendum at the end of the data sheet.


#### **Absolute Maximum Ratings**

$T_A = 2$	5°C	VALUE	UNIT
$V_{DS}$	Drain-to-Source Voltage	30	٧
$V_{GS}$	Gate-to-Source Voltage	±20	٧
	Continuous Drain Current (Package limited)	60	
I <sub>D</sub>	Continuous Drain Current (Silicon limited), $T_C = 25$ °C	83	Α
	Continuous Drain Current (1)	22	
I <sub>DM</sub>	Pulsed Drain Current (2)	280	Α
n	Power Dissipation <sup>(1)</sup>	3	W
$P_D$	Power Dissipation, T <sub>C</sub> = 25°C	53	VV
T <sub>J</sub> , T <sub>stg</sub>	Operating Junction and Storage Temperature Range	-55 to 150	°C
E <sub>AS</sub>	Avalanche Energy, single pulse $I_D = 28$ , $L = 0.1$ mH, $R_G = 25$ $\Omega$	39	mJ

- (1) Typical  $R_{\theta JA}=40^{\circ} C/W$  on a 1-inch  $^2$  , 2-oz. Cu pad on a 0.06-inch thick FR4 PCB.
- (2) Max R<sub>θ,IC</sub> = 2.8°C/W, pulse duration ≤100 μs, duty cycle ≤1%



#### **Gate Charge**







## **Table of Contents**

	Features		6.1 Trademarks
	Description 1		6.3 Glossary
	Revision History2	7	Mechanical, Packaging, and Orderable
5	Specifications3		Information 8
	5.1 Electrical Characteristics		7.1 Q5A Package Dimensions
	5.2 Thermal Information		7.2 Recommended PCB Pattern
	5.3 Typical MOSFET Characteristics		7.3 Recommended Stencil Opening
6	Device and Documentation Support		7.4 Q5A Tape and Reel Information

## 4 Revision History

DATE	REVISION	NOTES
August 2014	*	Initial release.

Submit Documentation Feedback

## 5 Specifications

www.ti.com

#### 5.1 Electrical Characteristics

 $(T_{\Delta} = 25^{\circ}C \text{ unless otherwise stated})$ 

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
STATIC	CHARACTERISTICS					
BV <sub>DSS</sub>	Drain-to-Source Voltage	V <sub>GS</sub> = 0 V, I <sub>D</sub> = 250 μA	30			V
I <sub>DSS</sub>	Drain-to-Source Leakage Current	V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 24 V			1	μΑ
I <sub>GSS</sub>	Gate-to-Source Leakage Current	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = 20 V			100	nA
V <sub>GS(th)</sub>	Gate-to-Source Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250 \mu A$	1.1	1.4	1.8	V
В	Drain-to-Source On-Resistance	$V_{GS} = 4.5 \text{ V}, I_D = 10 \text{ A}$		4.8	5.8	mΩ
R <sub>DS(on)</sub>	Drain-to-Source On-Resistance	$V_{GS} = 10 \text{ V}, I_D = 18 \text{ A}$		3.5	4.2	mΩ
g <sub>fs</sub>	Transconductance	V <sub>DS</sub> = 3 V, I <sub>D</sub> = 18 A		79		S
DYNAMI	C CHARACTERISTICS					
C <sub>iss</sub>	Input Capacitance		,	1780	2310	pF
C <sub>oss</sub>	Output Capacitance	$V_{GS} = 0 \text{ V}, V_{DS} = 15 \text{ V}, f = 1 \text{ MHz}$		208	270	pF
C <sub>rss</sub>	Reverse Transfer Capacitance			79	102	pF
$R_G$	Series Gate Resistance			1.4	2.8	Ω
$Q_g$	Gate Charge Total (4.5 V)			13	17	nC
Qg	Gate Charge Total (10 V)			27	35	nC
Q <sub>gd</sub>	Gate Charge Gate-to-Drain	V <sub>DS</sub> = 15 V, I <sub>D</sub> = 18 A		2.8		nC
$Q_{gs}$	Gate Charge Gate-to-Source			5.1		nC
Q <sub>g(th)</sub>	Gate Charge at V <sub>th</sub>			2.5		nC
Q <sub>oss</sub>	Output Charge	V <sub>DS</sub> = 15 V, V <sub>GS</sub> = 0 V		6		nC
t <sub>d(on)</sub>	Turn On Delay Time			3		ns
t <sub>r</sub>	Rise Time	V <sub>DS</sub> = 15 V, V <sub>GS</sub> = 10 V,		12		ns
t <sub>d(off)</sub>	Turn Off Delay Time	$I_{DS} = 18 \text{ A}, R_G = 0 \Omega$		18		ns
$t_f$	Fall Time			2		ns
DIODE C	CHARACTERISTICS					
$V_{SD}$	Diode Forward Voltage	I <sub>SD</sub> = 18 A, V <sub>GS</sub> = 0 V		8.0	1	V
Q <sub>rr</sub>	Reverse Recovery Charge	V <sub>DS</sub> = 15 V, I <sub>F</sub> = 18 A,		8.2		nC
t <sub>rr</sub>	Reverse Recovery Time	di/dt = 300 A/µs		9.3		ns

## 5.2 Thermal Information


 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$ 

	THERMAL METRIC	MIN	TYP	MAX	UNIT
$R_{\theta JC}$	Junction-to-Case Thermal Resistance <sup>(1)</sup>			2.8	°C/W
$R_{\theta JA}$	Junction-to-Ambient Thermal Resistance (1)(2)			50	C/VV


<sup>(1)</sup> R<sub>0JC</sub> is determined with the device mounted on a 1-inch² (6.45-cm²), 2-oz. (0.071-mm thick) Cu pad on a 1.5-inches × 1.5-inches (3.81-cm × 3.81-cm), 0.06-inch (1.52-mm) thick FR4 PCB. R<sub>0JC</sub> is specified by design, whereas R<sub>0JA</sub> is determined by the user's board design.

(2) Device mounted on FR4 material with 1-inch<sup>2</sup> (6.45-cm<sup>2</sup>), 2-oz. (0.071-mm thick) Cu.

Product Folder Links: CSD17577Q5A




Max  $R_{\theta JA} = 50^{\circ} C/W$  when mounted on 1 inch² (6.45 cm²) of 2-oz. (0.071-mm thick) Cu.



Max  $R_{\theta JA} = 140^{\circ} C/W$  when mounted on a minimum pad area of 2-oz. (0.071-mm thick) Cu.

## 5.3 Typical MOSFET Characteristics

(T<sub>A</sub> = 25°C unless otherwise stated)



Submit Documentation Feedback


Copyright © 2014, Texas Instruments Incorporated



www.ti.com

# **Typical MOSFET Characteristics (continued)**

(T<sub>A</sub> = 25°C unless otherwise stated)







Figure 2. Saturation Characteristics






Figure 3. Transfer Characteristics




Figure 4. Gate Charge




Figure 5. Capacitance





Figure 6. Threshold Voltage vs Temperature

Figure 7. On-State Resistance vs Gate-to-Source Voltage

## TEXAS INSTRUMENTS

## **Typical MOSFET Characteristics (continued)**

## (T<sub>A</sub> = 25°C unless otherwise stated)







Figure 8. Normalized On-State Resistance vs Temperature








Figure 10. Maximum Safe Operating Area

Figure 11. Single Pulse Unclamped Inductive Switching




Figure 12. Maximum Drain Current vs Temperature

Submit Documentation Feedback

Copyright © 2014, Texas Instruments Incorporated



www.ti.com SLPS516-AUGUST 2014

## 6 Device and Documentation Support

## 6.1 Trademarks

NexFET is a trademark of Texas Instruments.

## 6.2 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## 6.3 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.


Product Folder Links: CSD17577Q5A



## 7 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## 7.1 Q5A Package Dimensions




DIM	MILLIMETERS							
DIM	MIN	NOM	MAX					
А	0.90	1.00	1.10					
b	0.33	0.41	0.51					
С	0.20	0.25	0.34					
D1	4.80	4.90	5.00					
D2	3.61	3.81	4.02					
E	5.90	6.00	6.10					
E1	5.70	5.75	5.80					
E2	3.38	3.58	3.78					
E3	3.03	3.13	3.23					
е	1.17	1.27	1.37					
e1	0.27	0.37	0.47					
e2	0.15	0.25	0.35					
Н	0.41	0.56	0.71					
K	1.10	_	_					
L	0.51	0.61	0.71					
L1	0.06	0.13	0.20					
θ	0°	_	12°					

Submit Documentation Feedback



## 7.2 Recommended PCB Pattern




## **Recommended PCB Pattern (continued)**

DIM	MILLIM	ETERS	INCHES			
DIM	MIN	MAX	MIN	MAX		
F1	6.205	6.305	0.244	0.248		
F2	4.46	4.56	0.176	0.18		
F3	4.46	4.56	0.176	0.18		
F4	0.65	0.7	0.026	0.028		
F5	0.62	0.67	0.024	0.026		
F6	0.63	0.68	0.025	0.027		
F7	0.7	0.8	0.028	0.031		
F8	0.65	0.7	0.026	0.028		
F9	0.62	0.67	0.024	0.026		
F10	4.9	5	0.193	0.197		
F11	4.46	4.56	0.176	0.18		


For recommended circuit layout for PCB designs, see application note SLPA005 – Reducing Ringing Through PCB Layout Techniques.

## 7.3 Recommended Stencil Opening



# TEXAS INSTRUMENTS

## 7.4 Q5A Tape and Reel Information



#### Notes:

- 1. 10-sprocket hole-pitch cumulative tolerance ±0.2
- 2. Camber not to exceed 1 mm in 100 mm, noncumulative over 250 mm
- 3. Material: black static-dissipative polystyrene
- 4. All dimensions are in mm (unless otherwise specified).
- 5. A0 and B0 measured on a plane 0.3 mm above the bottom of the pocket.

Submit Documentation Feedback



## PACKAGE OPTION ADDENDUM

7-Nov-2018

#### **PACKAGING INFORMATION**

Orderable Device	Status	Package Type	_	Pins	_	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
CSD17577Q5A	ACTIVE	VSONP	DQJ	8	2500	Pb-Free (RoHS Exempt)	CU SN	Level-1-260C-UNLIM	-55 to 150	CSD17577	Samples
CSD17577Q5AT	ACTIVE	VSONP	DQJ	8	250	Pb-Free (RoHS Exempt)	CU SN	Level-1-260C-UNLIM	-55 to 150	CSD17577	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.





7-Nov-2018

#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<a href="www.ti.com/legal/termsofsale.html">www.ti.com/legal/termsofsale.html</a>) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated