

SR320 THRU SR3200

SCHOTTKY BARRIER RECTIFIER




REVERSE VOLTAGE: 20 to 200 VOLTS
FORWARD CURRENT: 3.0 AMPERE

FEATURES

- High current capability
- High surge current capability
- Low forward voltage drop
- Exceeds environmental standards of MIL-S-19500/228
- For use in low voltage, high frequency inverters free wheeling, and porlarity protection applications

MECHANICAL DATA

Case: Molded plastic, DO-201AD
 Epoxy: UL 94V-O rate flame retardant
 Lead: Axial leads, solderable per MIL-STD-202, method 208 guaranteed
 Polarity: Color band denotes cathode end
 Mounting position: Any
 Weight: 0.04ounce, 1.1gram



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.
 Single phase, half wave, 60Hz, resistive or inductive load.
 For capacitive load, derate current by 20%.

	Symbols	SR320	SR330	SR340	SR350	SR360	SR380	SR3100	SR3150	SR3200	Units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	20	30	40	50	60	80	100	150	200	Volts
Maximum RMS Voltage	V_{RMS}	14	21	28	35	42	56	70	105	140	Volts
Maximum DC Blocking Voltage	V_{DC}	20	30	40	50	60	80	100	150	200	Volts
Maximum Average Forward Rectified Current .375"(9.5mm) Lead Length	$I_{(AV)}$	3.0									Amp
Peak Forward Surge Current, 8.3ms single half-sine-wave superimposed on rated load (JEDEC method)	I_{FSM}	80									Amp
Maximum Forward Voltage at 3.0A DC and 25°C	V_F	0.55			0.7		0.85		0.95		Volts
Maximum Reverse Current at $T_A=25^\circ C$ at Rated DC Blocking Voltage $T_A=100^\circ C$	I_R	2.0									mAmp
Typical Junction Capacitance (Note 1)	C_J	30									pF
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	40									°C/W
Operating Junction Temperature Range	T_J	-55 to +125				-55 to +150					°C
Storage Temperature Range	T_{stg}	-55 to +150									°C

NOTES:

- 1- Measured at 1 MHz and applied reverse voltage of 4.0 VDC.
- 2- Thermal Resistance From Junction to Ambient 0.375"(9.5mm) lead length P.C.B. Mounted

SR320 THRU SR3200

SCHOTTKY BARRIER RECTIFIER



RATINGS AND CHARACTERISTIC CURVES




FIG.1 TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2 TYPICAL REVERSE CHARACTERISTICS




FIG.3 TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.4 TYPICAL JUNCTION CAPACITANCE




FIG.5 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT