

Part No.

: 103JT Series

Spec. No.

: S08-U007

CHECKED BY	SUBMITTED BY



SPECIFICATIONS	User Part No.;	Approved	Checked	Drawn
Application;	Part No.; 103JT Series	技師 08.7.21 池田	20.7.15	0 8, 7, 15

1. Scope

This specification defines rating, dimensions, electric properties, mechanical properties and climatic properties for the following part.

2. Meaning of part number

Example 103 JT - 050

1 : Zero-power resistance 103→10×10³ Ω



3 : Dimension

050 → 50mm



3. Rating and Characteristic

		Tolerance			Dissipation	Thermal time	Rated
	Zero-power	of	B-value	Tolerance	factor	constant	maximum
Part No.	resistance	zero-power		of B-value			power
	(R25)	resistance	(B25/85)		(in still air)	(in still air)	dissipation
	[kΩ]	[%]	[K]	[%]	[mW/deg. C]	[s]	[mW]
103JT-025							
103JT-050	400		0.405	.,,,,	A	A	0.5
103JT-075	10.0	+/- 1.0	3 435	+/- 1.0	Approx. 0.7	Approx. 5.0	3.5
103JT-100							

4. Operating temperature range

: -50 deg. C ~ +90 deg. C


5. Storage temperature range

: -10 deg. C ~ +40 deg. C

Company ;	Note;	Date	15-Jul-08
SE/MITEC Ishizuka Electronics Corporation		Spec.No.	S08-U007

User Part No.	
Part No.	103JT Series

6. Dimensions



25.0+/-1.0

50.0+/-1.0


75.0+/-1.0

100.0+/-1.0

Unit: mm



7. Marking



103JT-025

103JT-050

103JT-075

103JT-100

- 1. Trade mark
- 5
- 2. Zero-power resistance at 25 deg. C $103 \rightarrow 10 \times 10^3 \, [\Omega]$
- 3. Lot No. X:0~9, A~Z

8. Properties

8.1 Electric properties

Item	Test conditions	Criteria
8.1.1 Insulation resistance	Measured at DC. 100 V between part of the film area and lead-wire.	Over 100 MΩ
8.1.2 Voltage proof	Measured at AC. 100 V for one minute between the film area and lead-wire.	Limited current is under 1 mA or more.

SENTE Ishizuka Electronics Corporation

Spec.No.

S08-U007

User Part No. Part No. 103JT Series

8.2 Mechanical prope	erties	
Item	Test conditions	Criteria
8.2.1	After 1 N loading weight is applied to the wire	Variation of R ₂₅ and
Tensile of terminations	terminations for 10 s +/- 1 s.	B _{25/85} after test shall of
	1N———	within +/- 1 % of those
	Rubber	of the initial values.
		No visible damage.
8.2.2	After three times natural fall to a maple board	
Free fall	from 0.75 m high.	
8.2.3	The lead wire shall be bent into 90 angle and	Variation of R ₂₅ and
Bending of	bent back in one operation.	B _{25/85} after test shall of
terminations	R1.0mm	within +/- 1 % of those
		of the initial values.
	7//////////////////////////////////////	Not to produce
	3.0 mm min	disconnection of a
		lead.
	7.0 mm min.	
8.2.4	Terminals of the test samples shall be one time	Soldered newly, more
Solderability	immersed into solder bath at 245 deg. C +/- 5	than 90%
	deg. C for 2 s ~ 3 s.	
	Solder : Sn-3.0Ag-0.5Cu	
	Flux : Rosin 25%, Ethyl alcohol 75%	
8.2.5	Terminals of the test samples shall be dipped	Variation of R25 and
Resistance to	into the soldering bath at 260 deg. C +/- 5 deg.	B _{25/85} after test shall of
soldering heat	C to the point 2 mm from the body and held	within +/- 1 % of those
	there for 5 s +/- 1 s.	of the initial values.
		No visible damage.
8.2.6	Put a test sample between 2 glass epoxy plates	
Press of termination	which is 1.6 mm thickness and 40 square mm	
	and press 30 N weight for 60 s +/- 3 s from	
	both side.	
	3014	
	Vanimumis	
0 0 7	One time 4N lead for 40 - 1/ 4	Variation of D
8.2.7 Tensile of terminations	One time 1N load for 10 s +/- 1 s as shown	Variation of R25 and
rensile or terminations	below.	B _{25/85} after test shall be
and the second second second second second		within +/- 1 % of those
1000		of the initial values.
/ 监 图。\		No visible damage.
10 10 25	(3 _{mm)} 1N	(except the bend of the
(12, 10, 25)		lead wire due to the 1N
[設計部門]	, The state of the	load.)
/ NX A AL 1/		1

ELLI Ishizuka Electronics Corporation	Spec.No.	S08-U007
---------------------------------------	----------	----------

User Part No.	
Part No.	103JT Series

8.3 Climatic properties

8.3 Climatic propertion		
ltem	Test conditions	Criteria
8.3.1	At -55 deg. C +/- 3 deg. C for 1 000 h and then	Variation of R ₂₅ and
Cold	stored at room temperature and humidity for 1 h.	B _{25/85} after test shall be
		within +/- 1 % of those
8.3.2	At +90 deg. C +/- 3 deg. C for 1 000 h and then	of the initial values.
Dry heat	stored at room temperature and humidity for 1 h.	-
8.3.3	At +90 deg. C +/- 3 deg. C with the DC. 1 mA	and the second s
Dry heat	load for 1 000 h and then stored at room	L AR W
(Under loading)	temperature and humidity for 1 h.	Later Come
, -,		('12, 10, 2
8.3.4	100 times in the following order and conditions	1 26 31 37
Change of temperature	and then stored at room temperature and	\ 淡計部
	humidity for 1 h.	The second secon
	"At room temperature (Initial value)."	
	"At -25 deg. C +/- 3 deg. C for 30 min."	
	"At room temperature for 3 min."	
	"At +90 deg. C +/- 3 deg. C for 30 min."	
	"At room temperature for 3 min."	
8.3.5	At +40 deg. C +/- 3 deg. C, 90 %RH ~ 95 %RH	-
Damp heat	for 1 000 h and then stored at room temperature	
	and humidity for 1 h.	
8.3.6	At +40deg. C +/- 3 deg. C, 90 %RH ~ 95 %RH	
Damp heat	lwith the DC. 1 mA load for 1 000 h and then	
Under loading)	stored at room temperature and humidity for 1 h.	
(Onder loading)	stored at room temperature and number of 111.	

Note

"Room temperature" is defined as the temperature between 15 deg. C and 35 deg. C.

"Room humidity" is defined as the humidity between 25 %RH ~ 75 %RH.

9. Packaging

9.1 Packaging Plastic bag

9.2 Quantity 1 000 pcs / bag

9.3 Label Part No., Type No., Quantity and Lot No. shall be the mention form on label.

User Part No.	
Part No.	103JT Series

Precautions for Use of JT Thermistor

Warning.

Comply with the following precautions for use, since JT Thermistor may be broken down or it may cause failure and/or malfunction of equipment.



- (1) Thermistor is designed for a particular use. Do not utilize it for other use applied.
- (2) Check by yourself performance and function of your equipment with the Thermistor by your actual evaluation test and reliability test.
- (3) Pay attention to voltage to be applied to the Thermistor because its lowered resistance by self-heating may cause failure and/or malfunction of equipment.
- (4) Do not use the Thermistor out of operating temperature range specified.
- (5) Take all possible measures such as a safety circuit or concomitance use of another Thermistor with same performance to prevent any accident.
- (6) Take measures as follows in case of electrical noise is concerned.
 - · A protect circuit.
 - · An electrical shield over the Thermistor including lead-wires.
- (7) When the Thermistor is sealed, examine a kind of sealant, quantity, curing condition and adhesiveness and confirm its reliability.
- (8) Do not apply rating power in excess of that specified.
- (9) Do not apply any mechanical impact such as falling or pressure in excess of those specified.
- (10) When lead-wires and covering films are bent, do not exceed 2.5N forced and 90° two times bend.
 - ※ One bend is defined as bend by 90° and then bend to the original position.
- (11) When lead-wires and covering films are cut or bent, proceed with holding the portion of 3 mm away from a Thermistor element.
- (12) Do not apply more than 1N force to the Thermistor in the axial direction.
- (13) When a terminal of the Thermistor is connected, keep it clean without such as blot or rust, otherwise it may cause poor contact.
- (14) When the Thermistor is soldered, do not melt films and/or solder of the Thermistor itself.
- (15) Do not attach a soldering iron to a Thermistor element and films.
- (16) Do not bend, hold with something hard and twist portion of the Thermistor element.
- (17) Do not keep using the Thermistor for a long time at more than 85 %RH, except when it is taken measures against humidity.
- (18) Give warning to a user not to touch the Thermistor, if the user can touch the Thermistor in your application.
- (19) Do not use the Thermistor under the following environment, except it is taken measures.
 - Corrosive gas. (Cl2, NH3, SOx, NOx etc)
 - · High conductive conditions, (electrolyte, water, saline solution and etc.)
 - · Acids, alkalis, organic solvent.
 - · Dusty place.
 - Condensing place

User Part No.	
Part No.	103JT Series

Caution.

Pay attention of the following cautions for use of JT Thermistor.



- (2) Pay attention to the following description when the Thermistor is installed to your equipment, otherwise it may cause malfunction of your equipment when the Thermistor can not detect real temperature.
 - When the Thermistor detects temperature of air or liquid, put the Thermistor in order to detect the certain ambient temperature and not to be affected by a heater a chiller.
 - When the Thermistor detects temperature of a solid substance, then fill thermal conductive grease or adhesive up between the substance and the Thermistor, and pay attention that the Thermistor is not affected by air-flow or wind from outside.
- (3) When the Thermistor is installed with pushing, pressing, clamping or inserting, then please consult us about installing condition such as mechanical properties of the Thermistor.
- (4) Pay attention to the following storage condition, otherwise it may cause deterioration and/or damage of the Thermistor.
 - Store the Thermistor at -10 deg. C ~ +40 deg. C, less than 75 %RH in a carton not to be loaded at a depository without rapid temperature change, direct sunlight, corrosive gas and dust,
 - Storage term limitation.
 Use the Thermistor up within 6 month after its delivery.
- (5) When something at more than 150 deg. C touches to the films of the Thermistor in soldering process, then the film may melt.



User Part No.	
Part No.	103JT Series

Revision records

Revision No.	Date	Revised by	Revision item	Former specification	New specification
а					
b					
С					
d					
е					
f					
g					
h					
i					
j					



STATE Ishizuka Electronics Corporation	Spec.No.	S08-U007
--	----------	----------