

8A, 20V - 100V Surface Mount Schottky Barrier Rectifier

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for over-voltage protection
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21

Δ	D	D	C	Δ	TI	O	N	S

- Switching mode power supply (SMPS)
- Adapters
- Lighting application
- Converter

MECHANICAL DATA

- Case: DO-214AB (SMC)
- Molding compound meets UL 94V-0 flammability rating
- Part no. with suffix "H" means AEC-Q101 qualified
- Packing code with suffix "G" means green compound (halogen-free)
- Moisture sensitivity level: level 1, per J-STD-020
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 0.21 g (approximately)

KEY PARAMETERS							
PARAMETER	VALUE	UNIT					
I _{F(AV)}	8	Α					
V_{RRM}	20 - 100	V					
I _{FSM}	150	Α					
Package	DO-214AB (SMC)						
Configuration	Single die						





DO-214AB (SMC)

ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)								
PARAMETER	SYMBOL	SK 82C	SK 83C	SK 84C	SK 85C	SK 86C	SK 810C	UNIT
Marking code on the device		SK 82C	SK 83C	SK 84C	SK 85C	SK 86C	SK 810C	
Repetitive peak reverse voltage	V_{RRM}	20	30	40	50	60	100	V
Reverse voltage, total rms value	V _{R(RMS)}	14	21	28	35	42	70	V
Maximum DC blocking voltage	V_{DC}	20	30	40	50	60	100	V
Forward current	I _{F(AV)}		•		3			А
Surge peak forward current, 8.3 ms single half sine-wave superimposed on rated load per diode	I _{FSM}			1	50			А
Critical rate of rise of off-state voltage	dV/dt	10,000					V/µs	
Junction temperature	TJ	- 55 to +125 - 55 to +150					°C	
Storage temperature	T _{STG}	- 55 to +150						°C



THERMAL PERFORMANCE								
PARAMETER	SYMBOL	TYP	UNIT					
Junction-to-ambient thermal resistance per diode	$R_{\Theta JA}$	20	°C/W					

PARAMETER		CONDITIONS	SYMBOL	TYP.	MAX.	UNIT
(4)	SK82C SK83C SK84C			-	0.55	V
Forward voltage per diode (1)	SK85C SK86C	$I_F = 8A, T_J = 25^{\circ}C$	V _F	-	0.75	V
	SK810C			-	0.90	V
Reverse current @ rated V _R pe	er diode ⁽²⁾	T _J = 25°C	I _R	-	0.5	mA
Reverse current @ rated V _R	SK82C SK83C SK84C	T _ 100°C	1	-	15	mA
per diode ⁽²⁾	SK85C SK86C SK810C	T _J = 100°C	l _R	-	10	mA

Notes:

- 1. Pulse test with PW=0.3 ms
- 2. Pulse test with PW=30 ms





ORDERING INFORMATION									
PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING				
SK8xxC (Note 1,2)	π	R7	G	SMC	850 / 7" Plastic reel				
		R6		SMC	3,000 / 13" Paper reel				
		M6		SMC	3,000 / 13" Plastic reel				
		V7		Matrix SMC	850 / 7" Plastic reel				
		V6		Matrix SMC	3,000 / 13" Plastic reel				

Note:

- "xx" defines voltage from 20V (SK82C) to 100V (SK810C)
 Only V6 and V7 are all green compound (halogen free)

EXAMPLE									
EXAMPLE P/N	PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION				
SK82CHR7G	SK82C	Н	R7	G	AEC-Q101 qualified Green compound				



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics





Fig.4 Typical Forward Characteristics



4



CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)

Fig.5 Maximum Non-repetitive Forward Surge Current





Fig.6 Typical Transient Thermal Characteristics




5




PACKAGE OUTLINE DIMENSIONS

DO-214AB (SMC)



DIM.	Unit	(mm)	Unit (inch)		
DIIVI.	Min.	Max.	Min.	Max.	
Α	2.90	3.20	0.114	0.126	
В	6.60	7.11	0.260	0.280	
С	5.59	6.22	0.220	0.245	
D	2.00	2.62	0.079	0.103	
E	1.00	1.60	0.039	0.063	
F	7.75	8.13	0.305	0.320	
G	0.10	0.20	0.004	0.008	
Н	0.15	0.31	0.006	0.012	

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
А	3.30	0.130
В	2.50	0.098
С	6.80	0.268
D	4.40	0.173
Е	9.40	0.370

MARKING DIAGRAM

Matrix SMC

SMC





P/N =Marking Code G =Green Compound

ΥW =Date Code F =Factory Code



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.