

Serial No. : 2020-0036 DATE: 2020/1/20

HONHEVER(HK)LIMITED

SPECIFICATION

Product Name	CRYSTAL OSCILLATOR	
Туре	DSA321SDN	
Nominal Frequency	19.200MHz	
Spec No.	7DD01920A07	

If there is a change in this specifications, the specification number may be changed.

	RECEIPT	
DATE		
RECEIVED	(signati	

General Manufacturer of Quartz Devices

DAISHINKU CORP.

1389 Shinzaike, Hiraoka-cho, Kakogawa, Hyogo 675-0194 Japan

Phone: (81)79-425-3161 Fax.:(81)79-425-1134 http://www.kds.info/index_en.htm

C.ENG. T. Hanales

ENG. Ekamoda

1. Device Name VC-TCXO

2. Model Name DSA321SDN

3. Nominal Frequency 19.200 MHz

4. Mass 0.03g max.

5. Absolute Maximum Ratings

	Item	Symbol	Rating	unit
1	Supply voltage	Vcc	-0.3~+4.6	V
2	Storage temperature range	T_stg	-40~+85	°C

6. Recommended Operating Conditions

		Item	Symbol	min.	typ.	max.	unit
	1	Supply voltage	Vcc	+2.97	+3.3	+3.63	V
	2	Load impedance (resistance part)	Load_R	9	10	11	kΩ
		(parallel capacitance)	Load_C	9	10	11	pF
	3	Control voltage range	Vcont	+0.5	+1.5	+2.5	V
Γ	4	Operating temperature range	T_OPR	-40	-	+85	°C

7. Electrical Characteristics

 $(T_A=-40\sim+85^{\circ}C, L_{OAD}_R//C=10k\Omega//10pF, V_{CC}=+3.3V, V_{CONT}=+1.5V, unless otherwise noted)$

	lt a un	Conditions				Natas	
	Item	Conditions	min.	typ	max.	unit	Notes
1	Current consumption		-	ı	+1.5	mA	
2	Output level		8.0	ı	1.2	V _{P-P}	1
3	Symmetry	GND level (DC cut)	40/60	ı	60/40	%	
4	Harmonics	2 nd and 3 rd Harmonics	-	ı	-8	dBc	
		Other Harmonics	-	ı	-15	dBc	
5	Frequency stability						
	1.Tolerance	At shipping Ref. to nominal frequency V _{CONT} =+1.5V	-	ı	±0.5	ppm	2
		After 2 times reflow Ref. to nominal frequency V _{CONT} =+1.5V	-	-	±1.0	ppm	2,3
	2.vs Temperature	T _A =-40~+85°C (V _{CONT} =+1.5V)	-	-	±1.0	ppm	4
		T _A =-30~+85°C (V _{CONT} =+1.5V)	-	-	±0.5	ppm	4
	3.vs Supply voltage	Vcc=+3.3V±10%	-	-	±0.2	ppm	
	4.vs Load variation	L _{OAD} _R//C=(10kΩ//10pF)±10%	-	-	±0.2	ppm	
	5.vs Aging	T _A =Room ambient	-	-	±3.0	ppm/10years	
6	Start up time	@90% of final Vo∪⊤ level	-	•	2.0	ms	
		Within ±0.5ppm of final frequency	-	-	2.0	ms	
7	Frequency control 1.Control range	V _{CONT} =+1.5±1.0V	±3	ı	±5	ppm	5
	2.Input resistance		500	-	-	kΩ	
8	SSB phase noise	Relative to f0 level offset 100Hz	-	-	-110	dBc/Hz	
		Relative to f0 level offset 1kHz	-	•	-130	dBc/Hz	
		Relative to f0 level offset 10kHz	-	•	-140	dBc/Hz	
		Relative to f0 level offset 100kHz	-	-	-145	dBc/Hz	


Notes

- 1. Clipped sine wave (DC-coupled)
- 2. T_A=+25°C
- 3. Please leave after reflow in 2h or more at room ambient.
- 4. Ref.to frequency (T_A=+25°C)
- 5. Positive slope (Frequency becomes high in proportion to frequency control voltage.)

TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	1/12

8. Outline, Pin Connections

<u>Outline</u>



Ц			0.25	
->	 > 	<	0.25	

10000
95.0 05.0 06.0 07.0
(INDEX)
#4 #3 #3 #3 #3 #3 #3 #3 #3 #3 #3 #3 #3 #3

Pin Connections

Pin No.	Connection
#1	V _{CONT}
#2	GND
#3	Output
#4	Vcc

Marking

(1) Frequency 19.20 (MHz, 4digits)

(2) Model code


Year (1digit) +Week (2digits) (3) Date code

e.g.2020/01/01 -> 001

unit: mm

Dimensional Tolerance: ±0.15 (Unless otherwise noted)

9. Measurement Circuit



TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	2/12

10. Mechanical Characteristics

	All test is performed after 3times reflow (Clause.13) except 10.10 (Resistance to soldering heat)						
	Item	Description	Requirements				
1	Drop	Natural drop (On concrete) 1.6mm thick FR-4 board mounting on set or test fixture.(Aluminum material weight 100g) Height: 150cm Test cycle: 10cycles Direction: X,Y,Z,6directions Reference specification EIAJ-ED-4702C Method 5	df/f=<±1.0ppm				
2	Vibration	Sweep range: 10~2000Hz Sweep speed: 20min/cycle Amplitude: 1.5mm (10~55Hz) Acceleration: 200m/s² (55~2000Hz) Direction: X,Y,Z,3directions Test time: each 2h Reference specification: IEC 60068-2-6	df/f=<±0.5ppm				
3	Shock	Acceleration: 1000m/s² Direction: X,Y,Z,6directions Duration: 6ms Test cycle: 10times/each direction Reference specification IEC 60068-2-27	df/f=<±0.5ppm				
4	PCB bend strength	PWB: t=1.6mm Pressure Jig Tip: R5 PCB holding distance: 90mm Pressure speed: 1.0mm/s Bend width: 3mm Duration: 5±1s Reference specification IEC 60068-2-21 Ue1	df/f=<±0.5ppm No visible damage. No leak damage.				
5	Adherence nature	PWB : t=1.6mm Pressure Jig Tip : R0.5 Direction : X,Y, 2directions Pressure : 10N Duration : 10±1s Reference specification IEC 60068-2-21 Ue3	df/f=<±0.5ppm No visible damage. No leak damage.				
6	Package strength	Pressure Jig Tip: R0.5 Product holding distance 1/2 product long side Z axis direction from top of product Pressure:10N Duration: 10±1s Reference specification IEC 60068-2-77	df/f=<±0.5ppm No mechanical damage. No leak damage.				
7	Fine leak	It shall be measured by the He leak detector Reference specification IEC 60068-2-17	Less than 1.0x10 ⁻⁹ Pa·m³/s.				
8	Solderability	Coating ROSIN Flux. Solder bath temperature :+245±5°C Duration : 3±0.5s Reference specification IEC 60068-2-58	A new uniform coating of solder shall cover a minimum of 90% of the surface being immersed.				
9	Resistance to soldering heat	Reflow In refer to temperature profile shown in clause 13. Test cycle: 3cycles It shall be measured after 2h at room temperature, humidity. Measurement after 24h or 48h. Reference specification IEC 60068-2-58	df/f=<±1.0ppm dVout=<±0.2V _{P-P} No visible damage.				

TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	3/12

11. Environmental Characteristics


All test is performed after 3times reflow (Clause13)

	Item	Description	Requirements
1	Low temperature	Temperature : -40±2°C	d5/5- < 1.4 On the
	storage	Duration : 240h	df/f=<±1.0ppm
	_	It shall be measured after 2h at room temperature,	dV _{OUT} =<±0.2V _{P-P} The electrical characteristics
		humidity.	are satisfied.
		Reference specification IEC 60068-2-1 Ab	are satisfied.
2	High temperature	Temperature : +85±2°C	df/f=<±1.0ppm
	storage	Duration: 240h	dVout=<±0.2Vp-p
		It shall be measured after 2h at room temperature,	The electrical characteristics
		humidity.	are satisfied.
		Reference specification IEC 60068-2-2 Bb	are satisfied.
3	Humidity	Temperature : +85±2°C	
		Humidity: 85±5% R.H.	df/f=<±1.0ppm
		Duration: 240h	$dV_{OUT} = < \pm 0.2V_{P-P}$
		It shall be measured after 2h at room temperature,	The electrical characteristics
		humidity.	are satisfied.
		Reference specification IEC 60068-2-78	
4	HTB	Temperature : +85±2°C	
		Duration: 240h	df/f=<±1.0ppm
		BIAS : Max value of supply voltage	$dV_{OUT} = < \pm 0.2V_{P-P}$
		It shall be measured after 2h at room temperature,	The electrical characteristics
		humidity.	are satisfied.
		Reference specification IEC 60068-2-2 Bb	
5	THB	Temperature : +40±2°C	
		Humidity : 90∼95% R.H.	df/f=<±1.0ppm
		Duration : 240h	dV _{OUT} =<±0.2V _{P-P}
		BIAS : Max value of supply voltage	The electrical characteristics
		It shall be measured after 2h at room temperature,	are satisfied.
		humidity.	
_	Th	Reference specification IEC 60068-2-78	
6	Thermal shock	Thermal shock : -40°C:30min ⇔ +85°C:30min	JE/E 41.4 October
		Test cycle : 200cycles	df/f=<±1.0ppm
		Shift time: 2~3min	dV _{OUT} =<±0.2V _{P-P}
		It shall be measured after 2h at room temperature,	The electrical characteristics
		humidity.	are satisfied.
7	ESD	Reference specification IEC 60068-2-14	
′	ESD	Model : Charge Device Model (CDM)	
		V=±0.75kV Number of times : 3times	df/f=<±1.0ppm
		Test Terminal : Each terminals	$dV_{OUT} = < \pm 0.2V_{P-P}$
		Except common terminal	The electrical characteristics
		(Connect to test terminal)	are satisfied.
		Reference specification EIA/JESD22-C101	
		Model :Human Body Model (HBM)	
		V=±1.5kV (C=100pF, R=1500Ω)	
		Number of times: 1time	df/f=<±1.0ppm
		Test Terminal : Each terminals	dV _{OUT} =<±0.2V _{P-P}
		Except common terminal.	The electrical characteristics
		(Connect to test terminal)	are satisfied.
		Reference specification EIA/JESD22-A114	
Ь	l	Noticionos apecinication Lin/JEODZZ-ATT4	<u> </u>


TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	4/12

12. Flatness of Terminal

When the component is placed on the flat surface, the gap from the connecting terminal shall not exceed 0.05 mm.



13. Reflow Profile




Ts	(°C)	150~200
ts time	(s)	60~120
T∟	(°C)	217
t time	(s)	60~90
Тр	(°C)	max.260
tp	(s)	max.30

14. Terminals / Land Pattern Layout


14.1 Terminals

A through hole is not located on the bottom (mounting side).



14.2 Land Pattern Layout

The following land pattern is reference design. The electrical characteristic shall be satisfied with mounting to this land. The land pattern can be changed in the limits to which test land and mounting land are not connected. And it does not any effect to the electrical characteristics.



unit: mm

Dimensional Tolerance: ±0.15mm

TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date 2020/01/20	Spec. No. 7DD01920A07	Rev.	Page 5/12

15. Packing Condition

15.1 Taping package

(1) Emboss tape format and dimensions

See Fig.1

(2) Quantity on reel

2000pcs. max. / reel

(3) Taping specification

See Fig.2

No lack of a product.

(4) Reel specification

See Fig.3

(5) Taping material list

See right table.

15.2 Packing

The products packed in the antistatic bag.

*Moisture sensitivity level: IPC/JEDEC Standard J-STD-033 / Level1

No dry pack required and baking after re-storage is unnecessary.

15.3 Packing box

Max 10reels/packing box. However, in the case of less than 10reels, It is contained by any boxes.

Taping material List

Emboss: PS (Conductivity)

Reel: PS (Conductivity)

Cover Tape: PET + Olefin Resin (Conductivity)

The space in a box is fill up with cushion.

15.4 Label detail

A Lot label is put on a reel, and Indication label and Pb-Free label is put on packing box.


Indication label

TYPE XXXXXXXX SPEC NO. XXXXXXXXXXX PARTS NO. XXXXXXXXXXX LOTNO. XXXXXXXXX FREQ. XX.XXX MHZ Q'TY XXXX CTL NO. XXXXXXXXX MADE IN JAPAN


Pb-free Label



KDS Lot label (Example)




TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	6/12




The product is packed up with the method which does not break in the handling by shipping agent.

TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	7/12

DM-Z0002: Style-010 Ver.1





When a tape end is taken out to the front, sprocket holes becomes right hand side.

Peel strength

Pulling angle 165~180° pulling speed at 300mm/min, strength should be 0.1~0.7N.





Fig.2. Taping specification

TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	9/12



Material:Polystyrene (Conductivity) unit:mm

Section A




Fig.3. Reel specification

TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	10/12

16. Notes on mounting and handling

- 16.1 Storage environment
 - (1) The temperature and humidity of storage place, Please give +5~+40°C and 40~85% R.H. as standard.
 - (2) Please use this product within one year from the packing label date of issue.
 - (3) Please avoid the place which generates corrosive gas, and the place with much dirt.
 - (4) Please keep it in a place with little temperature change.

Dew condensation arises owing to rapid temperature change and solderability becomes bad.

- 16.2 Be cautions to static electricity and high voltage.
- 16.3 This product has sufficient durability to fall and vibration. However, conditions may change to the fall after mounting to PWB, and vibration. When you should drop on floor the PWB which mounted the product or too much shock is added. Please use after performance check.
- 16.4 Please check that the curvature of the substrate at the time of substrate cutting does not affect product. Moreover, especially when a product is near the position of PWB guide pin, and the position of PWB break, be careful.
- 16.5 The part concerned does not correspond to washing.
- 16.6 Please repair at +260°C in 10s with hot air or +350°C in 5s with solder Iron.

17. Mandatory control

17.1 Ozone-depleting substance

It regulates by the U.S. air purifying method (November, 1990 establishment). ODS of CLASS1 and CLASS2 is not contained or used.

17.2 PBDE, PBBs

PBDE, PBBs are not contained into all the material currently used for this product.

17.3 RoHS

Following material restricted by RoHS (2011/65/EU, (EU) 2015/863) is not included or used.

17.4 Law Concerning Examination and Regulation of Manufacture, etc. of Chemical Substances

All the material currently used for this product is based on "Law Concerning Examination and Regulation of Manufacture, etc. of Chemical Substances". It is a registered material.

17.5 Lead

Leads, such as solder, are not used for this product. (Lead Free)

17.6 About the existence of silver and mercury use

The silver of very small quantity is contained in the conductive adhesives used for adhesion of Blank. Moreover, mercury is used. It does not get down.

18. The country of origin / factory name / address

Country of origin: Japan

Factory name: DAISHINKU Corp. Tottori Production Div.
Address: 7-3-21 Wakabadai minami, Tottori 689-1112

TITLE	Remark		
DSA321SDN TYPE CRYSTAL OSCILLATOR SPECIFICATION			
Date	Spec. No.	Rev.	Page
2020/01/20	7DD01920A07	-	11/12

2020-0036 REVISION RECORD

Rev. No.	Date	Reason	Contents	Approved	Checked	Drawn
-	2020/01/20	-	Initial Release	T.Hanaki	S.Sakamoto	E.Kameda
				+		
				+		
				1		
				+		

DM-Z0002: Style-008 Ver.1