


P.C.B. Land Pattern



Material

Housing Material: LCP, UL94V-0, black

Contact Terminal: Copper Alloy

Metallic Shell: Brass

Electrical

Voltage Rating: 30 V AC

Current Rating: Signal (Pins 2,3,4): 1.0A, Power (Pins

1,5): 1.8A

Contact Resistance: 30mΩ Max

Insulation resistance: 1000MΩ Min

Dielectric withstanding voltage: 250V AC/Minute

Mechanical

Durability: 3,000 cycles

Mating Force: 35N (3.57Kgf) Max

Unmating Force: 8N (0.82Kgf) Min.

U254-05XX-4BHJ233-XB

1:AU 1U"

6:AU 30U"

T:TIN

N:NICKEL

B:Brass

S:Scrolls F:Flat

广东星坤科技股份有限公司

生
效

日期

ΔX
MARK







文件工程章

REVISIONS

www.xk-cg.cn www.helloxkb.com www.helloxkb.cn

ANGULAR
L ≤ 4 ±5°
4 < L ≤ 16 ±0.2
16 < L ≤ 63 ±0.3
L > 63 ±0.4
UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE:
DWN		DATE		VIEW:	MICRO USB
CHKD		DATE		UNIT: mm/in	PART NO.:
APPD		DATE		SIZE: A4	DWG NO.:
KXB INDUSTRIAL PRECISION CO., LIMITED					U254-05XX-4BHJ233-FB
WEIGHT		SHEET		REVISION	
1.0g		1/1		A0	



Material

Housing Material: LCP, UL94V-0, black

Contact Terminal: Copper Alloy

Metallic Shell: Sus

Electrical

Voltage Rating: 30 V AC

Current Rating: Signal (Pins 2,3,4): 1.0A, Power (Pins 1,5): 1.8A

Contact Resistance: 30mΩ Max

Insulation resistance: 1000MΩ Min

Dielectric withstanding voltage: 250V AC/Minute

Mechanical

Durability: 3,000 cycles

Mating Force: 35N (3.57Kgf) Max

Unmating Force: 8N (0.82Kgf) Min.

U254-05XX-4BHJ233-X

1:AU 1U"


6:AU 30U"

T:TIN

N:NICKEL

LS:Scrolls F:Flat

2*0.61 [0.024]



广东星坤科技股份有限公司

生
效

日
期

ΔX
MARK

文件工程章

REVISIONS

www.xk-cg.cn www.helloxkb.com www.helloxkb.cn

ANGULAR ±5°
L ≤ 4 ±0.2
4 < L ≤ 16 ±0.3
16 < L ≤ 63 ±0.4
L > 63 ±0.5

UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE:
DWN		DATE		VIEW:	MICRO USB
CHKD		DATE		UNIT: mm/in	PART NO.:
APPD		DATE		SIZE: A4	DWG NO.:
KXB INDUSTRIAL PRECISION CO., LIMITED					U254-05XX-4BHJ233-F
WEIGHT		SHEET		REVISION	
1.0g		1/1		A0	