

POLYMER PTC RESETTABLE FUSE




Part Number: TRA800

1、 Physical Dimensions

Unit:mm

| Part Number | A | B | C | D | E | Lead |
|-------------|------|------|-----|------|-----|------|
| | Max | Max | TYP | Nor | Max | Φ |
| TRA800 | 17.8 | 22.9 | 5.1 | 10±2 | 3.1 | 0.80 |



Logo
 A 800 — Holding Current
 Max.Interrupt voltage
 XX — Lot No.

2、 Electrical Characteristics

| Part Number | I _H (A) | I _T (A) | V _{max} (V) | I _{max} (A) | T _{trip} (Max time to trip) | | Pd _{typ} (W) | R _{min} (Ω) | R _{max} (Ω) | R1 _{max} (Ω) |
|-------------|-----------------------|-----------------------|-------------------------|-------------------------|---|---------|--------------------------|-------------------------|-------------------------|--------------------------|
| | | | | | Current(A) | Time(S) | | | | |
| TRA800 | 8.0 | 16.0 | 16 | 100 | 40.0 | 9.0 | 3.0 | 0.004 | 0.013 | 0.018 |

I_H: Holding Current: maximum current at which the device will not trip in 25°C still air.

I_T: Tripping Current minimum current at which the device will trip in 25°C still air.

V_{max}: Maximum voltage device can withstand without damage at rated current.

I_{max}: Maximum fault current device can withstand without damage at rated voltage.

T_{trip}: Maximum time to trip(s) at assigned current.

Pd_{typ}: Rated working power.

R_{min}: Minimum resistance of device prior to trip at 25°C.


R_{max}: Maximum resistance of device prior to trip at 25°C.

R1_{max}: Maximum resistance of device is measured one hours post reflow at 25°C.

3、 Thermal Derating

| Part Number | Ambient Operating Temperature | | | | | | | | |
|-------------|-------------------------------|-------|------|------|------|------|------|------|------|
| | -40°C | -20°C | 0°C | 25°C | 40°C | 50°C | 60°C | 70°C | 85°C |
| TRA800 | 11.56 | 10.30 | 9.16 | 8.00 | 6.56 | 6.08 | 5.36 | 4.84 | 4.14 |

4、 Wave Soldering Parameters



| Profile Feature | Condition |
|---|----------------------------|
| Average Ramp-Up Rate (T _{smax} to TP) | 4°C/second max. |
| Preheat | |
| -Temperature Min (T _{smin}) | 100°C |
| -Temperature Max (T _{smax}) | 125°C |
| -Time (T _{smin} to T _{smax}) | 60-180 seconds |
| Peak Temperature (TP) | 265°C |
| Max Time at Peak Temperature (t _P) | 5 seconds |
| Ramp-Down Rate | 6 °C /second max. |
| Time 25°C to Peak Temperature | 5 minutes max. |
| Storage Condition | 0°C ~35°C, ≦70%RH, 2 Years |

5、 Package Information

Packing quantity:500pcs/bag

6、 Agency Recognition: TUV



Caution: Operation beyond the rated voltage or current may result in rupture electrical arcing or flame. Specifications are subject to change without notice.

TEL: 86-0769-3892 0554 FAX: 86-0769-8793 2077 E-mail:sales@tlcet.com.cn

Address: No.18, 5th GaoLi Road, TangXia Town, DongGuan, GuangDong, P.R China 523710