

2A, 18V, 500KHz, Synchronous Step-Down DC/DC Converter

FEATURES

- 4.5V to 18V input voltage
- Output adjustable from 0.8V to 15V
- Output current up to 2A
- Integrated $140 \text{m}\Omega/90 \text{m}\Omega$ power MOSFET switches
- Shutdown current 3μA typical
- Efficiency up to 95%
- Fixed frequency 500KHz
- Internal soft start
- Over current protection and Hiccup
- Over temperature protection
- RoHS Compliant and 100% Lead (Pb) Free

APPLICATIONS

- Distributed power systems
- Networking systems
- FPGA, DSP, ASIC power supplies
- Notebook computers
- Green electronics or appliance

ORDERING INFORMATION

PART	PACKAGE	RoHS	Ship, Quantity
ZTP7192T	TSOT23-6L	Yes	Tape and Reel

DESCRIPTION


The ZTP7192T is a high-frequency, synchronous, rectified, step-down, switch-mode converter with internal power MOSFETs. It offers a very compact solution to achieve a 2A continuous output current over a wide input supply range, with excellent load and line regulation. The ZTP7192T has synchronous-mode operation for higher efficiency over the output current-load range.

Current-mode operation provides fast transient response and eases loop stabilization.


Protection features include over-current protection and thermal shutdown.

The ZTP7192T requires a minimal number of readily available, standard external components and is available in space-saving TSOT23-6L package.

Pins Configuration







Note1: R5 and C7 are optional.

Note2: Cff are optional. Users can adjust the Cff value according to their bandwidth requirements.

Details please see the DVT report.

Copyright © ZillTek Technology Corp.



Absolute Maximum Ratings

Supply Voltage V_{IN}
Enable Voltage V_{EN} -0.3V to $V_{IN} V_{IN} V_$
Switch Node V_{SW}
-0.3V(-5V for <10nS)to 19V(21V for < 10nS)
Boost V _{BOOT} V _{SW} -0.3 V to V _{SW} +6 V
All Other Pins0.3V to +6V
Power Dissipation @25 $^{\circ}$ C 1.2W
Junction Temperature+150°C
Lead Temperature+260°C
Storage Temperature Range65°C to +150°C
ESD, HBM
ESD, MM 200V

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Electro-Static Discharge Sensitivity

This integrated circuit can be damaged by ESD.

It is recommended that all integrated circuits be handled with proper precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure.

Recommended Operating Conditions

Supply Voltage V _{IN}	4.5V to 18V
Output Voltage V _{OUT}	0.8V to V _{IN} -3V
Operating Temperature Range	40°C to +125°C

Package Thermal Characteristics


TSOT23-6L:

Thermal Resistance, θ_{JA}	 100°C/W
Thermal Resistance, Oc.	.55°C/W

Pins Description

SOT 23-6L Symbol		Description
1	GND	Ground.
2	SW	Power switching output.
3	IN	Power input.
4	FB	Feedback input.
5	EN	Enable input.
6	воот	High-side gate drive boost input.

Functional Block Diagram





Electrical Specifications

($T_A = +25$ °C, $V_{IN} = +12$ V, unless otherwise noted.)


PARAMETER	Symbol	TEST CONDITIONS	MIN	ТҮР	MAX	UNIT
Supply Voltage	V _{IN}		4.5		18	V
Output Voltage	V _{OUT}		0.8		15	V
Shutdown Supply Current		V _{EN} = 0V		3	6	μΑ
Supply Current		$V_{EN} = 2.0V V_{FB} = 0.88V$		0.7		mA
Feedback Voltage	V_{FB}	$4.5 \text{V} \leq \text{V}_{\text{IN}} \leq 18 \text{V}$	0.784	0.8	0.816	V
Feedback Over-voltage Threshold				0.96		V
Error Amplifier Voltage Gain *	A _{EA}			1000		V/V
High-Side Switch-On Resistance *	R _{DS(ON)1}			140		mΩ
Low-side Switch-On Resistance *	R _{DS(ON)2}			90		mΩ
High-Side Switch Leakage Current		$V_{EN} = 0V$, $V_{SW} = 0V$, $T_A = +125$ °C		X	10	μΑ
Upper Switch Current Limit		Minimum Duty Cycle	3	3.6	5	А
Lower Switch Current Limit		From Drain to Source		0		Α
Oscillation Frequency	Fosc1		400	500	600	KHz
Short Circuit Oscillation Frequency	F _{OSC2}	$V_{FB} = 0V$	200	250	300	KHz
Maximum Duty Cycle	D _{MAX}	$V_{FB} = 0.5V$		90		%
Minimum On Time *			R	120		ns
EN Falling Threshold Voltage		V _{EN} Falling	1.02	1.12	1.22	V
EN Rising Threshold Voltage		V _{EN} Rising	1.12	1.22	1.32	٧
Input Under Voltage Lockout Threshold		V _{IN} Rising	3.25	3.5	3.75	٧
Input Under Voltage Lockout Threshold Hysteresis				240		mV
Soft-Start Period				1		ms
Thermal Shutdown *				150		°C


^{*} Guaranteed by design, not tested.





Typical Characteristics


 V_{IN} = 12V, V_{O} = 3.3V, L1 = 4.7 μ H, C1 = 10 μ F, C2 = 10 μ F x 2, T_{A} = +25°C, unless otherwise noted.






















Line regulation

0.6% 0.4% 0.2% 0.0% -0.2% -0.4% -0.6% 4 5 6 7 8 9 10 11 12 13 14 15 16

Load regulation



Temperature Rise vs Load Current(Vo=5V,L=6.8uH)



APPLICATION INFORMATION

Overview

The ZTP7192T is a synchronous rectified, current-mode, step-down regulator. It regulates input voltages from 4.5V to 18V down to an output voltage as low as 0.8V, and supplies up to 2A of load current.

The ZTP7192T uses current-mode control to regulate the output voltage. The output voltage is measured at FB through a resistive voltage divider and amplified through the internal trans-conductance error amplifier. The converter uses internal N-Channel MOSFET switches to step-down the input voltage to the regulated output voltage. Since the high side MOSFET requires a gate voltage greater than the input voltage, a boost capacitor connected between SW and BOOT is needed to drive

The ZTP7192T has power save mode for light load. During this time, the internal clock is blocked, thus the ZTP7192T skips some pulses for PFM(Pulse Frequency Modulation) mode and achieves the light load power

the high side gate. The boost capacitor is charged from

the internal 5V rail when SW is low.

When the ZTP7192T FB pin exceeds 20% of the nominal regulation voltage of 0.8V, the over voltage comparator is tripped, forcing the high-sideswitch off.

Pins Description

save.

BOOT: High-Side Gate Drive Boost Input. BOOT supplies the drive for the high-side N-Channel MOSFET switch. Connect a $0.1\mu\text{F}$ or greater capacitor from SW to BOOT to power the high side switch.

IN: Power Input. IN supplies the power to the IC, as well as the step-down converter switches. Drive IN with a 4.5V to 18V power source. Bypass IN to GND with a suitably large capacitor to eliminate noise on the input to the IC.

SW: Power Switching Output. SW is the switching node that supplies power to the output. Connect the output LC filter from SW to the output load. Note that a capacitor is required from SW to BOOT to power the high-side switch.

GND: Ground.

FB: Feedback Input. FB senses the output voltage to regulate that voltage. Drive FB with a resistive voltage divider from the output voltage. The feedback threshold is 0.8V.

EN: Enable Input. EN is a digital input that turns the regulator on or off. Drive EN high to turn on the regulator, drive it low to turn it off. Pull up with $100k\Omega$ resistor for automatic startup.

Setting the Output Voltage

The external resistor divider sets the output voltage. The feedback resistor R1 also sets the feedback-loop bandwidth through the internal compensation capacitor (see the Typical Application circuit). Choose R1 around $10k\Omega$, and R2 by:

$$R2 = R1 / (V_{OUT}/0.8V - 1)$$

Use a network below for when Vout is low.




Figure 1: Network.

Table 1 lists the recommended T-type resistors value for common output voltages.(RT=0)

V _{OUT} (V)	R1 (KΩ)	R2 (KΩ)	Rt (Ω)
1.05	103.8(1%)	332.1(1%)	0(1%)
1.2	100(1%)	200.1(1%)	0(1%)
1.8	85(1%)	68(1%)	0(1%)
2.5	67.5(1%)	31.8(1%)	0(1%)
3.3	47.5(1%)	15.2(1%)	0(1%)
5	83.1(1%)	15.8(1%)	0(1%)

Table 1: Resistor selection for common output voltages.

Rt is used to set control loop's bandwidth, which is proportional to the relation by R1, R2, RT:

1/[(Rt+20k)*(1+R1/R2)+R1]

So Increase RT & Decrease R1&R2 value(keeping R1/R2 ratio), the bandwidth can be kept the same(the relation value need to be the same)

Inductor

The inductor is required to supply constant current to the output load while being driven by the switched input voltage. A larger value inductor will result in less ripple current that will result in lower output ripple voltage. However, the larger value inductor will have a larger physical size, higher series resistance, and/or lower saturation current. A good rule for determining the inductance to use is to allow the peak-to-peak ripple current in the inductor to be approximately 30% of the maximum switch current limit. Also, make sure that the peak inductor current is below the maximum switch current limit. The inductance value can be calculated by:

$$L = [V_{OUT} / (f_S \times \Delta I_L)] \times (1 - V_{OUT} / V_{IN})$$

Where V_{OUT} is the output voltage, V_{IN} is the input voltage, f_S is the switching frequency, and ΔI_L is the peak-to-peak inductor ripple current.

Choose an inductor that will not saturate under the maximum inductor peak current. The peak inductor current can be calculated by:

$$I_{LP} = I_{LOAD} + [V_{OUT} / (2 \times f_S \times L)] \times (1 - V_{OUT} / V_{IN})$$

Where I_{LOAD} is the load current.

The choice of which style inductor to use mainly depends on the price vs. size requirements and any EMI requirements.

Optional Schottky Diode

During the transition between high-side switch and low-side switch, the body diode of the low-side power MOSFET conducts the inductor current. The forward voltage of this body diode is high. An optional Schottky diode may be paralleled between the SW pin and GND pin to improve overall efficiency. Table 2 lists example Schottky diodes and their Manufacturers.

Part Number	Voltage and Current Rating	Vendor
B130	30V, 1A	Diodes Inc.
SK13	30V, 1A	Diodes Inc.
MBRS130	30V, 1A	International Rectifier

Table 2: Diode selection guide.

Input Capacitor

The input current to the step-down converter is discontinuous, therefore a capacitor is required to

supply the AC current to the step-down converter while maintaining the DC input voltage. Use low ESR capacitors for the best performance. Ceramic capacitors are preferred, but tantalum or low-ESR electrolytic capacitors may also suffice. Choose X5R or X7R dielectrics when using ceramic capacitors.

Since the input capacitor (C1) absorbs the input switching current it requires an adequate ripple current rating. The RMS current in the input capacitor can be estimated by:

$$I_{C1} = I_{LOAD} \times [(V_{OUT}/V_{IN}) \times (1 - V_{OUT}/V_{IN})]^{1/2}$$

The worst-case condition occurs at $V_N = 2V_{OUT}$, where $I_{C1} = I_{LOAD}/2$. For simplification, choose the input capacitor whose RMS current rating greater than half of the maximum load current.

The input capacitor can be electrolytic, tantalum or ceramic. When using electrolytic or tantalum capacitors, a small, high quality ceramic capacitor, i.e. $0.1\mu\text{F}$, should be placed as close to the IC as possible. When using ceramic capacitors, make sure that they have enough capacitance to provide sufficient charge to prevent excessive voltage ripple at input. The input voltage ripple for low ESR capacitors can be estimated by:

$$\Delta V_{IN} = [I_{LOAD}/(C1 \times f_S)] \times (V_{OUT}/V_{IN}) \times (1 - V_{OUT}/V_{IN})$$

Where C1 is the input capacitance value.

Output Capacitor

The output capacitor is required to maintain the DC output voltage. Ceramic, tantalum, or low ESR electrolytic capacitors are recommended. Low ESR capacitors are preferred to keep the output voltage ripple low. The output voltage ripple can be estimated by:

$$\Delta V_{OUT} = [V_{OUT}/(f_S \times L)] \times (1 - V_{OUT}/V_{IN})$$
$$\times [R_{ESR} + 1/(8 \times f_S \times C2)]$$

Where C2 is the output capacitance value and R_{ESR} is the equivalent series resistance (ESR) value of the output capacitor.

In the case of ceramic capacitors, the impedance at the switching frequency is dominated by the capacitance. The output voltage ripple is mainly caused by the capacitance. For simplification, the output voltage ripple can be estimated by:

$$\Delta V_{OUT} = [V_{OUT}/(8 \times f_S^2 \times L \times C2)] \times (1 - V_{OUT}/V_{IN})$$

In the case of tantalum or electrolytic capacitors, the ESR dominates the impedance at the switching

 ${\bf Copyright}\, {\bf \mathbb{C}}\,\, {\bf ZillTek\, Technology\, Corp.}$

frequency. For simplification, the output ripple can be approximated to:

 $\Delta V_{OUT} = [V_{OUT}/(f_S \times L)] \times (1 - V_{OUT}/V_{IN}) \times R_{ESR}$

The characteristics of the output capacitor also affect the stability of the regulation system. The ZTP7192T can be optimized for a wide range of capacitance and ESR values.

External Bootstrap Diode

An external bootstrap diode may enhance the efficiency of the regulator, the applicable conditions of external BOOT diode are:

- V_{OUT} = 5V or 3.3V; and
- Duty cycle is high: D = V_{OUT}/V_{IN} > 65%

In these cases, an external BOOT diode is recommended from the output of the voltage regulator to BOOT pin, as shown in Figure 2.




Figure 2: Add optional external bootstrap diode to enhance efficiency.

The recommended external BOOT diode is IN4148, and the BOOT capacitor is $0.1 \sim 1 \mu F$.

When $V_{IN} \le 6V$, for the purpose of promote the efficiency, it can add an external Schottky diode between IN and BOOT pins, as shown in Figure 3.




Figure 3: Add a Schottky diode to promote efficiency when $V_{IN} \leq 6V$.

PCB Layout Guide

PCB layout is very important to achieve stable operation. Please follow the guidelines below.

1) Keep the path of switching current short and

- minimize the loop area formed by Input capacitor, high-side MOSFET and low-side MOSFET.
- 2) Bypass ceramic capacitors are suggested to be put close to the V_{IN} Pin.
- 3) Ensure all feedback connections are short and direct.
 Place the feedback resistors and compensation
 components as close to the chip as possible.
- 4) Rout SW away from sensitive analog areas such as
- 5) Connect IN, SW, and especially GND respectively to a large copper area to cool the chip to improve thermal performance and long-term reliability.
- 6) It is recommended to reserve a place for Cff in layout.

BOM of ZTP7192T

Please refer to the Typical Application Circuit.

Item	Reference	Part
1	C1	10μF
2	C5	100nF
3	C7	0.1μF
4	R4	100K

Table 3: BOM selection table I.

	L1	R1	R2	C2
Vout = 5.0V	6.8µH	83.1K	15.8K	10μF×2
Vout = 3.3V	4.7μΗ	47.5K	15.2K	10μF×2
Vout = 2.5V	3.3μΗ	67.5K	31.8K	10μF×2
Vout = 1.8V	2.2μΗ	85K	68K	10μF×2
Vout = 1.2V	2.2μΗ	100K	200.1K	10μF×2

Table 4: BOM selection table II.(RT=0oHm)




Figure 4: Structure of the feedback circuit.

Copyright © ZillTek Technology Corp.





VOUT	5V	3.3V	2.5V	1.8V	1.5V	1.2V	1V
R2(MAX)	500K	500K	500K	500K	500K	500K	500K
R2(MIN)	2K	2K	2K	2K	2K	2K	2K
R1(MAX)	2.5M	1.5M	1M	625k	438K	250K	125K
R1(MIN)	10K	6K	4K	2.5K	1.75K	1K	0.5K


Table 5: Feedback application range.

Input Capacitance: Cin, minimum application range at least is $10\,\mu F$. Output Capacitance: Cout, minimum application range is $10\,\mu F$ to $100\,\mu F$

PACKAGE DIMENSION TSOT23-6L







Symbol	Dimensio	ns in mm	Dimensions in Inch		
Symbol	Min	Max	Min	Max	
А	1.100	1.300	0.043	0.066	
A1	0.000	0.100	0.000	0.004	
В	1.600	1.700	0.063	0.067	
b	0.350	0.500	0.014	0.020	
С	2.650	2.950	0.104	0.116	
D	2.820	3.020	0.111	0.119	
е	0.950 BSC		0.037	7 BSC	
Н	0.080	0.200	0.003	0.008	
L	0.300	0.600	0.012	0.024	