


# **XH** CONNECTOR (High box type)

2.5 mm pitch/Disconnectable Crimp style connectors



XH connector high box type, with 17.0 mm mounting height and with 5.8 mm thickness.

- Header for 2.5 mm pitch XH connector for use specifically with resin coated ("potted") PC boards
- Interchangeability


PC board layout and Assembly layout


## Specifications -

- Current rating: 3 A AC/DC (AWG #22)
- Voltage rating: 250 V AC/DC
- Temperature range: -25℃ to +85℃
  - (including temperature rise in applying
  - electrical current)
- Contact resistance: Initial value/ 10 m $\Omega$  max.
- After environmental tests/ 20 m $\Omega$  max.
- Insulation resistance: 1,000 M $\Omega$  min.
- Withstanding voltage: 1,000 VAC/minute
  Applicable wire: AWG #30 to #22
- Applicable PC board thickness: 1.6 mm
- \* In using the products, refer to "Handling Precautions for Terminals and Connectors" described on our website (Technical documents of Product information page).
- \* RoHS2 compliance
- \* Dimensional unit: mm
- \* Contact JST for details.

## Standards -

- N° Recognized E60389
- GE Certified LR20812






Note: 1. The above figure is the figure viewed from the connector mounting side.

2. Tolerances are non-cumulative:  $\pm$  0.05 mm for all centers.

3. Hole dimensions differ according to the type of PC board and piercing method. If PC boards made of hard material are used, the hole dimensions should be larger. The dimensions above should serve as a guideline. Contact JST for details.

#### Contact



Madel Na	Applicable wire		Insulation O.D. (mm)	Q'ty∕	
Model No.	mm <sup>2</sup>	AWG#	Insulation O.D. (mm)	reel	
SXH-001T-P0.6	0.08~0.33	28~22	0.9~1.9	8.000	
SXH-002T-P0.6	0.05~0.13	30~26	0.9~1.3	0,000	

Material and Finish

Phosphor bronze, tin-plated (reflow treatment)


RoHS2 compliance

- Note: 1. Contact JST if you requier gold-plated contacts or contacts made of brass.
  - Contact JST also if you require shielded wires, thin wires or other special wires.

Contact	Crimping	Applicator			
	machine	Crimp applicator	Dies	Crimp applicator with dies	
SXH-001T-P0.6		MKS-L	MK/SXH-001-06	APLMK SXH001-06	
SXH-002T-P0.6			MK/SXH-002-06	APLMK SXH002-06	

Note: Contact JST for fully automatic crimping applicator.

Housing



No. of	Model No.	D	Q'ty/		
circuits	woder No.	A	В	С	bag
2	XHP-2	2.5	5.7	7.3	1,000
3	XHP-3	5.0	8.2	9.8	1,000
4	XHP-4	7.5	10.7	12.3	1,000
5	XHP-5	10.0	13.2	14.8	1,000
6	XHP-6	12.5	15.7	17.3	1,000
7	XHP-7	15.0	18.2	19.8	1,000
8	XHP-8	17.5	20.7	22.3	1,000
9	XHP-9	20.0	23.2	24.8	1,000
10	XHP-10	22.5	25.7	27.3	1,000

Material and Finish

PA 6, UL94V-0, natural (white)

RoHS2 compliance


<For reference> As the color identification,

the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact JST.

ex. XHP-2-<u>oo</u>

(blank)...natural (white) BK...black R...red E...blue Y...yellow M...green

### Shrouded header



No. of circuits Model No.	Madal Na	Dimensi	Dimensions (mm)	
	woder No.	A	В	Q'ty/box
2	BH2B-XH-2	2.5	7.4	700
3	BH3B-XH-2	5.0	9.9	500
4	BH4B-XH-2	7.5	12.4	300
5	BH5B-XH-2	10.0	14.9	300
6	BH6B-XH-2	12.5	17.4	250
7	BH7B-XH-2	15.0	19.9	200
8	BH8B-XH-2	17.5	22.4	150
9	BH9B-XH-2	20.0	24.9	150
10	BH10B-XH-2	22.5	27.4	150

#### Material and Finish

Post: Copper alloy, copper-undercoated, tin-plated (reflow treatment) Wafer: Glass-filled PA 66, UL94V-0, natural (ivory)

RoHS2 compliance This product displays (LF)(SN) on a label.

<For reference> As the color identification,

the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact JST.

ex. BH2B-XH-2-<u>oo</u>

(blank)...natural (ivory) R...red C...black E...blue Y...yellow M...green

2.45

Α

в