




Lonten N-channel 100V, 60A, 8.5mΩ Power MOSFET

<p>Description</p> <p>These N-Channel enhancement mode power field effect transistors are using split gate trench DMOS technology. This advanced technology has been especially tailored to minimize on-state resistance, provide superior switching performance, and with stand high energy pulse in the avalanche and commutation mode. These devices are well suited for high efficiency fast switching applications.</p> <p>Features</p> <ul style="list-style-type: none"> ◆ 100V,60A,$R_{DS(ON),max}=8.5m\Omega@V_{GS}=10V$ ◆ Improved dv/dt capability ◆ Fast switching ◆ 100% EAS Guaranteed ◆ Green device available <p>Applications</p> <ul style="list-style-type: none"> ◆ Motor Drives ◆ UPS ◆ DC-DC Converter 	<p>Product Summary</p> <table> <tr> <td>V_{DSS}</td> <td>100V</td> </tr> <tr> <td>$R_{DS(on),max}@V_{GS}=10V$</td> <td>8.5mΩ</td> </tr> <tr> <td>I_D</td> <td>60A</td> </tr> </table> <p>Pin Configuration</p>  <p style="text-align: center;">PPAK5×6</p>  <p style="text-align: center;">N-Channel MOSFET</p> 	V_{DSS}	100V	$R_{DS(on),max}@V_{GS}=10V$	8.5mΩ	I_D	60A
V_{DSS}	100V						
$R_{DS(on),max}@V_{GS}=10V$	8.5mΩ						
I_D	60A						

Absolute Maximum Ratings $T_c = 25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	100	V
Continuous drain current ($T_c = 25^\circ\text{C}$) ¹⁾	I_D	60	A
Continuous drain current ($T_c = 100^\circ\text{C}$) ¹⁾		47	A
Pulsed drain current ²⁾	I_{DM}	240	A
Gate-Source voltage	V_{GSS}	± 20	V
Avalanche energy, single pulse ³⁾	E_{AS}	110	mJ
Power Dissipation ($T_c = 25^\circ\text{C}$)	P_D	96	W
Storage Temperature Range	T_{STG}	-55 to +150	$^\circ\text{C}$
Operating Junction Temperature Range	T_J	-55 to +150	$^\circ\text{C}$

Thermal Characteristics

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	1.3	$^\circ\text{C/W}$

Package Marking and Ordering Information

Device	Device Package	Marking
LSGN10R085W3	PPAK5×6	SGN10R085W3

Electrical Characteristics T_J = 25°C unless otherwise noted

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Static characteristics						
Drain-source breakdown voltage	BV _{DSS}	V _{GS} =0 V, I _D =250uA	100	---	---	V
Gate threshold voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250uA	1.4	1.8	2.2	V
Drain-source leakage current	I _{DSS}	V _{DS} =100V, V _{GS} =0V, T _J = 25°C	---	---	1	μA
		V _{DS} =80V, V _{GS} =0V, T _J = 125°C	---	---	10	μA
Gate leakage current, Forward	I _{GSSF}	V _{GS} =20 V, V _{DS} =0 V	---	---	100	nA
Gate leakage current, Reverse	I _{GSSR}	V _{GS} =-20 V, V _{DS} =0 V	---	---	-100	nA
Drain-source on-state resistance	R _{DS(on)}	V _{GS} =10 V, I _D =30 A	---	7.3	8.5	mΩ
Drain-source on-state resistance		V _{GS} =4.5 V, I _D =20 A	---	8.8	10.5	mΩ
Forward transconductance	g _{fs}	V _{DS} =5V, I _D =30A	---	112	---	S
Dynamic characteristics						
Input capacitance	C _{iss}	V _{DS} = 50 V, V _{GS} = 0 V, F = 1MHz	---	2630	---	pF
Output capacitance	C _{oss}		---	453	---	
Reverse transfer capacitance	C _{rss}		---	36	---	
Turn-on delay time	t _{d(on)}	V _{DD} = 50V, V _{GS} =10V, I _D = 30A	---	10.5	---	ns
Rise time	t _r		---	63	---	
Turn-off delay time	t _{d(off)}		---	30	---	
Fall time	t _f		---	96	---	
Gate resistance	R _g	V _{GS} =0V, V _{DS} =0V, F=1MHz	---	1.1	---	Ω
Gate charge characteristics						
Gate to source charge	Q _{gs}	V _{DS} =50 V, I _D =30A, V _{GS} = 10 V	---	10.2	---	nC
Gate to drain charge	Q _{gd}		---	6.6	---	
Gate charge total	Q _g		---	45	---	
Drain-Source diode characteristics and Maximum Ratings						
Continuous Source Current	I _S	V _G =V _D =0 V, Force Current	---	---	60	A
Pulsed Source Current	I _{SM}		---	---	240	A
Diode Forward Voltage ⁴⁾	V _{SD}	V _{GS} =0V, I _S =30A, T _J =25°C	---	---	1.3	V
Reverse Recovery Time	t _{rr}	I _S =30A, di/dt=100A/us, T _J =25°C	---	65	---	ns
Reverse Recovery Charge	Q _{rr}		---	104	---	nC

Notes:

- 1: The maximum junction current rating is package limited.
- 2: Repetitive Rating: Pulse width limited by maximum junction temperature.
- 3: V_{DD}=50V, V_{GS}=10V, L=0.5mH, I_{AS}=21A, R_G=25Ω, Starting T_J=25°C.
- 4: Pulse Test: Pulse Width ≤300 μs, Duty Cycle≤2%.

Electrical Characteristics Diagrams

Figure 1. Typ. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Capacitance Characteristics




Figure 4. Gate Charge Waveform




Figure 5. Body-Diode Characteristics




Figure 6. Rds(on)-Drain Current




Figure 7. Rdson-Junction Temperature(°C)




Figure 8. Maximum Safe Operating Area




Figure 9. On-Resistance vs. Gate-to-Source voltage




Figure 10. BVdss vs. Junction temperature





Figure 11. Normalized Maximum Transient Thermal Impedance (RthJC)



Test Circuit & Waveform

Figure 8. Gate Charge Test Circuit & Waveform




Figure 9. Resistive Switching Test Circuit & Waveforms




Figure 10. Unclamped Inductive Switching (UIS) Test Circuit & Waveform






Figure 11. Diode Recovery Circuit & Waveform




Mechanical Dimensions for PPAK5×6



COMMON DIMENSIONS						
SYMBOL	MILLIMETERS			INCHS		
	MIN	NOM	MAX	MIN	NOM	MAX
A	1	1.1	1.2	0.039	0.043	0.047
b	0.3	0.4	0.5	0.012	0.016	0.020
C	0.154	0.254	0.354	0.006	0.010	0.014
D1	5	5.2	5.4	0.197	0.205	0.213
D2	3.8	4.1	4.25	0.150	0.161	0.167
E1	5.95	6.15	6.35	0.234	0.242	0.250
E2	5.66	5.86	6.06	0.223	0.231	0.239
E4	3.52	3.72	3.92	0.139	0.146	0.154
e	1.27 BSC			0.050 BSC		
H	0.4	0.5	0.6	0.016	0.020	0.024
L	0.5	0.6	0.7	0.020	0.024	0.028
L1	-	-	0.12	-	-	0.005
K	1.14	1.29	1.44	0.045	0.051	0.057

PPAK5×6 Part Marking Information



Disclaimer

The content specified herein is for the purpose of introducing LONTEN's products (hereinafter "Products"). The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

LONTEN does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of the Products or technical information described in this document.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). LONTEN shall bear no responsibility in any way for use of any of the Products for the above special purposes.

Although LONTEN endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a LONTEN product.

The content specified herein is subject to change for improvement without notice. When using a LONTEN product, be sure to obtain the latest specifications.