



Spec No. :DS35-2016-0139 Effective Date: 03/29/2017 Revision: A

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4

LITE-ON Technology Corp. / Optoelectronics No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C. Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660 http://www.liteon.com/opto



SMD LED LTST-G563EGBW-HM4

1. Description

SMD LEDs with built-in embedded IC from Lite-On is a new solution for customer's constant current application, are available in miniature sizes and special configurations for automated PC board assembly and space-sensitive applications. These SMD LEDs are suitable for use in a wide variety of electronic equipment, including cordless and cellular phones, notebook computers, network systems, home appliances, and indoor signboard applications.


1.1 Features

- ROHS Compliant
- Packaged in 12mm tape on 7" diameter reels
- EIA STD package
- Compatible with automatic placement equipment and infrared reflow solder process
- Preconditioning: accelerate to JEDEC level 3
- RGB and driver chip are integrated in a package, to form a complete control of pixel point with constant current.
- One pixel contains R, G, and B color that each can achieve 256 level brightness grayscale, which forms 16,777,216 combination colors. Internal clock frequency is operated at 800 kHz.
- Serial data transmission signal by only single wire.

2. Package Dimensions / Configuration

1.2 Applications

- Telecommunication, office automation, home appliances, industrial equipment
- Status indicator
- Signal and symbol luminary
- Front panel backlighting
- Full-color strip.
- Indoor/outdoor decorative lighting/ curtain display



2.1 Package Dimensions

Part No. : LTST-G563EGBW-HM4 BNS-OD-FC002/A4



Part No.	Lens Color	Source Color
LTST-G563EGBW-HM4		InGaN Blue
	Water Clear	InGaN Green
		AllnGaP Red


Notes:

LITEON[®]

OPTOELECTRONICS

- 1. All dimensions are in millimeters.
- 2. Tolerance is ± 0.2 mm unless otherwise noted.

2.2 PIN Configuration



No.	Symbol	Function description			
1	VSS	Ground			
2	DIN	Control date signal input			
3	DOUT	Control data signal output			
4	VDD	Power supply LED			




SMD LED LTST-G563EGBW-HM4

3. Rating and Characteristics

3.1 Absolute Maximum Ratings at Ta=25°C

Parameter	LTST-G563EGBW-HM4				
	Symbol	Ratings	Unit		
DC Forward Current	IF	5	mA		
IC Power Supply Voltage	VDD	+3.8~+5.5	V		
IC Input Voltage	VI	-0.5~VDD+0.5	V		
Operating Temperature Range	-25℃ to + 85℃				
Storage Temperature Range	-40℃ to + 105℃				

3.2 Suggest IR Reflow Condition for Pb Free Process:



IR-Reflow Soldering Profile for lead free soldering (Acc. to J-STD-020B)

Part No. : LTST-G563EGBW-HM4 BNS-OD-FC002/A4



SMD LED LTST-G563EGBW-HM4

3.3 Optical Characteristics (Ta=25℃)

Descuration	Question		LTS	Unit	Test		
Parameter	Symbol	color	MIN	TYP.	МАХ	Unit	Condition (IC output)
		Red	180	-	360		
Luminous Intensity	IV	Green	400	-	900	mcd	5mA Note 1
		Blue	70	-	224		
Viewing Angle	2 θ _{1/2}	-		120		deg	Note 2 (Fig.5)
	λd	Red	618	-	630		
Dominant Wavelength		Green	520	-	535	nm	5mA Note 3
		Blue	463	-	475		

3.4 Electrical Characteristics (Ta=-20~+70°C, V DD=4.5~5.5V, Vss=0V, unless otherwise specified)

			LTST-G563EGBW-HM4			11-24
Parameter	Symbol	Condition	MIN	TYP.	МАХ	Unit
Input current	h	VI=VDD/Vss	-	-	±1	μA
	Vін	DIN , SET	0.7Vdd	-	-	V
Input voltage level	VIL	DIN , SET	-	-	0.3Vdd	V
Hysteresis voltage	Vн	DIN , SET	-	0.35	-	V

3.5 Switching Characteristics (Ta=-20~+70°C, V DD=4.5~5.5V, Vss=0V, unless otherwise specified)


Devenuetor	Symbol	Condition	LTST-	G563EGBV	V-HM4	11-14
Parameter	Symbol	Condition	MIN	TYP.	МАХ	Unit
Transmission delay time	Tplz	D _{IN} →D _{OUT} CL=15pF, RL=10KΩ	-	-	300	ns
Fall time	Ттнг	CL=300pF, OUTR/OUTG/OUTB	-	-	20	μs
Input capacity	Cı	-	-	-	15	pF



SMD LED LTST-G563EGBW-HM4

3.6 Data transfer time (TH+TL=1.2µs±600ns)

Timing Wave Form



High Speed Mode

Item	Description	Typical	Allowance
Тон	0 code, high voltage time	300 ns	± 150ns
ToL	0 code, low voltage time	900 ns	± 150ns
Т _{1Н}	1 code, high voltage time	900 ns	± 150ns
T₁∟	1 code, low voltage time	300 ns	± 150ns
RES	reset time	>50 µs	-

Notes:

- 1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.
- 2. $\theta_{1/2}$ is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
- The dominant wavelength, λd is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device. Peak Emission Wavelength Tolerance is +/- 1nm.






SMD LED LTST-G563EGBW-HM4

4. CIE Specification


Color Bin Table						Test	@5m	Α			
Bin Code		C	Color Bin Li	mits		Bin Code		C	Color Bin Li	mits	
DITICODE	CIE-	Point1	Point2	Point3	Point4	BIII Code	CIE-	Point1	Point2	Point3	Point4
А	х	0.2450	0.2650	0.2650	0.2450	С	х	0.2650	0.2850	0.2850	0.2650
A	у	0.2450	0.2550	0.2750	0.2650	C	у	0.2550	0.2650	0.2850	0.2750
В	х	0.2450	0.2650	0.2650	0.2450	D	х	0.2650	0.2850	0.2850	0.2650
В	у	0.2650	0.2750	0.2950	0.2850	D	у	0.2750	0.2850	0.3050	0.2950





SMD LED LTST-G563EGBW-HM4

5. Typical Electrical / Optical Characteristics Curves.



(25℃ Ambient Temperature Unless Otherwise Noted)

Part No. : LTST-G563EGBW-HM4 BNS-OD-FC002/A4




SMD LED LTST-G563EGBW-HM4

6. User Guide


6.1 Cleaning

Do not use unspecified chemical liquid to clean LED they could harm the package. If cleaning is necessary, immerse the LED in ethyl alcohol or isopropyl alcohol at normal temperature for less one minute.


6.2 Recommend Printed Circuit Board Attachment Pad



Reflow Soldering



6.3 Package Dimensions of Tape And Reel




Note:

1. All dimensions are in millimeters (inches).



SMD LED LTST-G563EGBW-HM4

6.4 Package Dimensions of Reel



Notes:

- 1. Empty component pockets sealed with top cover tape.
- 2. 7 inch reel 1000 pieces per reel.
- 3. Minimum packing quantity is 500 pieces for remainders.
- 4. The maximum number of consecutive missing lamps is two.
- 5. In accordance with ANSI/EIA 481 specifications.





SMD LED LTST-G563EGBW-HM4

7. Cautions

7.1 Application

The LEDs described here are intended to be used for ordinary electronic equipment (such as office equipment, communication equipment and household applications).Consult Liteon's Sales in advance for information on applications in which exceptional reliability is required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as in aviation, transportation, traffic control equipment, medical and life support systems and safety devices).

7.2 Storage

The package is sealed:

The LEDs should be stored at 30°C or less and 70%RH or less. And the LEDs are limited to use within one year, while the LEDs is packed in moisture-proof package with the desiccants inside.

The package is opened:

The storage ambient for the LEDs should not exceed 30°C temperature and 60% relative humidity.

It is recommended that LEDs out of their original packaging are IR-reflowed within 168hrs.

For extended storage out of their original packaging, it is recommended that the LEDs be stored in a sealed container with appropriate desiccant, or in a desiccators with nitrogen ambient.

LEDs stored out of their original packaging for more than 168hrs should be baked at about 60 $^{\circ}$ C for at least 48 hours before solder assembly.

7.3 Cleaning

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LED if necessary.

7.4 Soldering

Recommended soldering conditions:

Reflo	w soldering	Soldering iron		
Pre-heat	150~200℃	Temperature	350℃ Max.	
Pre-heat time	Pre-heat time 120 sec. Max.		3 sec. Max.	
Peak temperature	Peak temperature 260°C Max.		(one time only)	
Soldering time	10 sec. Max.(Max. two times)			

Notes:

Because different board designs use different number and types of devices, solder pastes, reflow ovens, and circuit boards, no single temperature profile works for all possible combinations.

However, you can successfully mount your packages to the PCB by following the proper guidelines and PCB-specific characterization.

LITE-ON Runs both component-level verification using in-house **KYRAMX98** reflow chambers and board-level assembly. The results of this testing are verified through post-reflow reliability testing. Profiles used at LITE-ON are based on JEDEC standards to ensure that all packages can be successfully and reliably surface mounted.

Figure on page3 shows a sample temperature profile compliant to JEDEC standards. You can use this example as a generic target to set up your reflow process. You should adhere to the JEDEC profile limits as well as specifications and recommendations from the solder paste manufacturer to avoid damaging the device and create a reliable solder joint.




Part No. : LTST-G563EGBW-HM4 BNS-OD-FC002/A4



SMD LED LTST-G563EGBW-HM4

7.5 Driving Method

The LED needs to be incorporated with an appropriate controller to deliver PWM signals to each pixel. Below figure is shown as a reference design.



7.6 ESD (Electrostatic Discharge)

Static Electricity or power surge will damage the LED. Suggestions to prevent ESD damage:

- Use of a conductive wrist band or anti-electrostatic glove when handling these LEDs.
- All devices, equipment, and machinery must be properly grounded.
- Work tables, storage racks, etc. should be properly grounded.
- Use ion blower to neutralize the static charge which might have built up on surface of the LED's plastic lens as a result of friction between LEDs during storage and handling.

ESD-damaged LEDs will exhibit abnormal characteristics such as high reverse leakage current, low forward voltage, or "no lightup" at low currents.

To verify for ESD damage, check for "lightup " and Vf of the suspect LEDs at low currents.

The Vf of " good " LEDs should be >2.0V@0.1mA for InGaN product and >1.4V@0.1mA for AlInGaP product.

Part No. : LTST-G563EGBW-HM4 BNS-OD-FC002/A4



SMD LED LTST-G563EGBW-HM4

8. Reliability Test

No.	Test item	Test condition	Reference standard
1	Resistance to soldering heat	Tsld = 260℃, 10sec. 3 times	JEITA ED-4701 300 301
2	Solderability	TsId=245 \pm 5°C (Lead Free Solder, Coverage \geq 95% of the dipped surface)	JEITA ED-4701 300 303
3	Thermal Shock	85 ± 5℃ ~ -30℃ ± 5℃ 30min 30min 100cycles	JEITA ED-4701 300 307
4	Temperature Cycle	-55℃ ~ 25℃ ~ 100℃ ~ 25℃ 30min 5min 30min 5min 100cycles	JEITA ED-4701 100 105
5	High Temperature Storage	100℃ 1000hrs	JEITA ED- 4701 200 201
6	Low Temperature Storage	-55℃ 1000hrs	JEITA ED-4 701 200 202
7	Temperature Humidity Storage	60℃/90%RH 300hrs	JEITA ED-4701 100 103
8	Room temp life test	25℃, IF: Max current , 1000hrs	

9. Others

The appearance and specifications of the product may be modified for improvement without prior notice.





SMD LED LTST-G563EGBW-HM4

10. Suggested Checking List

LTEON®

OPTOELECTRONICS

Training and Certification

- 1. Everyone working in a static-safe area is ESD-certified?
- 2. Training records kept and re-certification dates monitored?

Static-Safe Workstation & Work Areas

- 1. Static-safe workstation or work-areas have ESD signs?
- 2. All surfaces and objects at all static-safe workstation and within 1 ft measure less than 100V?
- 3. All ionizer activated, positioned towards the units?
- 4. Each work surface mats grounding is good?

Personnel Grounding

- 1. Every person (including visitors) handling ESD sensitive (ESDS) items wears wrist strap, heel strap or conductive shoes with conductive flooring?
- 2. If conductive footwear used, conductive flooring also present where operator stand or walk?
- 3. Garments, hairs or anything closer than 1 ft to ESD items measure less than 100V*?
- 4. Every wrist strap or heel strap/conductive shoes checked daily and result recorded for all DLs?
- 5. All wrist strap or heel strap checkers calibration up to date?

Note: *50V for InGaN LED.

Device Handling

- 1. Every ESDS items identified by EIA-471 labels on item or packaging?
- 2. All ESDS items completely inside properly closed static-shielding containers when not at static-safe workstation?
- 3. No static charge generators (e.g. plastics) inside shielding containers with ESDS items?
- 4. All flexible conductive and dissipative package materials inspected before reuse or recycles?

Others

- 1. Audit result reported to entity ESD control coordinator?
- 2. Corrective action from previous audits completed?
- 3. Are audit records complete and on file?

