

Lonten N-channel 40V, 110A, 5.0mΩ Power MOSFET

Description

These N-Channel enhancement mode power field effect transistors are using trench DMOS technology. This advanced technology has been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulse in the avalanche and commutation mode. These devices are well suited for high efficiency fast switching applications.

Features

- ◆ 40V, 110A, $R_{DS(ON).max}=5.0\text{m}\Omega$ @ $V_{GS}=10\text{V}$
- ◆ Improved dv/dt capability
- ◆ Fast switching
- ◆ 100% EAS Guaranteed
- ◆ Green device available


Applications

- ◆ Motor Drives
- ◆ UPS
- ◆ DC-DC Converter

Product Summary

V_{DSS}	40V
$R_{DS(on).max}$ @ $V_{GS}=10\text{V}$	5.0mΩ
I_D	110A

Pin Configuration



N-Channel MOSFET



Absolute Maximum Ratings

$T_C = 25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	40	V
Continuous drain current ($T_C = 25^\circ\text{C}$)	I_D	110	A
Continuous drain current ($T_C = 100^\circ\text{C}$)		71	A
Pulsed drain current ¹⁾	I_{DM}	440	A
Gate-Source voltage	V_{GSS}	± 20	V
Avalanche energy ²⁾	E_{AS}	156	mJ
Power Dissipation ($T_C = 25^\circ\text{C}$)	P_D	106	W
Storage Temperature Range	T_{STG}	-55 to +150	°C
Operating Junction Temperature Range	T_J	-55 to +150	°C

Thermal Characteristics

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	1.17	°C/W

Package Marking and Ordering Information

Device	Device Package	Marking
LNC04R050	TO-220	LNC04R050

Electrical Characteristics
 $T_J = 25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Static characteristics						
Drain-source breakdown voltage	BV_{DSS}	$\text{V}_{\text{GS}}=0 \text{ V}, \text{I}_D=250 \mu\text{A}$	40	---	---	V
Gate threshold voltage	$\text{V}_{\text{GS(th)}}$	$\text{V}_{\text{DS}}=\text{V}_{\text{GS}}, \text{I}_D=250 \mu\text{A}$	1.0	---	2.0	V
Drain-source leakage current	I_{DSS}	$\text{V}_{\text{DS}}=40 \text{ V}, \text{V}_{\text{GS}}=0 \text{ V}, T_J = 25^\circ\text{C}$	---	---	1	μA
		$\text{V}_{\text{DS}}=32 \text{ V}, \text{V}_{\text{GS}}=0 \text{ V}, T_J = 125^\circ\text{C}$	---	---	30	μA
Gate leakage current, Forward	I_{GSSF}	$\text{V}_{\text{GS}}=20 \text{ V}, \text{V}_{\text{DS}}=0 \text{ V}$	---	---	100	nA
Gate leakage current, Reverse	I_{GSSR}	$\text{V}_{\text{GS}}=-20 \text{ V}, \text{V}_{\text{DS}}=0 \text{ V}$	---	---	-100	nA
Drain-source on-state resistance	$\text{R}_{\text{DS(on)}}$	$\text{V}_{\text{GS}}=10 \text{ V}, \text{I}_D=40 \text{ A}$	---	3.8	5	$\text{m}\Omega$
		$\text{V}_{\text{GS}}=4.5 \text{ V}, \text{I}_D=30 \text{ A}$	---	4.7	6.2	$\text{m}\Omega$
Forward transconductance	g_{fs}	$\text{V}_{\text{DS}}=5 \text{ V}, \text{I}_D=30 \text{ A}$	---	79	---	S
Dynamic characteristics						
Input capacitance	C_{iss}	$\text{V}_{\text{DS}}=20 \text{ V}, \text{V}_{\text{GS}}=0 \text{ V}, F=1 \text{MHz}$	---	4023.6	---	pF
Output capacitance	C_{oss}		---	410.4	---	
Reverse transfer capacitance	C_{rss}		---	338.5	---	
Turn-on delay time	$t_{\text{d(on)}}$	$\text{V}_{\text{DD}}=30 \text{ V}, \text{V}_{\text{GS}}=15 \text{ V}, \text{I}_D=30 \text{ A}$	---	231.6	---	ns
Rise time	t_r		---	213.6	---	
Turn-off delay time	$t_{\text{d(off)}}$		---	219.2	---	
Fall time	t_f		---	74	---	
Gate resistance	R_g	$\text{V}_{\text{GS}}=0 \text{ V}, \text{V}_{\text{DS}}=0 \text{ V}, F=1 \text{MHz}$	---	2.4	---	Ω
Gate charge characteristics						
Gate to source charge	Q_{gs}	$\text{V}_{\text{DS}}=30 \text{ V}, \text{I}_D=30 \text{ A}, \text{V}_{\text{GS}}=10 \text{ V}$	---	11	---	nC
Gate to drain charge	Q_{gd}		---	16.7	---	
Gate charge total	Q_g		---	66.7	---	
Drain-Source diode characteristics and Maximum Ratings						
Continuous Source Current	I_s		---	---	110	A
Pulsed Source Current ³⁾	I_{SM}		---	---	440	A
Diode Forward Voltage	V_{SD}	$\text{V}_{\text{GS}}=0 \text{ V}, \text{I}_s=40 \text{ A}, T_J=25^\circ\text{C}$	---	---	1.2	V
Reverse Recovery Time	t_{rr}	$\text{I}_s=20 \text{ A}, \text{di/dt}=100 \text{ A/us}, T_J=25^\circ\text{C}$	---	41.4	---	ns
Reverse Recovery Charge	Q_{rr}		---	29	---	nC

Notes:

1: Repetitive Rating: Pulse width limited by maximum junction temperature.

2: $\text{V}_{\text{DD}}=20 \text{ V}, \text{V}_{\text{GS}}=10 \text{ V}, L=0.5 \text{ mH}, \text{I}_{\text{AS}}=25 \text{ A}, R_g=25 \Omega$, Starting $T_J=25^\circ\text{C}$.

3: Pulse Test: Pulse Width $\leq 300 \mu\text{s}$, Duty Cycle $\leq 2\%$.

Electrical Characteristics Diagrams

Figure 1. Typ. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Capacitance Characteristics




Figure 4. Gate Charge Waveform




Figure 5. Body-Diode Characteristics




Figure 6. Rdson-Drain Current




Figure 7. Rdson-Junction Temperature(°C)




Figure 8. Maximum Safe Operating Area





Figure 9. Normalized Maximum Transient Thermal Impedance (RthJC)



Test Circuit & Waveform

Figure 8. Gate Charge Test Circuit & Waveform




Figure 9. Resistive Switching Test Circuit & Waveforms




Figure 10. Unclamped Inductive Switching (UIS) Test Circuit & Waveform






Figure 11. Diode Recovery Circuit & Waveform




TO-220 PACKAGE INFORMATION



SYMBOL	COMMON DIMENSIONS					
	MM		INCH			
	MIN	NOM	MAX	MIN	NOM	MAX
A	4.37	4.57	4.70	0.172	0.180	0.185
A1	1.25	1.30	1.40	0.049	0.051	0.055
A2	2.20	2.40	2.60	0.087	0.094	0.102
b	0.70	0.80	0.95	0.028	0.031	0.037
b2	1.17	1.27	1.47	0.046	0.050	0.058
c	0.45	0.50	0.60	0.018	0.020	0.024
D	15.10	15.60	16.10	0.594	0.614	0.634
D1	8.80	9.10	9.40	0.346	0.358	0.370
D2	5.50	-	-	0.217	-	-
E	9.70	10.00	10.30	0.382	0.394	0.406
E3	7.00	-	-	0.276	-	-
e	2.54BCS			0.1BSC		
e1	5.08BCS			0.2REF		
H1	6.25	6.50	6.85	0.246	0.256	0.270
L	12.75	13.50	13.80	0.502	0.531	0.543
L1	-	3.10	3.40	-	0.122	0.134
ØP	3.40	3.60	3.80	0.134	0.142	0.150
Q	2.60	2.80	3.00	0.102	0.110	0.118

TO-220 Part Marking Information



Disclaimer

The content specified herein is for the purpose of introducing LONTEN's products (hereinafter "Products"). The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

LONTEN does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of the Products or technical information described in this document.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). LONTEN shall bear no responsibility in any way for use of any of the Products for the above special purposes.

Although LONTEN endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a LONTEN product.

The content specified herein is subject to change for improvement without notice. When using a LONTEN product, be sure to obtain the latest specifications.