

GENERAL DESCRIPTION

OB3621x is highly integrated buck regulator with advanced features to provide high efficiency control and high precision constant current output for LED lighting applications.

The proprietary CC control scheme is used and high precision constant current regulation is realized.

OB3621x offers comprehensive protection coverage with auto-recovery features including LED open loop protection, LED short circuit protection, cycle-by-cycle current limiting, built-in leading edge blanking, VDD under voltage lockout (UVLO), over temperature protection (OTP), thermal foldback etc.

OB3621x is offered in SOP-8 package.


FEATURES

- High precision constant current regulation at universal AC input
- Low system cost and high efficiency
- Quasi-Resonant operation
- Programmable CC regulation
- Thermal foldback function to control LED output current
- Insensitive to inductance and line voltage variation
- LED short circuit protection
- LED open loop protection
- Cycle-by-cycle current limiting
- Built-in leading edge blanking (LEB)
- VDD under voltage lockout with hysteresis
- Over temperature protection (OTP)

APPLICATIONS

■ LED lighting

TYPICAL APPLICATION






GENERAL INFORMATION

Pin Configuration

The pin map is shown as below.



Ordering Information

Part Number	Description
OB3621MCP	8Pin SOP, Pb free in Tube
OB3621MCPA	8Pin SOP, Pb free in T&R
OB3621NCP	8Pin SOP, Pb free in Tube
OB3621NCPA	8Pin SOP, Pb free in T&R
OB3621PCP	8Pin SOP, Pb free in Tube
OB3621PCPA	8Pin SOP, Pb free in T&R
OB3621NCP-F	8Pin SOP, Pb free in Tube
OB3621NCPA-F	8Pin SOP, Pb free in T&R
OB3621PCP-F	8Pin SOP, Pb free in Tube
OB3621PCPA-F	8Pin SOP, Pb free in T&R
OB3621TCP	8Pin SOP, Pb free in Tube
OB3621TCPA	8Pin SOP, Pb free in T&R

Note: All Devices are offered in Pb-free Package if not otherwise noted.

Package Dissipation Rating

Package	RθJA (℃/V	V)
SOP8	90	

Absolute Maximum Ratings

Parameter		Value	
VDD Voltage)	-0.3 to 20V	
CS Input Vol	tage	-0.3 to 7V	
FB Input Vol	tage	-0.3 to 7V	
DRAIN	OB3621M/N/P/T	-0.3 to 500V	
Voltage	OB3621N/P-F	-0.3 to 300V	
Min/Max Operating Junction Temperature T _J		-40 to 150 ℃	
Operating Ambient Temperature T _A		-40 to 85 ℃	
Min/Max Storage Temperature T _{stq}		-55 to 150 ℃	
Lead Temperature (Soldering, 10secs)		260 ℃	

Note: Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute maximum-rated conditions for extended periods may affect device reliability.

Recommended Operating Condition

Symbol	Parameter	Range	
VDD	VDD Supply Voltage	8 to 12V	


Output Power Table

Product	Condition	90Vac~264Vac Input	220Vac±20% Input
OB3621MCP	lo≤0.2A	8W	13.5W
OB3621NCP	lo≤0.25A	12W	24.5W
OB3621PCP	lo≤0.3A	17W	33.5W
OB3621TCP	lo≤0.3A	23.9W	37.2W


Product	Condition	90Vac~132Vac Input
OB3621NCP-F	lo≤0.25A	14W
OB3621PCP-F	lo≤0.3A	19W

Note: Maximum practical continuous power in an open frame design with sufficient drain pattern as a heat sink, at 50°C ambient and 60°C temperature rise. Higher output power is possible with extra added heat sink, air circulation and decrease output current to reduce thermal resistance.





Marking Information



Y: Year Code

WW: Week Code (01-52)

ZZZ:Lot Code

C: SOP8

P:Pb-free Package

S: Internal Code(Optional)



Y: Year Code


WW: Week Code (01-52)

ZZZ:Lot Code

C: SOP8

P:Pb-free Package

S: Internal Code(Optional)



Y: Year Code

WW: Week Code (01-52)

ZZZ:Lot Code

C: SOP8

P:Pb-free Package

S: Internal Code(Optional)



Y: Year Code

WW: Week Code (01-52)

ZZZ:Lot Code

C: SOP8


P:Pb-free Package


S: Internal Code(Optional)



PACKAGE MECHANICAL DATA

8-Pin Plastic SOP





Cymbol	Dimensions In Millimeters		Dimensions In Inches	
Symbol	Min	Max	Min	Max
Α	1.350	1.750	0.053	0.069
A1	0.050	0.250	0.002	0.010
A2	1.250	1.650	0.049	0.065
b	0.310	0.510	0.012	0.020
С	0.100	0.250	0.004	0.010
D	4.700	5.150	0.185	0.203
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
е	1.270 (BSC)		0.050 (BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°





High Precision Non-Isolated LED Lighting Driver

IMPORTANT NOTICE

RIGHT TO MAKE CHANGES

On-Bright Electronics Corp. reserves the right to make corrections, modifications, enhancements, improvements and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

WARRANTY INFORMATION

On-Bright Electronics Corp. warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with its standard warranty. Testing and other quality control techniques are used to the extent it deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed. On-Bright Electronics Corp. assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using On-Bright's components, data sheet and application notes. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

LIFE SUPPORT

On-Bright Electronics Corp.'s products are not designed to be used as components in devices intended to support or sustain human life. On-bright Electronics Corp. will not be held liable for any damages or claims resulting from the use of its products in medical applications.

MILITARY

On-Bright Electronics Corp.'s products are not designed for use in military applications. On-Bright Electronics Corp. will not be held liable for any damages or claims resulting from the use of its products in military applications.