

www.vishay.com

Vishay Siliconix

# P-Channel 60 V (D-S) 175 °C MOSFET


| PRODUCT SUMMARY     |                                    |      |  |  |
|---------------------|------------------------------------|------|--|--|
| V <sub>DS</sub> (V) | $R_{DS(on)}(\Omega)$               |      |  |  |
| -60                 | 0.0069 at V <sub>GS</sub> = -10 V  | -110 |  |  |
| -60                 | 0.0088 at V <sub>GS</sub> = -4.5 V | -110 |  |  |

#### **FEATURES**

- TrenchFET® power MOSFET
- Package with low thermal resistance



 Material categorization: for definitions of compliance please see www.vishav.com/doc?99912



#### **Ordering Information:**

SUM110P06-07L-E3 (Lead (Pb)-free)

| <b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_C = 25$     | °C, unless otherw                 | rise noted)     |      |     |  |
|--|-----------------------------------|-----------------|------|-----|--|
| PARAMETER  | SYMBOL                            | LIMIT           | UNIT |     |  |
| Drain-Source Voltage                             | V <sub>DS</sub>                   | -60             | V    |     |  |
| Gate-Source Voltage                              | V <sub>GS</sub>                   | ± 20            | 7 v  |     |  |
| Continuous Drain Current d                       | T <sub>C</sub> = 25 °C            |                 | -110 |     |  |
| $(T_J = 175  ^{\circ}C)$                         | T <sub>C</sub> = 125 °C           | I <sub>D</sub>  | -95  |     |  |
| Pulsed Drain Current                             | I <sub>DM</sub>                   | -240            | A    |     |  |
| Avalanche Current                                | che Current                       |                 | -75  |     |  |
| Single Pulse Avalanche Energy <sup>a</sup>       | L = 0.1 mH                        | E <sub>AS</sub> | 281  | mJ  |  |
| Deway Dissination                                | T <sub>C</sub> = 25 °C °          | Б               | 375  | W   |  |
| Power Dissipation                                | T <sub>A</sub> = 25 °C b          |                 | 3.75 | ] " |  |
| Operating Junction and Storage Temperature Range | T <sub>J</sub> , T <sub>stg</sub> | -55 to +175     | °C   |     |  |

| THERMAL RESISTANCE RATINGS |                        |                   |         |      |  |  |  |
|----------------------------|------------------------|-------------------|---------|------|--|--|--|
| PARAMETER                  |                        | SYMBOL            | TYPICAL | UNIT |  |  |  |
| Junction-to-Ambient        | PCB mount <sup>b</sup> | $R_{thJA}$        | 40      | °C/W |  |  |  |
| Junction-to-Case           |                        | R <sub>thJC</sub> | 0.4     | C/VV |  |  |  |

#### Notes

- a. Duty cycle ≤ 1 %.
- b. When mounted on 1" square PCB (FR4 material).
- c. See SOA curve for voltage derating.
- d. Limited by package.



www.vishay.com

# Vishay Siliconix

| PARAMETER                                | SYMBOL                      | TEST CONDITIONS  | MIN. | TYP.   | MAX.   | UNIT |  |
|--|-----------------------------|--|------|--------|--------|------|--|
| Static                                   |                             |  |      |        |        |      |  |
| Drain-Source Breakdown Voltage           | V <sub>DS</sub>             | $V_{GS} = 0 \text{ V}, I_D = -250 \mu\text{A}$                               | -60  | -      | -      | V    |  |
| Gate Threshold Voltage                   | V <sub>GS(th)</sub>         | $V_{DS} = V_{GS}, I_D = -250 \mu A$  | -1   | -      | -3     |      |  |
| Gate-Body Leakage                        | I <sub>GSS</sub>            | $V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$                            | -    | -      | ± 100  | nA   |  |
|  |                             | $V_{DS} = -60 \text{ V}, V_{GS} = 0 \text{ V}$                               | -    | -      | -1     |      |  |
| Zero Gate Voltage Drain Current          | I <sub>DSS</sub>            | $V_{DS} = -60 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 125 ^{\circ}\text{C}$ | -    | -      | -50    | μA   |  |
|  |                             | $V_{DS} = -60 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 175 ^{\circ}\text{C}$ | -    | -      | -250   |      |  |
| On-State Drain Current <sup>a</sup>      | I <sub>D(on)</sub>          | $V_{DS} = -5 \text{ V}, V_{GS} = -10 \text{ V}$                              | -120 | -      | -      | Α    |  |
|  |                             | $V_{GS} = -10 \text{ V}, I_D = -30 \text{ A}$                                | -    | 0.0055 | 0.0069 |      |  |
| Drain-Source On-State Resistance a       | <sub>D</sub>                | $V_{GS} = -10 \text{ V}, I_D = -30 \text{ A}, T_J = 125 \text{ °C}$          | -    | -      | 0.0115 |      |  |
| Diain-Source On-State Resistance         | R <sub>DS(on)</sub>         | $V_{GS} = -10 \text{ V}, I_D = -30 \text{ A}, T_J = 175 \text{ °C}$          | ı    | -      | 0.0138 | Ω    |  |
|  |                             | $V_{GS} = -4.5 \text{ V}, I_D = -20 \text{ A}$                               | -    | 0.0070 | 0.0088 |      |  |
| Forward Transconductance <sup>a</sup>    | 9 <sub>fs</sub>             | $V_{DS} = -15 \text{ V}, I_{D} = -50 \text{ A}$                              | 20   | -      | -      | S    |  |
| Dynamic <sup>b</sup>                     |                             |  |      |        |        |      |  |
| Input Capacitance                        | C <sub>iss</sub>            |  | -    | 11 400 | -      | pF   |  |
| Output Capacitance                       | Coss                        | $V_{GS} = 0 \text{ V}, V_{DS} = -25 \text{ V}, f = 1 \text{ MHz}$            | -    | 1200   | -      |      |  |
| Reverse Transfer Capacitance             | $C_{rss}$                   |  | -    | 900    | -      |      |  |
| Total Gate Charge <sup>c</sup>           | $Q_g$                       |  | 1    | 230    | 345    | nC   |  |
| Gate-Source Charge <sup>c</sup>          | Q <sub>gs</sub>             | $V_{DS} = -30 \text{ V}, V_{GS} = -10 \text{ V}, I_D = -110 \text{ A}$       | -    | 50     | -      |      |  |
| Gate-Drain Charge <sup>c</sup>           | $Q_{gd}$                    |  | -    | 60     | -      |      |  |
| Gate Resistance                          | R <sub>g</sub>              | f = 1 MHz  | -    | 3      | -      | Ω    |  |
| Turn-On Delay Time <sup>c</sup>          | t <sub>d(on)</sub>          |  | -    | 20     | 30     |      |  |
| Rise Time <sup>c</sup>                   | t <sub>r</sub>              | $V_{DD} = -30 \text{ V}, R_L = 0.27 \Omega$                                  | -    | 25     | 40     | ns   |  |
| Turn-Off Delay Time <sup>c</sup>         | t <sub>d(off)</sub>         | $I_D \cong -110 \text{ A}, V_{GEN} = -10 \text{ V}, R_g = 1 \Omega$          | -    | 110    | 200    |      |  |
| Fall Time <sup>c</sup>                   | t <sub>f</sub>              |  | -    | 50     | 100    |      |  |
| <b>Drain-Source Body Diode Character</b> | istics (T <sub>C</sub> = 25 | 5 °C b)  |      |        |        |      |  |
| Continuous Current                       | IS                          |  | -    | -      | -110   | ۸    |  |
| Pulsed Current                           | I <sub>SM</sub>             |  | ı    | -      | -240   | Α    |  |
| Forward Voltage <sup>a</sup>             | $V_{SD}$                    | I <sub>F</sub> = -85 A, V <sub>GS</sub> = 0 V                                | -    | -1     | -1.5   | V    |  |
| Reverse Recovery Time                    | t <sub>rr</sub>             |  | -    | 91     | 137    | ns   |  |
| Peak Reverse Recovery Charge             | I <sub>RM(REC)</sub>        | I <sub>F</sub> = -85 A, dl/dt = 100 A/μs                                     | -    | -6     | -9     | Α    |  |
| Reverse Recovery Charge                  | Q <sub>rr</sub>             |  |      | 0.21   | 0.44   | μC   |  |


#### Notes

- a. Pulse test; pulse width  $\leq$  300 µs, duty cycle  $\leq$  2 %.
- b. Guaranteed by design, not subject to production testing.
- c. Independent of operating temperature.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




### TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




#### **Output Characteristics**




### Transconductance






#### **Transfer Characteristics**




#### On-Resistance vs. Drain Current







### TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




#### On-Resistance vs. Junction Temperature




Avalanche Current vs. Time




Source-Drain Diode Forward Voltage



**Drain Source Breakdown vs. Junction Temperature** 




Maximum Avalanche and Drain Current vs. Case Temperature



Safe Operating Area



### TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)





Normalized Thermal Transient Impedance, Junction-to-Case


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <a href="https://www.vishay.com/ppg?72439">www.vishay.com/ppg?72439</a>.



# TO-263 (D<sup>2</sup>PAK): 3-LEAD









DETAIL A (ROTATED 90°)



| _ | ,  | —b<br><del>-</del> -b | <br> |        |     | 1        |
|---|----|-----------------------|------|--------|-----|----------|
| 2 | T  |                       |      | C      | _ ( | <u>-</u> |
|   | SE | ^TIC                  | M    | ا<br>م |     | 1        |

- 1. Plane B includes maximum features of heat sink tab and plastic.
- 2. No more than 25 % of L1 can fall above seating plane by max. 8 mils.
- 3. Pin-to-pin coplanarity max. 4 mils.
- 4. \*: Thin lead is for SUB, SYB. Thick lead is for SUM, SYM, SQM.
- 5. Use inches as the primary measurement.

6 This feature is for thick lead.

|                                 |            | INC   | HES                 | MILLIMETERS |        |  |
|---------------------------------|------------|-------|---------------------|-------------|--------|--|
|                                 | DIM.       | MIN.  | MAX.                | MIN.        | MAX.   |  |
| Α                               |            | 0.160 | 0.190               | 4.064       | 4.826  |  |
|                                 | b          | 0.020 | 0.039               | 0.508       | 0.990  |  |
|                                 | b1         | 0.020 | 0.035               | 0.508       | 0.889  |  |
|                                 | b2         | 0.045 | 0.055               | 1.143       | 1.397  |  |
| c*                              | Thin lead  | 0.013 | 0.018               | 0.330       | 0.457  |  |
|                                 | Thick lead | 0.023 | 0.028               | 0.584       | 0.711  |  |
| c1                              | Thin lead  | 0.013 | 0.017               | 0.330       | 0.431  |  |
| CI                              | Thick lead | 0.023 | 0.027               | 0.584       | 0.685  |  |
|                                 | c2         | 0.045 | 0.055               | 1.143       | 1.397  |  |
|                                 | D          | 0.340 | 0.380               | 8.636       | 9.652  |  |
|                                 | D1         | 0.220 | 0.240               | 5.588       | 6.096  |  |
|                                 | D2         | 0.038 | 0.042               | 0.965       | 1.067  |  |
|                                 | D3         | 0.045 | 0.055               | 1.143       | 1.397  |  |
|                                 | D4         | 0.044 | 0.052               | 1.118       | 1.321  |  |
|                                 | Е          | 0.380 | 0.410               | 9.652       | 10.414 |  |
|                                 | E1         | 0.245 | -                   | 6.223       | -      |  |
|                                 | E2         | 0.355 | 0.375               | 9.017       | 9.525  |  |
|                                 | E3         | 0.072 | 0.078               | 1.829       | 1.981  |  |
|                                 | е          | 0.100 | BSC                 | 2.54 BSC    |        |  |
|                                 | K          | 0.045 | 0.055               | 1.143       | 1.397  |  |
| L                               |            | 0.575 | 0.625               | 14.605      | 15.875 |  |
| L1                              |            | 0.090 | 0.110               | 2.286       | 2.794  |  |
|                                 | L2         | 0.040 | 0.055               | 1.016       | 1.397  |  |
| L3                              |            | 0.050 | 0.070               | 1.270       | 1.778  |  |
| L4                              |            | 0.010 | 0.010 BSC 0.254 BSG |             |        |  |
| М                               |            | -     | 0.002               | -           | 0.050  |  |
| ECN: T13-0707-Rev. K, 30-Sep-13 |            |       |                     |             |        |  |

DWG: 5843





### RECOMMENDED MINIMUM PADS FOR D<sup>2</sup>PAK: 3-Lead



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index



# **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.