www.vishay.com

Vishay General Semiconductor

# Surface Mount Schottky Barrier Rectifier



DO-214AC (SMA)

2.0 A

50 V, 60 V

40 A

0.53 V

150 °C

DO-214AC (SMA)

Single

**PRIMARY CHARACTERISTICS** 

I<sub>F(AV)</sub>

V<sub>RRM</sub>

IFSM

 $V_F$  at  $I_F = 2.0 \text{ A}$ 

T<sub>J</sub> max.

Package

**Diode variations** 

## **FEATURES**

- Low profile package
- · Ideal for automated placement
- Guardring for overvoltage protection
- Low power losses, high efficiency
- Low forward voltage drop
- · High surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 gualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

## **TYPICAL APPLICATIONS**

For use in low voltage, high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

## **MECHANICAL DATA**

Case: DO-214AC (SMA)


Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/NHE3\_X - RoHS-compliant and AEC-Q101 qualified ("\_X" denotes revision code e.g. A, B, ....)

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 2 whisker test, HE3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes the cathode end

<b>MAXIMUM RATINGS</b> ( $T_A = 25 \text{ °C}$ unless otherwise noted)						
PARAMETER	SYMBOL	SS25S	SS26S	UNIT		
Device marking code		25S	26S			
Maximum repetitive peak reverse voltage	V <sub>RRM</sub>	50	60	V		
Maximum average forward rectified current (fig. 1)	I <sub>F(AV)</sub>	2.0		A		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	40		A		
Operating junction temperature range	T <sub>J</sub> , T <sub>STG</sub>	-55 to +150		°C		





www.vishay.com

## Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> ( $T_A = 25 \text{ °C}$ unless otherwise noted)							
PARAMETER	TEST CO	TEST CONDITIONS		TYP.	MAX.	UNIT	
Maximum instantaneous forward voltage <sup>(1)</sup>	I <sub>F</sub> = 1.0 A		- V <sub>F</sub>	0.51	-	V	
	I <sub>F</sub> = 2.0 A			0.60	0.75		
	I <sub>F</sub> = 1.0 A	- T <sub>A</sub> = 125 °C		0.43	-		
	I <sub>F</sub> = 2.0 A			0.53	0.62		
Maximum reverse current <sup>(2)</sup>	Rated V <sub>B</sub>	T <sub>A</sub> = 25 °C	T <sub>A</sub> = 25 °C	1	-	200	μA
	naleu v <sub>R</sub>	T <sub>A</sub> = 125 °C	IR	1.5	10	mA	

#### Notes

<sup>(1)</sup> Pulse test: 300 µs pulse width, 1 % duty cycle

<sup>(2)</sup> Pulse test: Pulse width  $\leq$  40 ms

<b>THERMAL CHARACTERISTICS</b> ( $T_A = 25 \text{ °C}$ unless otherwise noted)						
PARAMETER	SYMBOL	ABOL SS25S SS26S		UNIT		
Typical thermal resistance <sup>(1)</sup>	$R_{\theta JA}$	100		°C/W		
	$R_{ ext{ heta}JL}$	28				

#### Note

<sup>(1)</sup> PCB mounted with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
SS26S-E3/61T	0.064	61T	1800	7" diameter plastic tape and reel	
SS26S-E3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel	
SS26SHE3_B/H (1)	0.064	Н	1800	7" diameter plastic tape and reel	
SS26SHE3_B/I (1)	0.064	I	7500	13" diameter plastic tape and reel	

Note

(1) AEC-Q101 qualified

## RATINGS AND CHARACTERISTICS CURVES (T<sub>A</sub> = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics






Fig. 3 - Typical Instantaneous Forward Characteristics





Fig. 4 - Typical Reverse Characteristics

## **PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

DO-214AC (SMA)






Fig. 5 - Typical Junction Capacitance

Revision: 09-Nov-16 Document Number: 89055 3 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

0.074 (1.88)

MAX.



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.