




<p><b>General Description</b></p> <ul style="list-style-type: none"> <li>• Trench Power MOSFET Technology</li> <li>• Low <math>R_{DS(ON)}</math></li> <li>• Optimized for High Reliable Switch Application</li> <li>• High Current Capability</li> <li>• RoHS and Halogen-Free Compliant</li> </ul> <p><b>Applications</b></p> <ul style="list-style-type: none"> <li>• Motor Drive</li> <li>• Load Switch</li> <li>• Battery Protection</li> <li>• General DC/DC Converters</li> </ul>	<p><b>Product Summary</b></p> <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 70%;"><math>V_{DS}</math></td> <td style="text-align: right;">30V</td> </tr> <tr> <td><math>I_D</math> (at <math>V_{GS}=10V</math>)</td> <td style="text-align: right;">183A</td> </tr> <tr> <td><math>R_{DS(ON)}</math> (at <math>V_{GS}=10V</math>, typ)</td> <td style="text-align: right;">2.3m<math>\Omega</math></td> </tr> <tr> <td><math>R_{DS(ON)}</math> (at <math>V_{GS}=4.5V</math>, typ)</td> <td style="text-align: right;">2.7m<math>\Omega</math></td> </tr> </table> <p>100% UIS Tested 100% <math>R_G</math> Tested</p>	$V_{DS}$	30V	$I_D$ (at $V_{GS}=10V$ )	183A	$R_{DS(ON)}$ (at $V_{GS}=10V$ , typ)	2.3m $\Omega$	$R_{DS(ON)}$ (at $V_{GS}=4.5V$ , typ)	2.7m $\Omega$
$V_{DS}$	30V								
$I_D$ (at $V_{GS}=10V$ )	183A								
$R_{DS(ON)}$ (at $V_{GS}=10V$ , typ)	2.3m $\Omega$								
$R_{DS(ON)}$ (at $V_{GS}=4.5V$ , typ)	2.7m $\Omega$								



Orderable Part Number	Package Type	Form	Minimum Order Quantity
VIS30023	TO-263	Tape & Reel	3000

**Absolute Maximum Ratings**  $T_A=25^\circ C$  unless otherwise noted

Parameter	Symbol	Maximum	Units
Drain-Source Voltage	$V_{DS}$	30	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current <sup>(5)</sup>	$I_D$	$T_C=25^\circ C$	A
		$T_C=100^\circ C$	
Pulsed Drain Current <sup>(3)</sup>	$I_{DM}$	449	
Continuous Drain Current	$I_{DSM}$	$T_A=25^\circ C$	A
		$T_A=70^\circ C$	32
Avalanche Current <sup>(3)</sup>	$I_{AS}$	65	A
Avalanche energy $L=0.1mH$ <sup>(3)</sup>	$E_{AS}$	211	mJ
Power Dissipation <sup>(2)</sup>	$P_D$	$T_C=25^\circ C$	W
		$T_C=100^\circ C$	
Power Dissipation <sup>(1)</sup>	$P_{DSM}$	$T_A=25^\circ C$	W
		$T_A=70^\circ C$	4.3
Junction and Storage Temperature Range	$T_J, T_{STG}$	-55 to 150	$^\circ C$

**Thermal Characteristics**

Parameter	Symbol	Typ	Max	Units
Maximum Junction-to-Ambient <sup>(1)</sup> $t \leq 10s$	$R_{\theta JA}$	15.3	18.4	$^\circ C/W$
Maximum Junction-to-Ambient <sup>(1,4)</sup> Steady-State		67.9	81.5	$^\circ C/W$
Maximum Junction-to-Case Steady-State	$R_{\theta JC}$	0.74	0.89	$^\circ C/W$



# VIS30023


## 30V N-Channel Power Trench MOSFET

### Electrical Characteristics ( $T_J=25^\circ\text{C}$ unless otherwise noted)


Symbol	Parameter	Conditions	Min	Typ	Max	Units
<b>STATIC PARAMETERS</b>						
$BV_{DSS}$	Drain-Source Breakdown Voltage	$I_D=250\text{mA}, V_{GS}=0\text{V}$	30			V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=30\text{V}, V_{GS}=0\text{V}$ $T_J=55^\circ\text{C}$			1 5	$\mu\text{A}$
$I_{GSS}$	Gate-Body leakage current	$V_{DS}=0\text{V}, V_{GS}=\pm 20\text{V}$			$\pm 100$	nA
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\text{mA}$	1.4	1.8	2.2	V
$R_{DS(on)}$	Static Drain-Source On-Resistance	$V_{GS}=10\text{V}, I_D=20\text{A}$ $T_J=125^\circ\text{C}$		2.3 2.5	2.8	m $\Omega$
		$V_{GS}=4.5\text{V}, I_D=20\text{A}$		2.7	3.3	
$g_{FS}$	Forward Transconductance	$V_{DS}=5\text{V}, I_D=20\text{A}$		120		S
$V_{SD}$	Diode Forward Voltage	$I_S=1\text{A}, V_{GS}=0\text{V}$		0.69		V
$I_S$	Maximum Body-Diode Continuous Current				140	A
<b>DYNAMIC PARAMETERS</b>						
$C_{iss}$	Input Capacitance	$V_{GS}=0\text{V}, V_{DS}=15\text{V}, f=1\text{MHz}$		6335		pF
$C_{oss}$	Output Capacitance			756		pF
$C_{rss}$	Reverse Transfer Capacitance			367		pF
$R_g$	Gate resistance	$f=1\text{MHz}$		0.8		$\Omega$
<b>SWITCHING PARAMETERS</b>						
$Q_g(10\text{V})$	Total Gate Charge	$V_{GS}=10\text{V}, V_{DS}=15\text{V}, I_D=20\text{A}$		104		nC
$Q_g(4.5\text{V})$	Total Gate Charge			51		nC
$Q_{gs}$	Gate Source Charge			15		nC
$Q_{gd}$	Gate Drain Charge			18		nC
$t_{D(on)}$	Turn-On Delay Time	$V_{GS}=10\text{V}, V_{DS}=15\text{V},$ $R_L=0.75\text{W}, R_{GEN}=3\text{W}$		8.6		ns
$t_r$	Turn-On Rise Time			9.6		ns
$t_{D(off)}$	Turn-Off Delay Time			58.4		ns
$t_f$	Turn-Off Fall Time			22.8		ns
$t_{rr}$	Body Diode Reverse Recovery Time	$I_F=20\text{A}, di/dt=500\text{A/ms}$		29.3		ns
$Q_{rr}$	Body Diode Reverse Recovery Charge	$I_F=20\text{A}, di/dt=500\text{A/ms}$		20.5		nC

- 1)  $R_{\theta JA}$  is measured with the stand-alone device, without PCB, in a still air environment with  $T_A=25^\circ\text{C}$ . The Power dissipation  $P_{DSM}$  is based on  $R_{\theta JA} \leq 10\text{s}$  and the maximum allowed junction temperature of  $150^\circ\text{C}$ . The value in any given application depends on the user's specific board design.
- 2) The power dissipation  $P_D$  is based on  $T_{J(MAX)}=150^\circ\text{C}$ , using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.
- 3) Single pulse width limited by junction temperature  $T_{J(MAX)}=150^\circ\text{C}$ .
- 4)  $R_{\theta JA}$  is the sum of the thermal impedance from junction to case  $R_{\theta JC}$  and case to ambient.
- 5) The maximum current rating is package limited.


### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




**Fig 1.** Typical Output Characteristics




**Fig 2.** Typical Transfer Characteristics




**Fig 3.** Normalized On-Resistance vs. Temperature



**Fig 4.** Typical Capacitance vs.  $V_{DS}$




**Fig 5.** Typical Gate Charge vs.  $V_{GS}$




**Fig 6.** Typical Source-Drain Diode Forward Voltage


### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




**Fig 7. Maximum Safe Operating Area**



**Fig 8. Maximum Drain Current vs. Case Temperature**




**Fig 9. Normalized Maximum Transient Thermal Impedance, Junction-to-Case**




**Fig 10. Normalized Maximum Transient Thermal Impedance, Junction-to-Ambient**


### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




**Fig 11.** Single Pulse Power Rating Junction-to-Case




**Fig 12.** Single Pulse Power Rating Junction-to-Ambient



**Fig 13.** Maximum Power Rating vs. Temperature




**Fig 14.** Maximum Power Rating vs.  $V_{GS}$




**Fig 15.** On-Resistance vs. Drain Current


### TEST CIRCUIT




**Fig16.** Unclamped Inductive Test Circuit




**Fig17.** Unclamped Inductive Waveform




**Fig18.**  $Q_g$  Test Circuit



**Fig19.**  $Q_g$  Waveform




**Fig18.** Resistive Switching Test Circuit




**Fig19.** Switching Time Waveform



### TEST CIRCUIT



**Fig20.** Diode Recovery Test Circuit



**Fig21.** Diode Recovery Test Waveform



SYMBOL	MILLIMETERS	
	MIN [mm]	MAX [mm]
A	4.470	4.670
A1	0.000	0.150
B	1.120	1.420
b	0.710	0.910
b1	1.170	1.370
c	0.310	0.530
c1	1.170	1.370
D	10.010	10.310
E	8.500	8.900
e	2.540 TYP.	
e1	4.980	5.180
L	14.940	15.500
L1	4.950	5.450
L2	2.340	2.740
L3	1.300	1.700
$\Phi$	0°	8°
V	5.600 REF.	