Vishay Dale



Wirewound Resistors, Precision Power, Low Value, Commercial, Axial Lead



**DESIGN SUPPORT TOOLS** 

click logo to get started



## FEATURES

- Ideal for all types of current sensing applications including switching and linear power supplies, instruments and power amplifiers
- Excellent load life stability
- Low temperature coefficient
- · Low inductance
- MIL-PRF-49465 qualified, type RLV resistors can be found at: <u>www.vishay.com/doc?30283</u>

 Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Note

\* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS
------------------------------------

GLOBAL MODEL	HISTORICAL MODEL	POWER RATING P <sub>25 °C</sub> W	RESISTANCE RANGE <sup>(1)</sup> Ω	TOLERANCE ± %	TECHNOLOGY	WEIGHT (typical) g
LVR01	LVR-1	1	0.01 to 0.1 <sup>(2)</sup>	1, 3, 5, 10	Metal strip	0.5
LVR03	LVR-3	3	0.005 to 0.2	1, 3, 5, 10	Metal strip	2
LVR05	LVR-5	5	0.005 to 0.3	1, 3, 5, 10	Metal strip	5
LVR10	LVR-10	10	0.01 to 0.8	1, 3, 5, 10	Coil spacewound	11

#### Notes

(1) Resistance is measured 3/8" [9.52 mm] from the body of the resistor, or at 1.183" [30.05 mm], 1.315" [33.40 mm], 1.675" [42.545 mm] or 2.575" [65.405 mm] spacing for the LVR01, LVR03, LVR05 and LVR10 respectively

(2) LVR01: Standard resistance values are 0.01  $\Omega$ , 0.015  $\Omega$ , 0.02  $\Omega$ , 0.025  $\Omega$ , 0.03  $\Omega$ , 0.033  $\Omega$ , 0.04  $\Omega$ , 0.05  $\Omega$ , 0.051  $\Omega$ , 0.06  $\Omega$ , 0.068  $\Omega$ , 0.07  $\Omega$ , 0.08  $\Omega$ , 0.09  $\Omega$  and 0.1  $\Omega$  with 1 % tolerance. Other resistance values may be available upon request

TECHNICAL SPECIFICATIONS					
PARAMETER	UNIT	LVR01	LVR03	LVR05	LVR10
Operating Temperature Range	°C	-65 to +175	-65 to +275		
Dielectric Withstanding Voltage	V <sub>AC</sub>	1000	1000	1000	1000
Insulation Resistance	Ω	10 000 MΩ minimum dry			
Short Time Overload	-	5 x rated power for 5 s 10 x rated pow			10 x rated power for 5 s
Terminal Strength (minimum)	lb	5	10	10	10
Maximum Working Voltage	V	$(P \times R)^{1/2}$			

#### **GLOBAL PART NUMBER INFORMATION** Global Part Numbering example: LVR055L000FS73 (visit www.vishav.net Vishay Dale parts numbering manual for all options) ν R 0 5 5 L 0 0 0 F S 7 3 GLOBAL MODEL VALUE TOI FRANCE PACKAGING SPFCIAL LVR01 $D = \pm 0.5 \%$ E12 = lead (Pb)-free bulk (dash number) **R** = decimal LVR03 **F** = ± 1.0 % E03 = lead (Pb)-free lacer pack (LVR10) (up to 3 digits) $L = m\Omega$ From 1 to 999 LVR05 (values < 0.010 Ω) $G = \pm 2.0 \%$ E70 = lead (Pb)-free, tape / reel 1000 pieces (LVR01, 03) as applicable **LVR10 R1500** = 0.15 Ω $H = \pm 3.0 \%$ E73 = lead (Pb)-free, tape / reel 500 pieces **7L000** = 0.007Ω $J = \pm 5.0 \%$ B12 = tin / lead bulk **K** = ± 10.0 % L03 = tin / lead lacer pack (LVR10) **S70** = tin / lead, tape / reel 1000 pieces (LVR01, 03) S73 = tin / lead, tape/reel 500 pieces

Revision: 15-Nov-17

Document Number: 30206

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



รงหร

HALOGEN

FREE


GREEN

<u>(5-2008)</u>



**LVR** Vishay Dale

### **DIMENSIONS** in inches [millimeters]



	DIMENSIONS in inches [millimeters]			
MODEL	A ± 0.010 [0.254]	B ± 0.010 [0.254]	C ± 0.002 [0.051]	
LVR01	0.427 [10.85]	0.115 [2.92]	0.020 [0.508]	
LVR03	0.560 [14.22]	0.205 [5.21]	0.032 [0.813]	
LVR05	0.925 [23.50]	0.330 [8.38]	0.040 [1.02]	
LVR10	1.828 [46.43]	0.392 [9.96]	0.040 [1.02]	

#### Note

<sup>(1)</sup> On some standard reel pack methods, the leads may be trimmed to a shorter length than shown

#### **MATERIAL SPECIFICATIONS**

**Element:** Self-supporting nickel-chrome alloy (LVR10 also utilizes manganin)


Encapsulation: High temperature mold compound

Terminals: Tinned copper

Part Marking: Dale, model, wattage, value, tolerance, date code

**Packaging:** Reference "Wirewound Through Hole Resistor Packaging" (<u>www.vishay.com/doc?21028</u>)

#### DERATING



TEMPERATURE COEFFICIENT (ppm/°C)					
LVR01	LVR03	LVR05	LVR10		
$\begin{array}{c} \pm \ 1000 \ \text{for} \ 0.01 \ \Omega \ \text{to} \ 0.0249 \ \Omega \\ \pm \ 400 \ \text{for} \ 0.025 \ \Omega \ \text{to} \ 0.0499 \ \Omega \\ \pm \ 300 \ \text{for} \ 0.05 \ \Omega \ \text{to} \ 0.0749 \ \Omega \\ \pm \ 250 \ \text{for} \ 0.075 \ \Omega \ \text{to} \ 0.099 \ \Omega \\ \pm \ 150 \ \text{for} \ 0.1 \ \Omega \ \text{to} \ 0.1 \ \Omega \end{array}$	$\begin{array}{c} \pm 850 \text{ for } 0.005 \ \Omega \text{ to } 0.0099 \ \Omega \\ \pm 350 \text{ for } 0.01 \ \Omega \text{ to } 0.0249 \ \Omega \\ \pm 200 \text{ for } 0.025 \ \Omega \text{ to } 0.0499 \ \Omega \\ \pm 125 \text{ for } 0.05 \ \Omega \text{ to } 0.0749 \ \Omega \\ \pm 75 \text{ for } 0.075 \ \Omega \text{ to } 0.099 \ \Omega \\ \pm 50 \text{ for } 0.1 \ \Omega \text{ to } 0.2 \ \Omega \end{array}$	$\begin{array}{c} \pm\ 650\ for\ 0.005\ \Omega\ to\ 0.0099\ \Omega\\ \pm\ 250\ for\ 0.01\ \Omega\ to\ 0.0249\ \Omega\\ \pm\ 150\ for\ 0.025\ \Omega\ to\ 0.0499\ \Omega\\ \pm\ 100\ for\ 0.05\ \Omega\ to\ 0.0749\ \Omega\\ \pm\ 75\ for\ 0.075\ \Omega\ to\ 0.099\ \Omega\\ \pm\ 50\ for\ 0.1\ \Omega\ to\ 0.3\ \Omega\end{array}$	$\begin{array}{c} \pm \; 300 \; \text{for} \; 0.01 \; \Omega \; \text{to} \; 0.0249 \; \Omega \\ \pm \; 150 \; \text{for} \; 0.025 \; \Omega \; \text{to} \; 0.0499 \; \Omega \\ \pm \; 125 \; \text{for} \; 0.05 \; \Omega \; \text{to} \; 0.0749 \; \Omega \\ \pm \; 100 \; \text{for} \; 0.075 \; \Omega \; \text{to} \; 0.099 \; \Omega \\ \pm \; 50 \; \text{for} \; 0.1 \; \Omega \; \text{to} \; 0.8 \; \Omega \end{array}$		

PERFORMANCE				
TEST	CONDITIONS OF TEST	TEST LIMITS		
Thermal Shock	-65 °C to +125 °C, 5 cycles, 15 min at each extreme	± (0.2 % + 0.0005 Ω) Δ <i>R</i>		
Short Time Overload	5x rated power (LVR01, 03, 05), 10 x rated power (LVR10) for 5 s	± (0.5 % + 0.0005 Ω) Δ <i>R</i>		
Low Temperature Storage	-65 °C for 24 h	$\pm$ (0.2 % + 0.0005 Ω) ΔR		
High Temperature Exposure	250 h at +275 °C (+175 °C for LVR01)	± (2.0 % + 0.0005 Ω) Δ <i>R</i>		
Dielectric Withstanding Voltage	1000 V <sub>RMS</sub> , 1 min	± (0.1 % + 0.0005 Ω) Δ <i>R</i>		
Insulation Resistance	MIL-STD-202 Method 302, 100 V	1000 M $\Omega$ minimum		
Moisture Resistance	MIL-STD-202 Method 106, 7b not applicable	$\pm$ (0.2 % + 0.0005 Ω) Δ <i>R</i>		
Shock, Specified Pulse	MIL-STD-202 Method 213, 100 g's for 6 ms, 10 shocks	± (0.1 % + 0.0005 Ω) Δ <i>R</i>		
Vibration, High Frequency	Frequency varied 10 Hz to 2000 Hz, 20 g peak, 2 directions 6 h each	$\pm$ (0.1 % + 0.0005 Ω) Δ <i>R</i>		
Load Life	2000 h at rated power, +25 °C, 1.5 h "ON", 0.5 h "OFF"	± (2.0 % + 0.0005 Ω) Δ <i>R</i>		
Bias Humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	± (1.0 % + 0.0005 Ω) Δ <i>R</i>		



Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.