深圳市业展电子有限公司

承认书

SPECIFICATION FOR APPROVAL

Customer Name 客户料号	e							
Customer P/N 产品名称								
Product Name 产品规格	Alloy Shunt	Alloy Shunt Resistors – SBB Series						
Product Type	SBB-M-1F	-n-t2						
申请承认日期			版本					
Apply Date	2019-07-12	2	REV.					
Restrict use of		质.遵守 ACBEI ances of level 1	; Comply with "S	观范"中所要求之合 Specification for I				
供货商印鉴	APPROVED	CHECKED	PREPARED	承认印鉴				
Vendor Stamp				Stamp				
			邓小辉					

Mainland China: 深圳市业展电子有限公司

客户名称

Shenzhen Yezhan Electronics Co., Ltd.

Add: 深圳市龙华区环观中路荣倡工业园 7 栋 4 楼

Tel: 0755-26517682 Fax: 0755-83918284

E-mail: yezhan@yezhan.com.cn

标准书名 Classification 承认书 Specification	Spec No.	YZ-QR-EN-007
品 名 : 内拆分流电阻 SBB Series	Version	1.5
Product Name: Alloy Shunt Resistors	Page	5-2

1. 一般事项 General

1.1 适用范围 Scope

本承认书适用于深圳市业展电子有限公司 制造之[内折分流电阻]。

This specification is available for Alloy Shunt Resistors manufactured by

Shenzhen Yezhan Electronics Co., Ltd.

1.2 品质 Quality

本电阻器的制造系经高质量管理程序,并具有高信赖性的质量保证,且符合 RoHS 和无卤要求。

The resistor is manufactured by highly quality-controlled process and guaranteed high reliability,

it meets RoHS & Halogen-Free requirement.

1.3 标准试验狀态 Standard measuring conditions

温度 20±2℃、湿度 65±5%。

但在温度 5~35℃、湿度 45~85%之情况下,仍可给予判定。


Temperature $20\pm2^{\circ}$ C, Humidity $65\pm5\%$.

Being no doubt about the judgment, measurements can be made within the following Temperature

 $5\sim35$ °C, Humidity $45\sim85$ %.


1.4 形名 (例) Type designation (example)

依使用种類、线径、脚距、形狀、公称电阻值、电阻值容许差而区别,其构造如下: The type designation shall be in the following form and as specified.




标准书名 Classification 承认书 Specification	Spec No.	YZ-QR-EN-007
品 名 : 内拆分流电阻 SBB Series	Version	1.5
Product Name: Alloy Shunt Resistors	Page	5-3

1.5 功率曲线 Power Derating



1.6 温度系数曲线 TCR Derating



标准书名 Classification 承认书 Specification	Spec No.	YZ-QR-EN-007
	Version	1.5
Product Name: Alloy Shunt Resistors	Page	5-4

1.7 外形 External

项 目	参数
图解	T W
M	6.6mm±0.3mm
Н	3.0mm±0.5mm
Т	0.33mm±0.1mm
Α	2.5mm±0.2mm
X	4.8mm±0.5mm
D	0.9mm±0.1mm
W	6.9±0.3mm
阻值	1mΩ±1%
额定功率	5W
使用温度	-65℃~170℃


标准书名 Classification 承认书 Specification	Spec No.	YZ-QR-EN-007
品 名 : 内拆分流电阻 SBB Series	Version	1. 5
Product Name: Alloy Shunt Resistors	Page	5-5

2 应用范围 Applications

- 混合应用的电源电流传感器 Current sensor for power hybrid applications
- 变频器 Frequency converters
- 电源模块 Power modules
- 通讯系统 Communication system
- 自动化控制电源 Automatic control power supply
- 汽车市场的高电流应用 High current applications for the automotive market

3 包装 Packaging

编带 Embossed Plastic Tape Specifications



Туре	A	В	W	Е	F	P0	P1	P2	D0	T	Quantity (EA)
In	7. 5	8	16	1. 75	7. 35	6	12	12	1.5	3.8	3000
0ut	7. 5	12. 1	24	1. 75	12. 2	6	12	12	1.5	3. 5	1000

4 工作特性 Performance Date

Iterms	Additional Requirements	Reference	Limits
Temperature Cycling	1000 Cycles(-55℃ to +125℃) Measurement at 24±2hours after test conclusion	JESD22 Method JA-104	±0.5%
High Temperature Exposure	1000hrs.@T=125℃.Unpowered. Measurement at 24±2hours after test conclusion	MIL-STD-202 Method 108	±1%
Biased Humidity	1000hrs 85℃/85%RH。Note: Specified conditions: 10% of operating power. Measurement at 24±2hours after test conclusion	MIL-STD-202 Method 103	±0.5%
Operational Life	Condition D Steady State TA=125°C at rated power. Measurement at 24±2hours after test conclusion	MIL-STD-202 Method 108	±1%
Solderability	245℃±5℃,5s+0.5s/-0	J-STD-002C	95% Coverage Min
Resistance to Soldering Heat	260℃±5℃, 10s±1s Measurement at 24±2hours after test conclusion	MIL-STD-202 Method 210	±0.5%
Short Time Overload	5×Rated power for 5 s Measurement at 24±2hours after test conclusion	MIL-STD-202 Method 301	±0.5%