

# S32BF THRU S320BF

### 3.0AMPS. SCHOTTKY BARRIER RECTIFIERS

### **FEATURE**

- . For surface mounted application
- . High current capability
- . Low forward voltage drop
- . Low power loss, high efficiency
- . High surge current capability
- . High temperature soldering guaranteed:

260°C/10 seconds at terminals.

#### MECHANICAL DATA


. Terminal: Solder plated

. Case: Molded with UL-94 Class V-0 recognized

Flame Retardant Epoxy

. Polarity: color band denotes cathode

. Packaging: 12mm tape per EIA STD RS-481



Dimensions in inches and (millimeters)

## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	SYMBOL	S32BF	S34BF	S36BF	S310BF	S315BF	S320BF	units
Maximum Recurrent Peak Reverse Voltage	$V_{ m RRM}$	20	40	60	100	150	200	V
Maximum RMS Voltage	$V_{ m RMS}$	14	28	42	70	105	140	V
Maximum DC blocking Voltage	$V_{ m DC}$	20	40	60	100	150	200	V
Maximum Average Forward Rectified Current at $T_L$ =90°C	I <sub>F(AV)</sub>	3.0						A
Peak Forward Surge Current 8.3ms single half sine- wave superimposed on rated load (JEDEC method)		80.0						A
Maximum Forward Voltage at 3.0A DC	$V_{\mathrm{F}}$	0.45	0.55	0.70	0.85	0.95		V
Maximum DC Reverse Current @T <sub>A</sub> =25°C at rated DC blocking voltage @T <sub>A</sub> =100°C	$I_{\mathrm{R}}$	0.5     0.1       40.0     10.0					mA	
Typical Junction Capacitance (Note1)	C <sub>J</sub>	300			72			pF
Typical Thermal Resistance (Note 2)	R <sub>(JA)</sub>	75						℃/W
	$R_{(JL)}$	22						
Storage Temperature	T <sub>STG</sub>	-55 to +150						°C
Operation Junction Temperature	$T_{ m J}$	-55 to +125 -55 to +150					°C	

## Note:

- 1. Measured at 1.0 MHz and applied reverse voltage of 4.0Vdc
- 2. Thermal Resistance from Junction to Ambient and Lead, Mounted.Measured on P.C. Board with 0.2×0.2"(5.0×5.0mm) Copper Pad Areas.