NX5032GA

Features

A small surface-mount type crystal unit, ideal for Automotive.

Compatible with an engine control CPU clock delivering the high reliability that is particularly demanded, and compatible with low frequencies starting from 8 MHz. •Compact and thin. (5.0 × 3.2 × 1.3 mm typ.)

- •Stable start-up characteristic even under extremely severe environmental conditions.
- •Excellent environmental characteristics, including heat, vibration and shock resistance.
- •Meets the requirements for re-flow profiling using lead-free solder.
- •Conforms to AEC-Q200.




RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/863

Specifications

Item Model	NX5032GA	
Nominal Frequency	8 to 10.499MHz	10.5 to 40MHz
Overtone Order	Fundamental	
Frequency Tolerance (25 ±3 °C)	±50 × 10 ⁻⁶	
Frequency versus Temperature Characteristics (with reference to +25 °C)	±150 × 10 ⁻⁶	
Operating Temperature Range	-40 to +150 °C	
Storage Temperature Range	-40 to +150 °C	
Equivalent Series Resistance	Refer to *1	
Level of Drive	10 μW (Max. 500 μW)	
Load Capacitance	8 pF	
Specifications Number	STD-CSU-1	STD-CSU-2

Dimensions



Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*1 Equivalent Series Resistance

Nominal frequency (MHz)	Equivalent Series Resistance max. [Ω]	
8 to 9.5	300	
9.5 to 10	220	
10 to 15	150	
15 to 20	120	
20 to 24	100	
24 to 30	80	
30 to 40	50	



For Automotive