# **MOSFET** - Power, Single N-Channel

60 V, 0.68 mΩ, 477 A

# **NVMTSOD7N06CL**

#### **Features**

- Small Footprint (8x8 mm) for Compact Design
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Q<sub>G</sub> and Capacitance to Minimize Driver Losses
- Power 88 Package, Industry Standard
- AEC-Q101 Qualified and PPAP Capable
- Wettable Flank Option for Enhanced Optical Inspection
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

#### **MAXIMUM RATINGS** (T<sub>J</sub> = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V <sub>DSS</sub>	60	V
Gate-to-Source Voltage	9		$V_{GS}$	±20	V
Continuous Drain	Steady State	T <sub>C</sub> = 25°C	I <sub>D</sub>	477	Α
Current R <sub>0JC</sub> (Notes 1, 3)		T <sub>C</sub> = 100°C		337.6	
Power Dissipation R <sub>0</sub> JC (Note 1)		T <sub>C</sub> = 25°C	$P_{D}$	294.6	W
		T <sub>C</sub> = 100°C		147.3	
Continuous Drain	Steady State	T <sub>A</sub> = 25°C	I <sub>D</sub>	62.2	Α
Current R <sub>θJA</sub> (Notes 1, 2, 3)		T <sub>A</sub> = 100°C		44.0	
Power Dissipation		T <sub>A</sub> = 25°C	$P_{D}$	5.0	W
R <sub>θJA</sub> (Notes 1, 2)		T <sub>A</sub> = 100°C		2.5	
Pulsed Drain Current	$T_A = 25$	°C, t <sub>p</sub> = 10 μs	I <sub>DM</sub>	900	Α
Operating Junction and Storage Temperature Range			T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C
Source Current (Body Diode)			IS	245.5	Α
Single Pulse Drain-to-Source Avalanche Energy (I <sub>L(pk)</sub> = 40 A)			E <sub>AS</sub>	1754	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			T <sub>L</sub>	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	0.5	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	30	


- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface-mounted on FR4 board using a 650 mm<sup>2</sup>, 2 oz. Cu pad.
- 3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.




#### ON Semiconductor®

#### www.onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
60 V	0.68 m $\Omega$ @ 10 V	477.4
	0.90 mΩ @ 4.5 V	477 A



**N-CHANNEL MOSFET** 



### **MARKING DIAGRAM**



A = Assembly Location

WL = Wafer Lot Code

Y = Year Code

WW = Work Week Code

## **ORDERING INFORMATION**

See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

# **ELECTRICAL CHARACTERISTICS** ( $T_J = 25^{\circ}C$ unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit	
OFF CHARACTERISTICS	•					•		
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		60			V	
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> / T <sub>J</sub>	I <sub>D</sub> = 250 μA, ref to 25°C			16.8		mV/°C	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>GS</sub> = 0 V,	T <sub>J</sub> = 25°C			10		
		V <sub>DS</sub> = 60 V	T <sub>J</sub> = 125°C			250	μΑ	
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = 20 V				100	nA	
ON CHARACTERISTICS (Note 4)								
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D =$	= 250 μΑ	1.0		2.5	V	
Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>	I <sub>D</sub> = 250 μA, re	f to 25°C		-5.63		mV/°C	
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V	I <sub>D</sub> = 50 A		0.52	0.68		
		V <sub>GS</sub> = 4.5 V	I <sub>D</sub> = 50 A		0.69	0.90	mΩ	
Forward Transconductance	9FS	V <sub>DS</sub> =15 V, I <sub>D</sub> = 50 A			310		S	
CHARGES, CAPACITANCES & GATE RE	SISTANCE					•		
Input Capacitance	C <sub>ISS</sub>				16200			
Output Capacitance	C <sub>OSS</sub>	V <sub>GS</sub> = 0 V, f = 1 MH:	z, V <sub>DS</sub> = 25 V		8490		pF	
Reverse Transfer Capacitance	C <sub>RSS</sub>				270		1	
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 4.5 V, V <sub>DS</sub> = 30 V; I <sub>D</sub> = 50 A			103			
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 30 V; I <sub>D</sub> = 50 A			225		1	
Threshold Gate Charge	Q <sub>G(TH)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 30 V; I <sub>D</sub> = 50 A			21.6		nC	
Gate-to-Source Charge	Q <sub>GS</sub>				36.5			
Gate-to-Drain Charge	$Q_{GD}$				20.7			
Plateau Voltage	V <sub>GP</sub>				2.46		V	
SWITCHING CHARACTERISTICS (Note 5	)					•		
Turn-On Delay Time	t <sub>d(ON)</sub>				35.3			
Rise Time	t <sub>r</sub>	$V_{GS}$ = 10 V, $V_{DS}$	a = 30 V.		26.3		ns	
Turn-Off Delay Time	t <sub>d(OFF)</sub>	I <sub>D</sub> = 50 A, R <sub>G</sub>	= 2.5 Ω		263			
Fall Time	t <sub>f</sub>				60.7		1	
DRAIN-SOURCE DIODE CHARACTERIST	TICS	•			•		•	
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V,	T <sub>J</sub> = 25°C		0.67	1.2		
		$I_{S} = 50 \text{ A}$	T <sub>J</sub> = 125°C		0.59		V	
Reverse Recovery Time	t <sub>RR</sub>	V <sub>GS</sub> = 0 V, dIS/dt = 100 A/μs, I <sub>S</sub> = 50 A			115			
Charge Time	ta				70		ns	
Discharge Time	t <sub>b</sub>				45		1	
Reverse Recovery Charge	Q <sub>RR</sub>				307		nC	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperatures.

#### **TYPICAL CHARACTERISTICS**




Figure 5. On–Resistance Variation with Temperature

Figure 6. Drain-to-Source Leakage Current vs. Voltage

#### **TYPICAL CHARACTERISTICS**




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in Avalanche

#### **TYPICAL CHARACTERISTICS**




Figure 13. Thermal Characteristics


#### **DEVICE ORDERING INFORMATION**

Device	Marking	Package	Shipping <sup>†</sup>
NVMTS0D7N06CLTXG	0D7N06CL	DFNW8 (Pb-Free)	3000 / Tape & Reel


<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### **PACKAGE DIMENSIONS**

#### DFNW8 8.3x8.4, 2P CASE 507AP **ISSUE B**



# FRONT VIEW 8.40



## **RECOMMENDED LAND PATTERN\***

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

- WELL AS THE TERMINALS.
- 4. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH,
- 4. DIMENSIONS DI AND ET DO NOT INCLUDE MOLES FEACH, PROTRUSIONS, OR GATE BURRS.

  5. SEATING PLANE IS DEFINED BY THE TERMINALS.

  "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

DIM	MILLIMETERS				
Diw	MIN.	NOM.	MAX.		
Α	1.00	1.10	1.20		
A1	0.00		0.05		
b	0.90	1.00	1.10		
b1	0.43	0.53	0.63		
O	0.23	0.28	0.33		
О	8.20	8.30	8.40		
D1	7.90	8.00	8.10		
D2	6.80	6.90	7.00		
D3	6.90	7.00	7.10		
П	8.30	8.40	8.50		
E1	7.80	7.90	8.00		
E2	5.24	5.34	5.44		
E3	0.25	0.35	0.45		
е	2.00 BSC				
e/2	1.00 BSC				
e1	2.70 BSC				
e1/2	1.35 BSC				
K	1.50	1.57	1.70		
L	0.64	0.74	0.84		
L1	0.67	0.77	0.87		
Φ	0°		12°		

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.nsemi.com/site/pdf/Patent-Marking.pdf">www.nsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, Buyer shall indemnify

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT
North American Technical Support:
Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative