


## Vishay General Semiconductor

# Enhanced isoCink+TM Bridge Rectifiers



\*Tested to UL standard for safety electrically isolated semiconductor devices. UL 1557 4th edition.

Dielectric tested to maximum case, storage and junction temperature to 150  $^{\circ}\text{C}$  to withstand 1500 V.

Epoxy meets UL 94 V-0 flammability rating.

PRIMARY CHARACTERISTICS					
Package	PB				
I <sub>F(AV)</sub> 40 A					
V <sub>RRM</sub>	600 V, 800 V, 1000 V				
I <sub>FSM</sub>	400 A				
I <sub>R</sub>	10 μΑ				
V <sub>F</sub> at I <sub>F</sub> = 20 A	0.94 V				
T <sub>J</sub> max.	150 °C				
Circuit configuration	In-line				

#### **FEATURES**

 UL recognition file number E312394 (QQQX2) UL 1557 (see \*)



Enhanced high-current density single in-line package

RoHS

Superior thermal conductivity

- · Glass passivated chip junction
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912">www.vishay.com/doc?99912</a>

#### **TYPICAL APPLICATIONS**

General purpose use in AC/DC bridge full wave rectification for switching power supply, home appliances and white-goods applications.

#### **MECHANICAL DATA**

Case: PB

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: As marked on body

**Mounting Torque:** 10 cm-kg (8.8 inches-lbs) max. **Recommended Torque:** 5.7 cm-kg (5 inches-lbs)

MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)						
PARAMETER		SYMBOL	PB4006	PB4008	PB4010	UNIT
Maximum repetitive peak reverse voltage		$V_{RRM}$	600	800	1000	V
Average rectified forward current (Fig. 1, 2)	$T_{\rm C} = 87  ^{\circ}{\rm C}^{(1)}$ $T_{\rm A} = 25  ^{\circ}{\rm C}^{(2)}$	1	40 4.4		A	
	$T_A = 25  ^{\circ}C^{(2)}$	I <sub>O</sub>				
Non-repetitive peak forward surge current 8.3 ms single sine-wave, $T_J = 25$ °C $I_{FSM}$		400		А		
Rating for fusing (t < 8.3 ms) T <sub>J</sub> = 25 °C		I <sup>2</sup> t	<sup>2</sup> t 664		A <sup>2</sup> s	
Operating junction and storage temperature rar	nge	T <sub>J</sub> , T <sub>STG</sub>		-55 to +150		°C

#### Notes

- (1) With heatsink
- (2) Without heatsink, free air

# PB4006, PB4008, PB4010

# Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)							
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT	
Maximum instantaneous forward voltage per diode (1)	I <sub>F</sub> = 20 A	T <sub>A</sub> = 25 °C	V <sub>F</sub>	1.01	1.10	V	
		T <sub>A</sub> = 125 °C		0.94	1.00	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	
Reverse current per diode (2)		T <sub>A</sub> = 25 °C	1	=	10		
		T <sub>A</sub> = 125 °C	IR	130	500	μA	
Typical junction capacitance per diode	4.0 V, 1 MHz	,	CJ	120	=	pF	

#### Notes

 $^{(1)}\,$  Pulse test: 300  $\mu s$  pulse width, 1 % duty cycle

(2) Pulse test: 10 ms pulse width

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	PB4006	PB4008	PB4010	UNIT	
Typical thermal resistance	R <sub>0</sub> JC (1)	0.75			°C/W	
	R <sub>0JA</sub> (2)	18			C/VV	

#### Notes

(1) With 60 W air cooled heatsink

(2) Without heatsink, free air

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
PB4006-E3/45	7.53	45	20	Tube		

# Vishay General Semiconductor

### RATINGS AND CHARACTERISTICS CURVES (TA = 25 °C unless otherwise noted)




Fig. 1 - Derating Curve Output Rectified Current




Fig. 2 - Forward Current Derating Curve




Fig. 3 - Forward Power Dissipation




Fig. 4 - Typical Forward Characteristics Per Diode




Fig. 5 - Typical Reverse Characteristics Per Diode






Fig. 6 - Typical Junction Capacitance Per Diode

## Vishay General Semiconductor


### PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

### Case Type PB





#### **Back Side View**





## **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.