

General Description

The LP4059 is a complete constant-current/constant- voltage linear charger for single cell lithium-ion batteries. Its TDFN-6/SOT23-6 package and low external component count make the LP4059 ideally suited for portable applications. Furthermore, the LP4059 is specifically designed to work within USB power specifications. No external sense resistor is needed, and no blocking diode is required due to the internal MOSFET architecture. Thermal feedback regulates the charge current to limit the die temperature during high power operation or high ambient temperature. The charge voltage is fixed at 4.2V, and the charge current can be programmed externally with a single resistor. The LP4059 automatically terminates the charge cycle when the charge current drops to 1/10th the programmed value after the final float voltage is reached. The input current will be less than 1µA at this time. When the input supply (wall adapter or USB supply) is removed, the LP4059 automatically enters a low current state, dropping the battery drain current to less than 1µA. Other features include charge current monitor, automatic recharge and a status pin to indicate charge termination.

LowPowerSemi 微源半導體

Features

- Programmable Charge Current Up to 800mA
- Shutdown Current less than 1µA
- No MOSFET, Sense Resistor or Blocking Diode Required
- Protection of Reverse Connection of Battery
- Constant-Current/Constant-Voltage Operation with Thermal Regulation to Maximize Charge Rate Without Risk of Overheating
- 4.2V Charge Voltage with ± 1% Accuracy
- Automatic Recharge
- 2.9V Trickle Charge Threshold
- 3/10C Charge Termination


Applications

- Portable Media Players/MP3 players
- ♦ Cellular and Smart mobile phone
- ♦ PDA/DSC
- Bluetooth Applications

Marking Information


Part	Marking	Package	Shipping	
LP4059QVF	LP4059	TDFN-6	4K/REEL	
LP4059B6F	YWX	SOT23-6	3K/REEL	
Marking indication:				
Y:Production year W:Production week X:Production batch.				

Order Information






Typical Application Circuit



Functional Pin Description



Pin Description

Pin		Nome	Description	
SOT23-6	DFN-6	Name	Description	
			Charge Current Program and Charge Current Monitor Pin. The charge current is programmed by	
6	1	PROG	connecting a 1% resistor, RPROG, to ground. When charging in constant-current mode, this pin	
0	I	FROG	servos to 1V. In all modes, the voltage on this pin can be used to measure the charge current	
			using the following formula: IBAT=1000/RPROG	
2	2	GND	Ground.	
		VCC	Positive Input Supply Voltage. Provide power to the charger. VCC can range from 4.5V to 6.5V	
4	3		and should be bypassed with at least a $1\mu F$ capacitor. When VCC drops to within 30mV of the	
			BAT pin voltage, the LP4059 enters shutdown mode, dropping I_{BAT} to less than 1µA.	
3 4 BAT		BAT	Charge Current Output. Provides charge current to the battery and regulates the final float voltage	
3	4	DAT	to 4.2V. An internal precision resistor divider from this pin sets the float voltage.	
5	5	SLP	Connect to the I/O port of the MCU and connect a 1Mohm resistor to the BAT pin.	
	1 6		Open-Drain Charge Status Output. When the battery is charging, the CHRG pin is pulled low by an	
1			internal N-channel MOSFET. When the LP4059 detects an under voltage lockout condition or	
charge complete, CHRG is forced high impedance.		charge complete, CHRG is forced high impedance.		



Absolute Maximum Ratings Note 1

\diamond	Input to GND(VCC)	0.3V to 10V
\diamond	BAT to GND	5V to 8V
∻	VCC to BAT	8V
\diamond	Other Pin to GND	0.3V to 6V
\diamond	BAT Pin Current	800mA
\diamond	BAT Short-circuit Duration	Continuous
\diamond	Maximum Junction Temperature	150°C
\diamond	Operating Ambient Temperature Range (T _A)	20°C to 85°C
∻	Storage Temperature	65°C to 165°C
∻	Maximum Soldering Temperature (at leads, 10 sec)	260°C

Note 1. Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Thermal Information

\diamond	Maximum Power Dissipation (TDFN-6, PD, T _A =25°C) 1.2	W
\diamond	Thermal Resistance (TDFN-6, θJA) 95°C/	W
	L P Semi	

ESD Susceptibility

\diamond	HBM(Human Body Mode)		/
\diamond	MM(Machine Mode)	200\	/



Electrical Characteristics

(T_A=25°C, V_{CC}=5V, LP4059B5F, the specifications which apply over the full operating temperature range, unless otherwise noted.)

Symbol	Parameter	Condition	Min	Тур	Max	Units	
Vcc	Adapter/USB Voltage Range		4.5	5	6.5	V	
		Standby Mode (Charge Terminated)		50			
lcc	Input Supply Current	SLP=High		1		μA	
V _{FLOAT}	Regulated Output (Float) Voltage		4.158	4.2	4.242	V	
		RPROG=10k, Current Mode	80	100	120		
		R _{PROG} =2k, Current Mode	400	500	600		
Іват	BAT Pin Current	Reverse Current, VBAT=-4.2V		-1			
IDAT	DATTINGUIGH	Standby Mode, V _{BAT} =4.2V Shutdown Mode (R _{PROG} NC) Sleep Mode, V _{CC} =0V		1		μA	
V _{TRIKL}	Trickle Charge Threshold Voltage	R _{PROG} =10k, V _{BAT} Rising		2.9		V	
Itrikl	Trickle Charge Current	VBAT < VTRIKL		20		mA	
VTRHYS	Trickle Charge Hysteresis Voltage	R _{PROG} =10k		180		mV	
Vuv	Vcc Undervoltage Lockout Threshold	From Vcc Low to High		3.8		V	
VUVHYS	V _{CC} Undervoltage Lockout Hysteresis			500		mV	
VASD	Vcc-VBAT Lockout Threshold Voltage			100		mV	
Iterm	Termination Current Threshold	RPROG=10k RPROG=2k	導	30 30		%Іват	
VPROG	PROG Pin Voltage	RPROG=10k, Charge Mode		1		V	
VCHRG	CHRG Pin Output Low Voltage	I _{CHRG} =5mA			0.6	V	
I _{CHRG}	CHRG Pin Weak Pull-Down Current	V _{CHRG} =5V			5	uA	
ΔV_{RECHRG}	Recharge Battery Threshold Voltage	Vfloat-Vrechrg		150		mV	
TLIM	Junction Temperature in Constant Temperature Mode			150		°C	
Ron	Power FET "ON" Resistance (Between VCC and BAT)			500		mΩ	
tss	Soft-Start Time	IBAT=0 to IBAT=800/RPROG		200		μs	

Application Information

The LP4059 is a single cell lithium-ion battery charger using a constant-current/constant-voltage algorithm. It can deliver up to 800mA of charge current (using a good thermal PCB layout) with a final float voltage accuracy of \pm 1%. The LP4059 includes an internal P-channel power MOSFET and thermal regulation circuitry. No blocking diode or external current sense resistor is required; thus, the basic charger circuit requires only three external components. Furthermore, the LP4059 is capable of operating from a USB power source.

Normal Charge Cycle

P Semi

A charge cycle begins when the voltage at the VCC pin rises above the UVLO threshold level and a 1% program resistor is connected from the PROG pin to ground or when a battery is connected to the charger output. If the BAT pin is less than 2.9V, the charger enters trickle charge mode to bring the battery voltage up to a safe level for full current charging.

When the BAT pin voltage rises above 2.9V, the charger enters constant-current mode, where the programmed charge current is supplied to the battery. When the BAT pin approaches the final float voltage (4.2V), the LP4059 enters constant-voltage mode and the charge current begins to decrease. The charge cycle ends when the charge current drops to 1/10 of the programmed value.

Programming Charge Current

The charge current is programmed using a single resistor from the PROG pin to ground. The battery charge current is 1000 times the current out of the PROG pin. The program resistor and the charge current are calculated using the following equations:

R_{PROG}=1000V/I_{BAT}

I_{BAT}=1000V/R_{PROG}

The charge current out of the BAT pin can be determined at any time by monitoring the PROG pin voltage using the following equation:

IBAT=VPROG/RPROG×1000

Charge Termination

A charge cycle is terminated when the charge current falls to 1/10th the ISET rammed value after the final float voltage is reached. This condition is detected by using an internal, filtered comparator to monitor the ISET pin. When the ISET pin voltage falls below 200mV for longer than t_{TERM} (typically 1ms), charging is terminated. The charge current is latched off and the LP4059 enters standby mode, where the input supply current drops to 200µA. In this state, all loads on the BAT pin must be supplied by the battery. (Note: C/10 termination is disabled in trickle charging and thermal limiting modes).

Charge Status Indicator (CHRG&FULL)

The charge status output has two different states: strong pull-down (~5mA) and high impedance. The strong pull-down state indicates that the LP4059 is in a charge cycle. Once the charge cycle has terminated, the pin state is determined by under voltage lockout conditions. High impedance indicates that the charge cycle complete or the LP4059 is in under voltage lockout mode: either V_{CC} is less than 100mV above the BAT pin voltage or insufficient voltage is applied to the VCC pin. A microprocessor can be used to distinguish between these two states.

Function	CHRG	
Charging	Low Level	
Charge Complete	High Resistance	

Charge Current

An internal thermal feedback loop reduces the programmed charge current if the die temperature attempts to rise above a preset value of approximately 150°C. This feature protects the LP4059 from excessive temperature and allows the user to push the limits of the power handling capability of a given circuit board without risk of damaging the LP4059. The charge current can be set according to typical (not worst-case) ambient temperature with the assurance that the charger will automatically reduce the current in worst-case conditions.





Stability Considerations

The constant-voltage mode feedback loop is stable without an output capacitor provided a battery is connected to the charger output. With no battery present, an output capacitor is recommended to reduce ripple voltage. When using high value, low ESR ceramic capacitors, it is recommended to add a 1 Ω resistor in series with the capacitor. No series resistor is needed if tantalum capacitors are used.

Manual Shutdown

At any point in the charge cycle, the LP4059 can be put into shutdown mode by removing R_{PROG} . This reduces the battery drain current to less than 1µA. A new charge cycle can be initiated by reconnecting the program resistor. The CHRG pin is in a high impedance state if the LP4059 is in under voltage lockout mode: either V_{CC} is within 100mV of the BAT pin voltage or insufficient voltage is applied to the VCC pin.

Automatic Recharge

Once the charge cycle is terminated, the LP4059 continuously monitors the voltage on the BAT pin using a comparator with a 2ms filter time (t_{RECHRG}). A charge cycle restarts when the battery voltage falls below 4.05V (which corresponds to approximately 80% to 90% battery capacity). This ensures that the battery is kept at or near a fully charged condition and eliminates the need for periodic charge cycle initiations. CHRG output enters a strong pull-down state during recharge cycles.

Under voltage Lockout (UVLO)

An internal under voltage lockout circuit monitors the input voltage and keeps the charger in shutdown mode until V_{CC} rises above the under voltage lockout threshold .The UVLO circuit has a built-in hysteresis of 500mV. Furthermore, to protect against reverse current in the power MOSFET, the UVLO circuit keeps the charger in shutdown mode if V_{CC} falls to within 30mV of the battery voltage. If the UVLO comparator is tripped, the charger will not come out of shutdown mode until V_{CC} raises 100mV above the battery voltage.

Power Dissipation (SOT23-5)

The conditions that cause the LP4059 to reduce charge current through thermal feedback can be approximated by considering the power dissipated in the IC. Nearly all of this power dissipation is generated by the internal MOSFET—this is calculated to be approximately:

PD=(VCC-VBAT)×IBAT

Where PD is the power dissipated, VCC is the input supply voltage, VBAT is the battery voltage and IBAT is the charge current. The approximate ambient temperature at which the thermal feedback begins to protect the IC is:

VCC Bypass Capacitor

Many types of capacitors can be used for input bypassing; however, caution must be exercised when using multilayer ceramic capacitors. Because of the self-resonant and high Q characteristics of some types of ceramic capacitors, high voltage transients can be generated under some start-up conditions, such as connecting the charger input to a live power source .Adding a 1.5Ω resistor in series with an X5R ceramic capacitor will minimize start-up voltage transients.

Intelligent Charge Control

The LP4059 includes an intelligent charge control logic(SLP) that is connected to BAT through a $1M\Omega$ pull-up resistor. If the I/O interface connected to the SLP pin is in a high-impedance state, a charge cycle restarts when the battery voltage below 3.4V. When the battery voltage rises than 3.6V, the chip will stop charging. Controlling the SLP through an external I/O output signal can turn the chip on/off. When the SLP is in a low-level state, the chip will continue to charge. When the SLP is in a high-level or high-impedance state, chip enters standby mode. This reduces the battery drain current to less than 1µA and the supply current to less than 1µA.



Layout Considerations

For the main current paths as indicated in bold lines, keep their traces short and wide.

Put the input and output capacitor as close as possible to the device pins (VCC, BAT and GND).

Connect all analog grounds to a command node and then connect the command node to the power ground behind the output capacitors





D2

Nd

h

1

2

BOTTOM VIEW

E2

К


b

-1

Packaging Information

LP4059-00

TDFN-6




Al

SYMBOL	MILLIMETER			
14 2122	MIN NOM		MAX	
Α	0. 70	0.75	0.80	
A1	0	0.02	0.05	
b	0.25	0.30	0.35	
с	0.18	0.20	0.25	
D	1.90	2.00	2.10	
D2	1.50	1.60	1.70	
е	0.65 BSC			
Nd		1.30BSC		
Е	1.90	2.00	2.10	
E2	0.90	1.00	1.10	
К	0. 20	-	-	
L	0.20	0.25	0.30	
h	0.15	0.20	0.25	
SIZE OF L/F (MIL)	69X47			









L P Semi

Symbol	Dimensions In Millimeters		Dimensions In Inches	
Symbol	Min	Max	Min	Мах
А	0.889	1.295	0.031	0.051
A1	0.000	0.152	0.000	0.006
В	1.397	1.803	0.055	0.071
b	0.250	0.560	0.010	0.022
С	2.591	2.997	0.102	0.118
D	2.692	3.099	0.106	0.122
е	0.838	1.041	0.033	0.041
Н	0.080	0.254	0.003	0.010
L	0.300	0.610	0.012	0.024