

MLG1005S2N4BT000









Applications	Commercial Grade		
Feature	Multilayer Non-Mag Core Non-Magnetic Core (Dielectric Ceramic)		
Series Type	MLG		
Status	Production		
Brand	TDK		



Size		
Length(L)	1.00mm ±0.05mm	
Width(W)	0.50mm ±0.05mm	
Thickness Height	0.50mm ±0.05mm	
Recommended Land Pattern (A)	0.50mm Nom.	
Recommended Land Pattern (B)	0.40mm Nom.	
Recommended Land Pattern (C)	0.50mm Nom.	

Electrical Characteristics		
Inductance	2.4nH ±0.1nH at 100MHz	
Rated Current	800mA	
DC Resistance [Typ.]	80mΩ	
DC Resistance [Max.]	150mΩ	
Self Resonant Frequency [Min.]	7GHz	
Self Resonant Frequency [Typ.]	8.2GHz	
Q [Min.]	7 at 100MHz	
Q [Typ.]	11 at 100MHz	

Other			
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C		
Coldaring Mathad	Reflow		
Soldering Method	Iron Soldering		
AEC-Q200	No		
Packing	Punched (Paper)Taping [180mm Reel]		
Package Quantity	10000pcs		
Weight	0.001g		

[!] Images are for reference only and show exemplary products. ! This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.



MLG1005S2N4BT000













Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)









 $^{! \} Images \ are \ for \ reference \ only \ and \ show \ exemplary \ products. \\$

[!] This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.



MLG1005S2N4BT000











Associated Images





[!] Images are for reference only and show exemplary products. ! This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.