

# 300mA, Low Noise High PSRR LDO Regulator

#### **Description**

The FP6185 is a low dropout, low noise, high PSRR, very low quiescent current positive linear regulator. The FP6185 can supply 300mA output current with low dropout voltage at about 400mV that optimized for battery-powered systems or portable wireless devices such as mobile phones. The shutdown function can provide remote control for the external signal to decide the on/off state of FP6185 that consumes less than 0.1µA during shutdown mode.

The FP6185 regulator is able to operate with output capacitors as small as  $1\mu F$  for stability. Other than the current limit protection, FP6185 also offers the on chip thermal shutdown feature providing protection against overload or any condition when the ambient temperature exceeds the maximum junction temperature.

The FP6185 offers high precision output voltage of  $\pm 2\%$ . The FP6185 is available in SOT-23-5 package which features small size.

#### **Features**

- Low V<sub>IN</sub> and Wide V<sub>IN</sub> Range: 2V to 5.5V
- Output Current 300mA\*
- ±2% Output Voltage Accuracy
- Output Noise 65µVrms from 10Hz to 100kHz
- Vout Fixed 1.0V to 3.3V
- Low Dropout Voltage of 400mV at 300mA
- Ripple Rejection 75dB at 1KHz
- Very Low Quiescent Current at 35µA
- Needs Only 1µF Capacitor for Stability
- Thermal Shutdown Protection
- Current Limit Protection
- SOT-23-5 Package
- RoHS Compliant
- \*
- 1. Attention should be paid to the power dissipation of the package when the output current is large.

#### **Applications**

- PDAs, Mobile phones, GPS, Smartphones
- Wireless Handsets, Wireless LAN, Bluetooth®, Zigbee®
- Portable Medical Equipment
- Other Battery Powered Applications

FP6185-Preliminary 0.3-JUN-2017



### **Pin Assignment**

S5 Package (SOT-23-5)





Figure 1. Pin Assignment of FP6185

# **Ordering Information**



#### **Marking Information**

Part Number	Product Code
FP6185-11S5	FU4
FP6185-12S5	FD8
FP6185-15S5	FD9
FP6185-18S5	FE1
FP6185-25S5	FU5
FP6185-27S5	FU6
FP6185-28S5	FE3
FP6185-29S5	FE2
FP6185-30S5	FU7
FP6185-33S5	FE4

Note: Please consult Fitipower sales office or authorized distributors for availability of special output voltages.



# **Typical Application Circuit**




Figure 2. Typical Application Circuit of FP6185

Note: To prevent oscillation, it is recommended to use minimum  $1\mu F$  X7R or X5R dielectric capacitors if ceramics are used as input/output capacitors.

# **Functional Pin Description**

Pin Name	Pin No.	Pin Function
VIN	1	Power is supplied to this device from this pin which is required an input filter capacitor. In general, the input capacitor in the range of 1µF to 10µF is sufficient.
GND	2	Common ground pin.
SHDN	3	Pull this pin high to enable IC, pull this pin low to shutdown IC. Floating this pin will be shutdown due to the built-in pull-low resistor.
NC	4	No connection.
VOUT	5	The FP6185 is stable with an output capacitor 1µF or greater. The larger output capacitor will be required for application with larger load transients. The large output capacitor could reduce output noise, improve stability and PSRR.

### **Block Diagram**




Figure 3. Block Diagram of FP6185



# Absolute Maximum Ratings (Note 1)

Supply Voltage V <sub>IN</sub>	-0.3V to +6.5V					
• EN Voltage V <sub>EN</sub>	-0.3V to V <sub>IN</sub> +0.3V					
<ul> <li>Power Dissipation @ T<sub>A</sub>=25°C &amp; T<sub>J</sub>=125°C (P<sub>D</sub>)</li> </ul>						
SOT-23-5	0.4W					
<ul> <li>Package Thermal Resistance (θ<sub>JA</sub>) (Note 2)</li> </ul>						
SOT-23-5	250°C/W					
<ul> <li>Package Thermal Resistance (θ<sub>JC</sub>)</li> </ul>						
SOT-23-5	130°C/W					
• Lead Temperature (Soldering, 10sec.)	+260°C					
• Junction Temperature (T <sub>J</sub> )	-40°C to +150°C					
• Storage Temperature (T <sub>STG</sub> )						
Note 1: Streeges havend this listed under "Absolute Maximum Patings" may cause permanent damage to the device						

Note 1: Stresses beyond this listed under "Absolute Maximum Ratings" may cause permanent damage to the device. Note 2:  $\theta_{JA}$  is measured at 25°C ambient with the component mounted on a high effective thermal conductivity 4-layer board of JEDEC-51-7. The thermal resistance greatly varies with layout, copper thickness, number of layers and PCB size.

### **Recommended Operating Conditions**

VIN Supply Voltage	+2V to +5.5V
● Output Current (I <sub>OUT</sub> )	0mA to 300mA
Operating Temperature Range (T <sub>OPR</sub> )	-40°C to +85°C
Operating Junction Temperature Range (T <sub>J</sub> )	-40°C to +125°C

FP6185-Preliminary 0.3-JUN-2017



# **Electrical Characteristics**

 $(V_{IN}\!\!=\!\!V_{OUT}\!\!+\!1V,\overline{SHDN} \text{ pin connected to } V_{IN},\,C_{IN}\!\!=\!\!1\mu\text{F},\,C_{OUT}\!\!=\!\!1\mu\text{F},\,T_{A}\!\!=\!\!25^{o}\text{C},\,\text{unless otherwise specified})$ 

Parameter	Symbol	Conditions		Min	Тур	Max	Unit
Input Voltage Range	Vin			2		5.5	V
Current Limit	I <sub>LIMIT</sub>	R <sub>Load</sub> =1Ω		320			mA
Quiescent Current	IQ	I <sub>OUT</sub> =0mA			35		μA
Standby Current	I <sub>STBY</sub>	SHDN Pin Co	onnected to GND		0.1	1	μA
Output Voltage Accuracy	$\Delta V_{OUT}$	I <sub>OUT</sub> =1mA		-2		+2	%
			V <sub>OUT</sub> =1.2V		800	1200	
			V <sub>OUT</sub> =1.5V		600	900	
			V <sub>OUT</sub> =1.8V		475	700	
Dropout Voltage (Note 3)	$V_{DROP}$	I <sub>OUT</sub> =150mA	V <sub>OUT</sub> =2.5V		275	400	mV
			V <sub>OUT</sub> =2.7V		250	350	
			V <sub>OUT</sub> =3.0V		225	325	
			V <sub>OUT</sub> =3.3V		200	300	
	Vdrop		V <sub>OUT</sub> =1.2V		1550	2300	m∨
			V <sub>OUT</sub> =1.5V		950	1400	
		I <sub>OUT</sub> =300mA	V <sub>OUT</sub> =1.8V		750	1100	
Dropout Voltage (Note 3)			V <sub>OUT</sub> =2.5V		550	800	
			V <sub>OUT</sub> =2.7V		500	700	
			V <sub>OUT</sub> =3.0V		450	650	
			V <sub>OUT</sub> =3.3V		400	600	
Line Regulation	$\Delta V_{LINE}$	I <sub>OUT</sub> =1mA, V <sub>IN</sub>	I <sub>OUT</sub> =1mA, V <sub>IN</sub> =V <sub>OUT</sub> +1V to 5V		1	8	mV
Load Regulation (Note 4)	$\Delta V_{LOAD}$	I <sub>OUT</sub> =0mA to 3			6	30	mV
Ripple Rejection (Note 5)	PSRR	$V_{IN}=V_{OUT}+1V_{DC}+0.2V_{P-P(AC)},$ $f_{RIPPLE}=1KHz,V_{OUT}\geq1.8V,$ $I_{OUT}=30mA$			75		dB
Output Noise Voltage (Note 5)	V <sub>NOISE</sub>	C <sub>OUT</sub> =1µF, I <sub>OUT</sub> =0mA BW=10Hz ~ 100KHz			65		$\mu V_{RMS}$
Temperature Coefficient	TC	I <sub>OUT</sub> =1mA, V <sub>IN</sub> =5V			100		ppm/ºC
Thermal Shutdown Threshold	T <sub>SD</sub>				145		°C
(Note 5)	$\DeltaT_{SD}$	Hysteresis			25		°C
Output Discharge Resistance	R <sub>DIS</sub>	V <sub>SHDN</sub> =0V			60		Ω
SHDN Pin Current	I <sub>SHDN</sub>	V <sub>SHDN</sub> =2.5V			0.3		uA

FP6185-Preliminary 0.3-JUN-2017 **5** 



# **Electrical Characteristics (Continued)**

 $(V_{IN}\!\!=\!\!V_{OUT}\!\!+\!1V,\overline{SHDN} \text{ pin connected to } V_{IN},\,C_{IN}\!\!=\!\!1\mu\text{F},\,C_{OUT}\!\!=\!\!1\mu\text{F},\,T_{A}\!\!=\!\!25^{o}\text{C},\,\text{unless otherwise specified})$ 

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
SHDN Pin Threshold	$V_{\overline{SHDN}(ON)}$	Start-up	1.0			V
	V <sub>SHDN(OFF)</sub>	Shutdown			0.4	V

Note 3: The dropout voltage is defined as  $V_{IN}-V_{OUT}$ , which is measured when  $V_{OUT}$  drops 2% of its normal value with the specified output current.


Note 4: Load regulation and dropout voltage are measured at a constant junction temperature by using a 40ms low duty cycle current pulse.

Note 5: Guarantee by design.



### **Typical Performance Curves**

 $V_{IN}\!\!=\!\!V_{OUT}\!\!+\!1V, \;\; \overline{SHDN} \;\; \text{pin connected to} \;\; V_{IN}, \;\; C_{IN}\!\!=\!\!1\mu\text{F}, \;\; C_{OUT}\!\!=\!\!1\mu\text{F}, \;\; T_{A}\!\!=\!\!25^{\circ}\text{C}, \;\; \text{unless otherwise specified}$ 







Figure 4. Turn ON Waveform

Figure 5. Turn OFF Waveform







Figure 6. Turn ON Waveform

Figure 7. Turn OFF Waveform






Figure 8. Load Transient Response

Figure 9. Load Transient Response



# **Typical Performance Curves (Continued)**

 $V_{IN}\!\!=\!\!V_{OUT}\!\!+\!1V, \;\; \overline{SHDN} \;\; \text{pin connected to} \;\; V_{IN}, \;\; C_{IN}\!\!=\!\!1\mu\text{F}, \;\; C_{OUT}\!\!=\!\!1\mu\text{F}, \;\; T_{A}\!\!=\!\!25^{o}\text{C}, \; \text{unless otherwise specified}$ 




Figure 10. Line Transient Response




Figure 11. Line Transient Response




Figure 12. Output Voltage vs. Input Voltage




Figure 13. Output Voltage vs. Input Voltage




Figure 14. Output Voltage vs. Output Current




Figure 15. Output Voltage vs. Output Current



# **Typical Performance Curves (Continued)**

 $V_{IN}\!\!=\!\!V_{OUT}\!\!+\!1V, \;\; \overline{SHDN} \;\; \text{pin connected to} \;\; V_{IN}, \;\; C_{IN}\!\!=\!\!1\mu\text{F}, \;\; C_{OUT}\!\!=\!\!1\mu\text{F}, \;\; T_{A}\!\!=\!\!25^{o}\text{C}, \; \text{unless otherwise specified}$ 




Figure 16. Dropout Voltage vs. Output Current




Figure 17. Dropout Voltage vs. Output Current




Figure 18. Output Voltage vs. Temperature




Figure 19. Output Voltage vs. Temperature




Figure 20. Quiescent Current vs. Temperature




Figure 21. Quiescent Current vs. Temperature



# **Typical Performance Curves (Continued)**

 $V_{IN} = V_{OUT} + 1V, \quad \overline{SHDN} \ \ pin \ connected \ to \ V_{IN}, \ C_{IN} = 1 \mu F, \ C_{OUT} = 1 \mu F, \ T_A = 25^{o}C, \ unless \ otherwise \ specified$ 




Figure 22. Shutdown Current vs. Temperature




Figure 24. Output Noise Voltage




Figure 23. Shutdown Current vs. Temperature




Figure 25. Output Noise Voltage

11



#### **Application Information**

The FP6185 is a low dropout linear regulator that could provide 300mA output current at dropout voltage about 400mV. Current limit and on chip thermal shutdown features provide protection against any combination of overload or ambient temperature that could exceed maximum junction temperature.

#### 1. Output and Input Capacitor

The FP6185 regulator is designed to be stable with a wide range of output capacitors. The ESR of the output capacitor affects stability. Larger value of the output capacitor decreases the peak deviations and improves transient response for larger current changes.

The capacitor types (aluminum, ceramic, and tantalum) have different characterizations such as temperature and voltage coefficients. All ceramic capacitors are manufactured with a variety of dielectrics, each with different behavior across temperature and applications. Common dielectrics used are X5R, X7R and Y5V. It is recommended to use  $1\mu F$  to  $10\mu F$  X5R or X7R dielectric ceramic capacitors with  $30m\Omega$  to  $50m\Omega$  ESR range between device outputs and ground for stability. The FP6185 is designed to be stable with low ESR ceramic capacitors and higher values of capacitors and ESR could improve output stability. The ESR of output capacitor is very important because it generates a zero to provide phase lead for loop stability.

There are no requirements for the ESR on the input capacitor, but its voltage and temperature coefficient have to be considered for device application environment.

#### 2. Protection Features

In order to prevent overloading or thermal condition from damaging the device, FP6185 has internal thermal and current limiting functions designed to protect the device. It will rapidly shut off PMOS pass element during over-temperature condition.

#### 3. Thermal Consideration

The power handling capability of the device will be limited by allowable operation junction temperature (125°C). The power dissipated by the device will be estimated by  $P_D=I_{OUT}\times(V_{IN}-V_{OUT})$ . The power dissipation should be lower than the maximum power dissipation listed in "Absolute Maximum Ratings" section.

#### 4. Shutdown Operation


The FP6185 is shutdown by pulling the SHDN input low, and turned on by driving the SHDN high. If SHDN pin floating, the FP6185 will shut down because SHDN pin has built-in a pull low resistor (refer to Block Diagram).


FP6185-Preliminary 0.3-JUN-2017



### **Outline Information**


SOT-23-5 Package (Unit: mm)







SYMBOLS	DIMENSION IN MILLIMETER				
UNIT	MIN	MAX			
Α	0.90	1.45			
A1	0.00	0.15			
A2	0.90	1.30			
В	0.30	0.50			
D	2.80	3.00			
E	2.60	3.00			
E1	1.50	1.70			
е	0.90	1.00			
e1	1.80	2.00			
L	0.30	0.60			
Note: Callernad Casas, ICDCC MO 470 C					

Note: Followed From JEDEC MO-178-C.



### **Carrier Dimensions**





Tape	Size	Pocket Pitch	Reel Size (A)		Reel Width	Empty Cavity	Units per Reel
(W1)	mm	(P) mm	in	mm	(W2) mm	Length mm	
8		4	7	180	8.4	300~1000	3,000

**Life Support Policy**Fitipower's products are not authorized for use as critical components in life support devices or other medical systems.