

#### **Features**

- ESD Protect for 1 Line with Unidirectional
- Provide ESD protection for the protected line to IEC 61000-4-2 (ESD) ±30kV (air/contact)
  IEC 61000-4-4 (EFT) 80A (5/50ns)
  IEC 61000-4-5 (Lightning) 4A (8/20μs)
  Cable Discharge Event (CDE)
- 0402 small DFN package saves board space
- Protect one I/O line or one power line
- Fast turn-on and Low clamping voltage
- For low operating voltage applications: 3.3V maximum
- Solid-state silicon-avalanche and active circuit triggering technology
- Green Part

## **Applications**

- Mobile Phones
- Hand Held Portable Applications
- Computer Interfaces Protection
- Microprocessors Protection
- Serial and Parallel Ports Protection
- Control Signal Lines Protection
- Power lines on PCB Protection
- Latchup Protection


## Description

AZ5013-01F is a design which includes a unidirectional surge rated clamping cell to protect one power line, or one control line, or one low speed data line in an electronic systems. The AZ5013-01F has been specifically designed to protect sensitive components which connected to power and control lines from over-voltage damage and latch-up caused by Electrostatic Discharging (ESD), Electrical Fast Transients (EFT), Lightning, and Cable Discharge Event (CDE).

AZ5013-01F is a unique design which includes proprietary clamping cell in a single package. During transient conditions, the proprietary clamping cell prevents over-voltage on the power line or control/data lines, protecting any downstream components.

AZ5013-01F may be used to meet the ESD immunity requirements of IEC 61000-4-2, Level 4 (±15kV air, ±8kV contact discharge)

# Circuit Diagram / Pin Configuration






## **SPECIFICATIONS**


ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	RATING	UNITS	
Peak Pulse Current (tp =8/20us)	I <sub>PP</sub>	4	А	
Operating Supply Voltage (pin-1 to pin-2)	$V_{DC}$	3.8	V	
ESD per IEC 61000-4-2 (Air)	V <sub>ESD</sub>	±30	kV	
ESD per IEC 61000-4-2 (Contact)		±30		
Lead Soldering Temperature	T <sub>SOL</sub>	260 (10 sec.)	°C	
Operating Temperature	T <sub>OP</sub>	-55 to +85	°C	
Storage Temperature	T <sub>STO</sub>	-55 to +150	$^{\circ}$	

ELECTRICAL CHARACTERISTICS						
PARAMETER	SYMBOL	CONDITIONS	MINI	TYP	MAX	UNITS
Reverse Stand-Off	$V_{RWM}$	T=25 °C.			3.3	V
Voltage	<b>V</b> RWM	1=25 C.			3.3	V
Reverse Leakage	1	V <sub>RWM</sub> = 3.3V, T=25 °C.			1	
Current	l <sub>Leak</sub>	V <sub>RWM</sub> = 3.3V, 1=23 C.			'	μΑ
Reverse	\/	1 4mA T 25 °C 4.5	4.5		6.5	V
Breakdown Voltage	$V_{BV}$	$I_{BV} = 1$ mA, T=25 °C.	4.5			
Forward Voltage	$V_{F}$	I <sub>F</sub> = 15mA, T=25°C.	0.6	0.85	1	٧
ESD Clamping	V <sub>ESD_CL</sub>	IEC 61000-4-2 +6kV, T=25 °C,		6.5		V
Voltage	V ESD_CL	Contact mode.		0.5		V
Channel Input	C <sub>IN</sub>	$V_R = 0V, f = 1MHz, T=25$ °C		55	65	рF
Capacitance	ŬN .	VR-0V,1-11VII IZ, 1-23 0		33	65	Ы



## **Typical Characteristics**







## **Applications Information**

The AZ5013-01F is designed to protect one line against System ESD/EFT/Lightning pulses by clamping them to an acceptable reference.

The usage of the AZ5013-01F is shown in Fig. 1. Protected lines, such as data lines, control lines, or power lines, are connected at pin 1. The pin 2 should be connected directly to a ground plane on the board. All path lengths connected to the pins of AZ5013-01F should be kept as short as possible to minimize parasitic inductance in the board traces.

In order to obtain enough suppression of ESD induced transient, good circuit board is critical. Thus, the following guidelines are recommended:

- Minimize the path length between the protected lines and the AZ5013-01F.
- Place the AZ5013-01F near the input terminals or connectors to restrict transient coupling.
- The ESD current return path to ground should be kept as short as possible.
- Use ground planes whenever possible.
- NEVER route critical signals near board edges and near the lines which the ESD transient easily injects to.




Fig. 1

Fig. 2 shows another simplified example of using AZ5013-01F to protect the control lines, low

speed data lines, and power lines from ESD transient stress.





Fig. 2




### **Mechanical Details**



Symbol	Millim	neters	Inches		
	min	max	min	max	
Α	0.95	1.05	0.037	0.041	
В	0.55	0.65	0.022	0.026	
С	0.41	0.50	0.016	0.020	
D	0.45		0.018		
E	0.20	0.30	0.008	0.012	
F	0.45	0.55	0.018	0.022	


#### LAND LAYOUT



#### Notes:

This LAND LAYOUT is for reference purposes only. Please consult your manufacturing partners to ensure your company's PCB design guidelines are met.

#### **MARKING CODE**



**Top View** 

Part Number	Marking Code
AZ5013-01F	4
(Green Part)	u

Note: Green means Pb-free, RoHS, and Halogen free compliant.



**Ordering Information** 

PN#	Material	Type	Reel size	MOQ	MOQ/internal box	MOQ/carton
AZ5013-01F.R7GR	Green	T/R	7 inch	12,000/reel	4 reel=48,000/box	6 box=288,000/carton

# **Revision History**

Revision	Modification Description			
Revision 2012/11/08	Preliminary Release.			
Revision 2013/01/08	Formal Release.			
Revision 2015/01/29	Update the Ordering Information.			