


Vishay Siliconix

Power MOSFET

PRODUCT SUMMARY				
V _{DS} (V)	- 100			
$R_{DS(on)}\left(\Omega\right)$	V _{GS} = - 10 V	0.60		
Q _g (Max.) (nC)	18			
Q _{gs} (nC)	3.0			
Q _{gd} (nC)	9.0			
Configuration	Single			



FEATURES

- Isolated Package
- High Voltage Isolation = 2.5 kV_{RMS} (t = 60 s; f = 60 Hz



- Sink to Lead Creepage Distance = 4.8 mm
- P-Channel
- 175 °C Operating Temperature
- · Dynamic dV/dt Rating
- · Low Thermal Resistance
- Lead (Pb)-free Available

DESCRIPTION

Third generation Power MOSFETs from Vishay provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The TO-220 FULLPAK eliminates the need for additional insulating hardware in commercial-industrial applications. The moulding compound used provides a high isolation capability and a low thermal resistance between the tab and external heatsink. This isolation is equivalent to using a 100 micron mica barrier with standard TO-220 product. The FULLPAK is mounted to a heatsink using a single clip or by a single screw fixing.

ORDERING INFORMATION			
Package	TO-220 FULLPAK		
Lead (Pb)-free	IRFI9520GPbF		
	SiHFl9520G-E3		
SnPb	IRF19520G		
	SiHFI9520G		

PARAMETER	SYMBOL	LIMIT	UNIT		
Drain-Source Voltage		V_{DS}	- 100		
Gate-Source Voltage	V_{GS}	± 20	V		
Continuous Drain Current	V_{GS} at - 10 V $T_{C} = 25 ^{\circ}\text{C}$ $T_{C} = 100 ^{\circ}\text{C}$	I _D	- 5.2		
	V_{GS} at 10 V_{C} $T_{C} = 100 ^{\circ}C$		- 3.6	Α	
Pulsed Drain Current ^a	I _{DM}	- 21			
Linear Derating Factor			0.24	W/°C	
Single Pulse Avalanche Energy ^b	E _{AS}	300	mJ		
Repetitive Avalanche Currenta	I _{AR}	- 5.2	А		
Repetitive Avalanche Energy ^a	E _{AR}	3.7	mJ		
Maximum Power Dissipation	T _C = 25 °C	P_{D}	37	W	
Peak Diode Recovery dV/dtc	dV/dt	- 5.5	V/ns		
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to + 175	°C	
Soldering Recommendations (Peak Temperature)	for 10 s		300 ^d		
Mounting Torque	6-32 or M3 screw		10	lbf ⋅ in	
	0-32 OF IVIS SCIEW		1.1	N · m	

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11). b. $V_{DD}=$ 25 V, starting $T_J=25$ °C, L=16 mH, $R_G=25$ Ω , $I_{AS}=$ 5.2 A (see fig. 12). c. $I_{SD}\leq$ 6.8 A, $dI/dt\leq$ 110 A/ μ s, $V_{DD}\leq$ V_{DS} , $T_J\leq$ 175 °C. d. 1.6 mm from case.

- * Pb containing terminations are not RoHS compliant, exemptions may apply

IRFI9520G, SiHFI9520G

Vishay Siliconix



THERMAL RESISTANCE RATINGS					
PARAMETER	SYMBOL	TYP.	MAX.	UNIT	
Maximum Junction-to-Ambient	R _{thJA}	-	65	°C/W	
Maximum Junction-to-Case (Drain)	R _{thJC}	-	4.1	C/VV	

PARAMETER	SYMBOL	TES	MIN.	TYP.	MAX.	UNIT	
Static							
Drain-Source Breakdown Voltage	V _{DS}	V _{GS} :	- 100	-	-	V	
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$	Reference	Reference to 25 °C, I _D = - 1 mA		- 0.10	-	V/°C
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} =	V _{DS} = V _{GS} , I _D = 250 μA		-	- 4.0	V
Gate-Source Leakage	I _{GSS}	,	V _{GS} = ± 20 V		-	± 100	nA
Zana Oata Wallana Buit O		V _{DS} =	V _{DS} = - 100 V, V _{GS} = 0 V		-	- 100	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = - 80 V	', V _{GS} = 0 V, T _J = 150 °C	-	-	- 500	μΑ
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} = - 10 V	I _D = - 3.1 A ^b	-	-	0.60	Ω
Forward Transconductance	9 _{fs}	V _{DS} =	- 50 V, I _D = - 3.1 A ^b	1.9	-	-	S
Dynamic							
Input Capacitance	C _{iss}	$V_{GS} = 0 V$,		-	390	-	
Output Capacitance	C _{oss}		$V_{DS} = -25 \text{ V},$		170	-	
Reverse Transfer Capacitance	C _{rss}	f = 1.0 MHz, see fig. 5		-	45	-	pF
Drain to Sink Capacitance	С		f = 1.0 MHz	-	12	-	
Total Gate Charge	Qg		$V_{GS} = -10 \text{ V}$ $I_{D} = -6.8 \text{ A}, V_{DS} = -80 \text{ V},$ see fig. 6 and 13 ^b	-	-	18	nC
Gate-Source Charge	Q _{gs}	V _{GS} = - 10 V		-	-	3.0	
Gate-Drain Charge	Q _{gd}	1		-	-	9.0	
Turn-On Delay Time	t _{d(on)}				9.6	-	- ns
Rise Time	t _r	$V_{DD} = -50 \text{ V}, I_D = -6.8 \text{ A},$ $R_G = 18 \Omega, R_D = 7.1 \Omega,$ see fig. 10^b		-	29	-	
Turn-Off Delay Time	t _{d(off)}			-	21	-	
Fall Time	t _f			-	25	-	
Internal Drain Inductance	L _D	Between lead, 6 mm (0.25") from package and center of die contact		-	4.5	-	
Internal Source Inductance	L _S			-	7.5	-	- nH
Drain-Source Body Diode Characteristic	s						ı
Continuous Source-Drain Diode Current	I _S	MOSFET symbol showing the integral reverse p - n junction diode		-	-	- 5.2	- A
Pulsed Diode Forward Current ^a	I _{SM}			-	-	- 21	
Body Diode Voltage	V_{SD}	$T_J = 25 ^{\circ}\text{C}, I_S = -5.2 \text{A}, V_{GS} = 0 V^b$		-	-	- 6.3	V
Body Diode Reverse Recovery Time	t _{rr}	- T _J = 25 °C, I _F = -6.8 A, dl/dt = 100 A/μs ^b		-	100	200	ns
Body Diode Reverse Recovery Charge	Q _{rr}			-	0.33	0.66	μC
Forward Turn-On Time	t _{on}	Intrinsic tu	n-on is dominated by L _S and L _D)			_D)	

Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. Pulse width \leq 300 μ s; duty cycle \leq 2 %.



TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Fig. 1 - Typical Output Characteristics, $T_C = 25$ °C




Fig. 2 - Typical Output Characteristics, $T_C = 175$ °C




Fig. 3 - Typical Transfer Characteristics




Fig. 4 - Normalized On-Resistance vs. Temperature

Vishay Siliconix






Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 7 - Typical Source-Drain Diode Forward Voltage




Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 8 - Maximum Safe Operating Area






Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms




Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case




Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms

Vishay Siliconix






Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 13a - Basic Gate Charge Waveform






Fig. 13b - Gate Charge Test Circuit



Peak Diode Recovery dV/dt Test Circuit



• Compliment N-Channel of D.U.T. for driver



* $V_{GS} = -5 \text{ V}$ for logic level and -3 V drive devices

Fig. 14 - For P-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see http://www.vishay.com/ppg?91162.



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.