

## Radial Lead Resettable Polymer PTCs


### SC60-200CZ0D

#### Features

- u RoHS Compliant and Halogen-Free
- u Radial leaded Devices
- u Cured, flame retardant epoxy polymer insulating material meets UL94V-0 requirements
- u Operation Current: 2.00A, Maximum Voltage: 60Vdc, Operating Temperature: -40°C to +85°C

#### Applications

- u USB hubs, ports and peripherals
- u Power ports
- u IEEE1394 ports
- u Motor protection
- u Automotive application
- u Computers and peripherals
- u General electronics



#### Electrical Parameters

Part Number	$I_{hold}$ (A)	$I_{trip}$ (A)	$V_{max}$ (Vdc)	$I_{max}$ (A)	$P_{dtyp}$ (W)	Maximum Time To Trip		Resistance		
						Current (A)	Time (S)	$R_{min}$ ( $\Omega$ )	$R_{max}$ ( $\Omega$ )	$R1_{max}$ ( $\Omega$ )
SC60-200CZ0D	2.00	4.00	60	40	2.50	10.0	15.0	0.050	0.095	0.150

$I_{hold}$ = Hold current: maximum current at which the device will not trip at 25°C still air.

$I_{trip}$ = Trip current: minimum current at which the device will always at 25°C still air.

$V_{max}$ = Maximum voltage device can withstand without damage at rated current.

$I_{max}$ = Maximum fault current device can withstand without damage at rated voltage.

$T_{trip}$ =Maximum time to trip(s) at assigned current.

$P_{dtyp}$ = Typical power dissipation: typical amount of power dissipated by the device when in state air environment.

$R_{min}$ = Minimum device resistance at 25°C prior to tripping.

$R_{max}$ = Maximum device resistance at 25°C prior to tripping.

$R1_{max}$ = Maximum resistance of device at 25°C measured one hour after tripping.

Caution: Operation beyond the specified rating may result in damage and possible arcing and flame.


#### Temperature Derating Chart - $I_{hold}$ (A)

Ambient Operation Temperature	-40°C	-20°C	0°C	23°C	30°C	40°C	50°C	60°C	70°C	85°C
Percentage Reduction	145%	130%	120%	100%	95%	88%	80%	71%	66%	56%

## Radial Lead Resettable Polymer PTCs

**SC60-200CZ0D**


### Temperature Derating Curve



### Test Procedures and Requirement

Test	Test Conditions	Accept/Reject Criteria
Resistance	In still air @25±2°C	$R_{min} \leq R \leq R_{max}$
Hold Current	60 min, at $I_{hold}$ , In still air @25±2°C	No trip
Time to Trip	Specified current, $V_{max}$ , @25±2°C	$T \leq \text{Maximum Time To Trip}$
Trip Cycle Life	$V_{max}$ , $I_{max}$ , 100 cycles	No arcing or burning
Trip Endurance	$V_{max}$ , 24hours	No arcing or burning

### Soldering Parameters



<b>Pre-Heating Zone</b>	Refer to the condition recommended by the manufacturer. Max. ramping rate should not exceed 4°C/Sec
<b>Soldering Zone</b>	Max. solder temperature should not exceed 260°C
<b>Cooling Zone</b>	Cooling by natural convection in air


## Radial Lead Resettable Polymer PTCs

### SC60-200CZ0D

#### Physical Specifications

<b>Lead Material</b>	0.03-1.85A Tin-plated Copper clad steel 2.50-5.00A Tin-plated Copper
<b>Soldering Characteristics</b>	Solder ability per MIL-STD-202, Method 208E
<b>Insulating Material</b>	Cured, flame retardant epoxy polymer meets UL 94V-0 requirements.
<b>Device Labeling</b>	Marked with 'SC', voltage, current rating

#### Dimensions



Part Number	Dimensions (mm)						Lead Material
	A (Max)	B (Max)	C (Typ)	D (Min)	E (Max)	F (Typ)	Tinned Metal (mm)
SC60-200CZ0D	17.5	22.4	5.1	7.6	3.1	1.4	Φ0.80

#### Packaging Quantity

Part Number	Quantity (pcs/reel)
SC60-200CZ0D	500