

● ELECTRICAL PARAMETERS

谐振器产品技术指标		Min	Max	Units
1. Holder Type(型号规格)		SEAM 7.0*1.5		
2. Mode of Oscillation (振动模式)		Fundamental		
3. Frequency (标称频率)		32.768000		KHz
4. Load Capacitance (CL) (负载电容)		12.5		pF
5. Drive Level (激励功率)		1		uw
6. Equivalent Resistance (谐振电阻)		65		KΩ
7. Shunt Capacitance (Co) (静态电容)		0.8	typ	pF
8. Motional Capacitance (C1) (动态电容)		1.9	typ	fF
9. Frequency Tolerance at 25°C (调整频差)		-20	20	ppm
10. Insulation Resistance (at DC 100V) (绝缘电阻)		500		MΩ
11. Operating Temperature Range (工作温度范围)		-40	85	°C
12. Storage Temperature Range (储存温度范围)		-55	125	°C
13. Aging (老化率)		± 5		ppm/year
14. DLD2	N/A		N/A	Ω
15. FLD2			N/A	ppm
16. RLD2			N/A	Ω
17. SPDB			N/A	db
18. Other(其它)		N/A		

OUTLINE DIMENSIONS(UNIT:mm) 外形尺寸 (单位: mm)

