


PCB. WELDING DRAWING



CIRCUIT DIAGRAM

XKKB

SPECIFICATION
 Contact Rating : 50mA, 12V DC
 Contact Resistance : 100mΩ max
 Insulation Resistance : 100mΩ min.500V DC
 Dielectric Strength : 250V AC/1minute
 Travel: 0.25mm
 Operating Temp : -40°C ~ +90°C
 Storage Temp : -30°C ~ +80°C

PAPT NO	TS-1135-X
Operating Force	A: 100gf B: 160gf C: 26300gf

		DSND		DATE		SCALE: N/A	MODEL TYPE: TACT SWITCH	
Δ X						VIEW:	PART NO.:	
Δ X						UNIT: mm	DWG NO.: TS-1135-X	
Δ X						SIZE: A4		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO., LIMITED		
REVISIONS						WEIGHT	SHEET	REVISION
						1.0g	1/1	A0