



**Micro Commercial Components** 

Micro Commercial Components 20736 Marilla Street Chatsworth CA 91311

Phone: (818) 701-4933 (818) 701-4939 Fax:

# **US1AFL THRU US1MFL**

### Features

- Halogen free available upon request by adding suffix "-HF" Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix designates RoHS Compliant. See ordering information)
- Glass Passivated Chip
- Ultra Fast Switching For High Efficiency
- For Surface Mounted Applications
- Low Forward Voltage Drop And High Current Capability
- Low Reverse Leakage Current
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1

### **Maximum Ratings**


- Operating Temperature: -65°C to +175°C
- Storage Temperature: -65°C to +175°C
- Maximum Thermal Resistance; 30 °C/W Junction To Lead

MCC	Device	Maximum	Maximum	Maximum
Catalog	Marking	Recurrent	RMS	DC
Number		Peak Reverse	Voltage	Blocking
		Voltage		Voltage
US1AFL	US1A	50V	35V	50V
US1BFL	US1B	100V	70V	100V
US1CFL	US1C	150V	105V	150V
US1DFL	US1D	200V	140V	200V
US1GFL	US1G	400V	280V	400V
US1JFL	US1J	600V	420V	600V
US1KFL	US1K	800V	560V	800V
US1MFL	US1M	1000V	700V	1000V

### Electrical Characteristics @ 25°C Unless Otherwise Specified


			шотшое оросписи
Average Forward	I <sub>F(AV)</sub>	1.0A	T <sub>L</sub> = 110°C
Current			
Peak Forward Surge	I <sub>FSM</sub>	30A	8.3ms, half sine
Current			
Maximum			
Instantaneous			
Forward Voltage			
US1AFL-1DFL	$V_{F}$	1.0V	$I_{FM} = 1.0A;$
US1GFL		1.4V	T <sub>J</sub> = 25°C
US1JFL-1MFL		1.7V	
Maximum DC			
Reverse Current At	$I_R$	10uA	T <sub>A</sub> = 25°C
Rated DC Blocking	10	100uA	T <sub>A</sub> = 100°C
Voltage			1 <sub>A</sub> 100 0
Maximum Reverse			
Recovery Time	_	50ns	
US1AFL-US1GFL	$T_{rr}$	75ns	$I_F=0.5A, I_R=1.0A,$
US1JFL~US1KFL US1MFL		100ns	I <sub>rr</sub> =0.25A
Typical Junction			
Capacitance			
US1AFL-1GFL	$C_{J}$	20pF	Measured at
US1JFL-1MFL		17pF	1.0MHz, V <sub>R</sub> =4.0V

## 1 Amp Ultra Fast Rectifier 50 to 1000 Volts



DIMENSIONS						
	INCHES		ММ			
DIM	MIN	MAX	MIN	MAX	NOTE	
Α	.035	.047	0.90	1.20		
b	.049	.065	1.25	1.65		
С	.004	.016	0.10	0.40		
D	.089	.116	2.25	2.95		
E	.173	.220	4.40	5.60		
E1	.126	.181	3.20	4.60		
L	.028	.059	0.70	1.50		
	.020	.000	00	1.00	-	

#### SUGGESTED SOLDER PAD LAYOUT




Notes: 1. High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7.

<sup>\*</sup>Pulse test: Pulse width 300 sec, Duty cycle 1%




## US1AFL thru US1MFL


Figure 1
Typical Forward Characteristics



Instantaneous Forward Current - Amperesversus Instantaneous Forward Voltage - Volts




Average Forward Rectified Current - Amperes/ersus Lead Temperature - $^{\circ}$ C






### US1AFL thru US1MFL




Peak Forward Surge Current - Amperes*versus* Number Of Cycles At 60Hz - Cycles



Peak Forward Surge Current - Amperesversus Pulse Duration - Milliseconds (mS)

Figure 6
Reverse Recovery Time Characteristic And Test Circuit Diagram



+0.5A

0

-0.25

-1.0

1cm

Set Time Base for 20/100ns/cm

- 1. Rise Time = 7ns max.
- Input impedance = 1 megohm, 22pF
- 2. Rise Time = 10ns max.
- Source impedance = 50 ohms
- 3. Resistors are non-inductive



### **Ordering Information:**

Device	Packing	
Part Number-TP	Tape&Reel: 10Kpcs/Reel	

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

#### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

#### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

#### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.