

SMD Transient Voltage Suppressors

GP

Approval Sheet

Customer Information

Customer			
Part Name			
Part No.			
Model No.			
COMPANY		PURCHASE	R&D

Vendor Information

Name	SFI Electronics Technology Inc.
Part Name	Chip TVS
Part No.	SFI0603-050E100NP-LF
Lot No.	

SFI Electronics Technology Inc.

ADDRESS: No.6, Lane 340, Shan-Ying Road, Guishan, Tao Yuan, Taiwan

TEL: 886-3-3506998	FAX: 886-3-35076	89 E-mail : sfi@sfi.com.tw	,		
Quality Control		Document Control	Business Issue		
	ISO 9001:2008	REV : I	Prepared	Check	
TÜVRheinland	ISO 9001:2008 ISO 14001:2004 ISO/TS 16949:2009 Management System	2015 .10. 07			
CERTIFIED	www.tuv.com ID 1100008833	Sa Issue Date &			

Part No.	SFI060	3-050E100NP-LF	Document No.	AS-RD	0603ME041-LF	REV.	I
http://www.sfi	i.com.tw	E-mail: sfi@sfi.com.t	tw TEL: 886-3-0	3506998	FAX: 886-3-3507	689	-1-



SMD Transient Voltage Suppressors

G P

PART NO. SFI0603-050E100NP-LF

1.1 Technology Data	Symbol		Value	Unit
Maximum allowable continuous AC voltage at 50-60Hz	V_{RMS}		3.3	V
Maximum allowable continuous DC voltage	V_{DC}		5	V
Varistor breakdown voltage	Vv		24~36	V
Typical capacitance value measured at 1MHz	С		10	pF
Typical capacitance value tolerance	t		±30	%
Maximum allowable clamping voltage	V_{C}		65	V
Leakage current at V _{DC} (at initial state)	I_{LDC}	<	1	μΑ
Leakage current at V _{DC} (after ESD test)	I_{LDCA}	<	2	μΑ
1.2 Reference Data				
Response time	T _{rise}	<	1	ns
Operation ambient temperature	T_OPT		-50~+85	$^{\circ}\! \mathbb{C}$
Storage temperature range	T_{STG}		-50~+125	$^{\circ}\! \mathbb{C}$
ESD testing	IEC61000-4-2		Level 4	
1.3 Other Data				
Body			ZnO	
End termination			Ag/Ni/Sn	
Packaging			Reel	
Complies with standard			IEC61000-4-2	
Complies with RoHs standard			Yes	
Lead content		<	1000	ppm
Marking			None	

Notes:

- $\ensuremath{\,\raisebox{.4ex}{\star}}\, 1$ The varistor breakdown voltage was measured at 1mA.
- ± 2 The clamping voltage was measured at 8/20µs standard current.
- *3 The leakage current was measured at working voltage.
- $\ensuremath{\,{\star}\,{4}}$ The components shall be employed within 1 year, in the nitrogen condition.

Part No.	SF1060	3-050E100NP-LF	Document No.	AS-RD	0603ME041-LF	REV.	I
http://www.sf	i.com.tw	E-mail: sfi@sfi.com.t	tw TEL: 886-3-3	3506998	FAX: 886-3-3507	689	-2-




SMD Transient Voltage Suppressors


GP

2. Size

Model	0603(1608)
Length(L)	1.60±0.15
Width(W)	0.80±0.10
Thickness(T)	0.90 max.
Termination(a)	0.30±0.10



3. ESD Wave Form



IEC61000-4-2 Standards

SEVERITY LEVEL	EVERITY LEVEL AIR DIRCHARGE	
1	2KV	2KV
2	4KV	4KV
3	8KV	6KV
4	15KV	8KV

IEC61000-4-2 compliant ESD current pulse waveform

4. Environment Reliability Test

Characteristic	Test Method and	Descr	iption		
High Temperature Storage	The specimen shall be subjected to 125±2°C stored at room temperature and normal humid varistor voltage shall be within 10%.				
	The temperature cycle of specified	Step	Temperature	Period	
	temperature shall be repeated five times and	1	-40±3°C	30±3min	
Temperature Cycle	then stored at room temperature and normal humidity for one or two hours. The change of varistor voltage shall be within 10% and		room temperature	1 hour	
			125±3℃	30±3min	
	mechanical damage shall be examined.	4	room temperature	1 hour	
High Temperature Load	1000±2 hours, the specimen shall be stored a	After being continuously applied the maximum allowable voltage at 85±2°C 1000±2 hours, the specimen shall be stored at room temperature and norm temperature			
Damp Heat Load/ Humidity Load	The specimen should be subjected to 40±2°C and 90~95% RH, the maximum allowable voltage applied for 1000±2 hours and then stored at room temperature and normal humidity for one or two hours. The change of varistor voltage shall be within 10%.				
Low Temperature Storage	The specimen should be subjected to -40±2°C for 1000±2 hours without loa				

Part No.	SFI060	3-050E100NP-LF	Do	cument No.	AS-RD	0603ME041-LF	REV.	I
http://www.sfi	i.com.tw	E-mail: sfi@sfi.com.t	tw	TEL: 886-3-3	3506998	FAX: 886-3-3507	689	-3-



SMD Transient Voltage Suppressors

GP


5. Soldering Recommendations

5.1 Recommended solder pad layout

(Unit : mm)

A B C


0603 0.9~1.2 0.9~1.2 0.8~1.0



- 5.2 The SIR test of the solder paste shall be done (Based on JIS-Z-3284)
- 5.3 Steel plate and foot distance printing

Foot distance printing (mm)	Steel plate thickness (mm)
≧ 0.65mm	0.18mm
0.50~0.65mm	0.15mm
0.40~0.50mm	0.12mm
≦0.40mm	0.10mm

5.4 The IR reflow and temperature of soldering for Pb free process



☆ IR reflow Pb free process suggestion profile

- (1) The solder recommend is Sn96.5/Ag3.5 and thickness recommend as shown in table 5.3
- (2) Ramp-up rate (217°C to peak) +3°C/second max.
- (3) Temp. maintain at 175±25°C 180 seconds max.
- (4) Temp. maintain above 217°C 60~150 seconds

Part No.	SF1060	3-050E100NP-LF	Do	cument No.	AS-RD	0603ME041-LF	REV.	I
http://www.sf	i.com.tw	E-mail: sfi@sfi.com.t	tw	TEL: 886-3-3	3506998	FAX: 886-3-3507	689	-4-



SMD Transient Voltage Suppressors

GP

- (5) Peak temperature range $\underline{245+20/-10^{\circ}C}$ within $5^{\circ}C$ of actually peak temperature (t_p) 10~20 seconds
- (6) Ramp down rate -6°C/second max.
 - *Perform adequate test in advance as the reflow temperature profile will vary according to the conditions of the manufacturing process and the specification of the reflow furnace.
- 5.5 Resistance to soldering heat and high temperature resistance : 260°C, 10sec 3 times
- 5.6 Hand soldering

In hand soldering of the varistors, large temperature gradient between preheated the varistors and the tip of soldering iron may cause electrical failures and mechanical damages such as cracking or breaking of the devices. The soldering shall be carefully controlled and carried out, so that the temperature gradient is kept minimum with following recommended conditions for hand soldering. 5.6.1 Recommended soldering condition 1 (with preheating)

- (1) Solder
 - **0.12~0.18mm** thread solder (Sn96.5:Ag3.5) with soldering flux in the core rosin-based and non-activated flux is recommended.
- (2) Preheating

The varistors shall be preheated so that temperature gradient between the devices and the tip of soldering iron is 150° C or below.

(3) Soldering iron

Rated power of 20W max. with 3mm soldering tip in diameter Temperature of soldering iron tip 380°C max., 3~5sec (The required amount of solder shall be melted in advance on the soldering tip.)

(4) Cooling

After soldering, the varistors shall be cooled gradually at room ambient temperature.

- 5.6.2 Recommended soldering condition 2 (without preheating)
 - (1) Solder iron tip shall not directly touch to ceramic dielectrics.
 - (2) Solder iron tip shall be fully preheated before soldering while soldering iron tip to the external electrode of varistors.
- 5.7 Post soldering cleaning
 - 5.7.1 Residues of corrosive soldering fluxes on the PC board after cleaning may greatly have influences on the electrical characteristic and the reliability (such as humidity resistance) of the varistors which have been mounted on the board. It shall be confirmed that the characteristic and the reliability of the devices are not affected by the applied cleaning conditions.
 - 5.7.2 When an ultrasonic cleaning is applied to the mounted varistors on PC boards. Following conditions are recommended for preventing failures or damages of the devices due to the large vibration energy and the resonance conditions caused by the ultrasonic waves.
 - (1) Frequency 29MHz max.
 - (2) Radiated power 20W/liter max.
 - (3) Period 5 minutes max.

Part No.	SFI0603-050E100NP-LF		Document No.	AS-RD	0603ME041-LF	REV.	I
http://www.sfi.com.tw		E-mail: sfi@sfi.com.t	tw TEL : 886-3-3	3506998	FAX: 886-3-3507	689	-5-




SMD Transient Voltage Suppressors

GP

6. Packaging Specification

- 6.1 Carrier tape and transparent cover tape should be heat-sealed to carry the products, and the reel should be used to reel the carrier tape.
- 6.2 The adhesion of the heat-sealed cover tape shall be 40 +20/-15 grams.
- 6.3 Both the head and the end portion of the taping shall be empty for reel package and SMT auto-pickup machine. And a normal paper tape shall be connected in the head of taping for the operator to handle.



(Unit: mm)

Symbol	A ₀ ±0.05	B₀ ±0.05	K₀ ±0.05	D +0.10 -0.05	P ±0.10	P ₂ ±0.10	P ₀ ±0.10	W ±0.10	E ±0.10	F ±0.05
0603	1.05	1.90	0.95	1.56	4.00	2.00	4.00	8.00	1.75	3.50


Part No.	SFI0603-050E100NP-LF		Document No.	AS-RD	0603ME041-LF	REV.	I
http://www.sfi.com.tw		E-mail: sfi@sfi.com.t	tw TEL: 886-3-	3506998	FAX: 886-3-3507	689	-6-



SMD Transient Voltage Suppressors

GP

7. Reel Dimension



(Unit:mm)

Symbol	Α	В	С	D	E	W	W ₁
0603	178.0±1.0	60.0±0.5	13.0±0.2	21.0±0.2	2.0±0.5	9.0±0.5	1.5±0.1

8. Standard Packaging

Size	0603			
Pcs	4000			

Part No.	SFI0603-050E100NP-LF		Document No.	AS-RD	0603ME041-LF	REV.	I
http://www.sfi.com.tw		E-mail: sfi@sfi.com.t	tw TEL: 886-3-	3506998	FAX: 886-3-35070	689	-7-