





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	A1		UPDATE PIN LENGTH PER CUSTOMER REQUIREMENT	2016.3.7	A.Y	R.B

NOTES:

- 1.RATED CURRENT:3.0AMP.
- 2.CONTACT RESISTANCE:20mΩ MAX.
- 3.WITHSTAND VOLTAGE:1000V AC/DC
- 4.INSULATION RESISTANCE:1000MΩ MIN.
- 5.OPERATION TEMPERATURE:-40°C TO +105°C
- 6.CONTACT MATERIAL:COPPER ALLOY
- 7.CONTACT PLATING:
 3u" MIN. AU ON MATING AREA OVER NI UNDERPLATING
 80u" MIN. SN ON SOLDER AREA OVER NI UNDERPLATING
- 8.INSULATOR MATERIAL:PA9T UL94V-0 BK
- 9.RECOMMENDED SOLDERING PROCESS:
 WAVE SOLDERING, PEAK TEMPERATURE: 260°C, 5S
- 10.RECOMMENDED MATING TE PN: X-2271668-X



RECOMMENDED P.C.B LAYOUT (COMPONENT SIDE)

TUBE	16	1-2271729-6
TUBE	14	1-2271729-4
TUBE	6	2271729-6
PACKAGING	POS	PN
PRODUCT FAMILY TABLE		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Andy yang 1MAR2016	STE TE Connectivity											
DIMENSIONS: mm		CHK Rick Bian												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD XIANG XU	NAME AMPMODU, PIN HDR, 2.54PITCH 2ROW, 2HOUSING, VERTICAL, TH											
<table border="0"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± 0.25</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC				± -	1 PLC	± -	2 PLC	± 0.25	3 PLC	± -	4 PLC	± -
0 PLC	± -													
1 PLC	± -													
2 PLC	± 0.25													
3 PLC	± -													
4 PLC	± -													
ANGLES	± -													
MATERIAL	FINISH	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO								
-	-	-	-	A300779	C-2271729	-								
CUSTOMER DRAWING			SCALE	SHEET	REV									
			1:1	1 OF 1	A1									