<u>MOSFET</u> – Power, Single N-Channel 40 V, 0.67 mΩ, 370 A

Features

- Small Footprint (5x6 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- NVMFS5C404NLWF Wettable Flank Option for Enhanced Optical Inspection
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

| | (0 | | , | | | |
|--|---------------------|----------------------------|-----------------------------------|-----------------|------|--|
| Parameter | | | Symbol | Value | Unit | |
| Drain-to-Source Voltage | | | V _{DSS} | 40 | V | |
| Gate-to-Source Voltage | | | V _{GS} | ±20 | V | |
| Continuous Drain | Steady | T _C = 25°C | I _D | 370 | А | |
| Current R _{θJC} (Notes 1, 3) | | T _C = 100°C | | 260 | | |
| Power Dissipation | State | T _C = 25°C | PD | 200 | W | |
| R _{θJC} (Note 1) | | $T_{C} = 100^{\circ}C$ | | 100 | | |
| Continuous Drain | Steady State | T _A = 25°C | I _D | 52 | А | |
| Current R _{θJA} (Notes 1, 2, 3) | | $T_A = 100^{\circ}C$ | | 37 | | |
| Power Dissipation | | T _A = 25°C | PD | 3.9 | W | |
| $R_{\theta JA}$ (Notes 1 & 2) | | T _A = 100°C | | 1.9 | | |
| Pulsed Drain Current | T _A = 25 | °C, t _p = 10 μs | I _{DM} | 900 | А | |
| Operating Junction and Storage Temperature | | | T _J , T _{stg} | –55 to + 175 | °C | |
| Source Current (Body Diode) | | | ا _S | 191 | А | |
| Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = 38 A) | | | E _{AS} | 907 | mJ | |
| Lead Temperature for Soldering Purposes (1/8" from case for 10 s) | | | ΤL | 260 | °C | |

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

| Parameter | Symbol | Value | Unit |
|---|-----------------|-------|------|
| Junction-to-Case - Steady State | $R_{\theta JC}$ | 0.75 | °C/W |
| Junction-to-Ambient - Steady State (Note 2) | $R_{\theta JA}$ | 39 | |

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

2. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.


3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.




ON Semiconductor®

www.onsemi.com

| V _{(BR)DSS} | R _{DS(ON)} MAX | I _D MAX |
|----------------------|--------------------------------|--------------------|
| 40 V | $0.67~\mathrm{m}\Omega$ @ 10 V | 070 4 |
| 40 V | 1.0 mΩ @ 4.5 V | 370 A |





ORDERING INFORMATION


See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = $25^{\circ}C$ unless otherwise specified)


| Parameter | Symbol | Test Condition | | Min | Тур | Max | Unit | |
|--|--|---|------------------------|-----|-------|-----------|-------|--|
| OFF CHARACTERISTICS | | | | | | | | |
| Drain-to-Source Breakdown Voltage | V _{(BR)DSS} | V _{GS} = 0 V, I _D = 250 μA | | 40 | | | V | |
| Drain-to-Source Breakdown Voltage Temperature Coefficient | V _{(BR)DSS} / T _J | | | | 21.6 | | mV/°C | |
| Zero Gate Voltage Drain Current | I _{DSS} | V _{GS} = 0 V, | T _J = 25 °C | | | 10 | | |
| | | V _{DS} = 40 V | T _J = 125°C | | | μA 250 | | |
| Gate-to-Source Leakage Current | I _{GSS} | V _{DS} = 0 V, V _{GS} = 20 V | | | | 100 | nA | |
| ON CHARACTERISTICS (Note 4) | | | | | | | | |
| Gate Threshold Voltage | V _{GS(TH)} | V_{GS} = V_{DS} , I_D = 250 μ A | | 1.2 | | 2.0 | V | |
| Threshold Temperature Coefficient | V _{GS(TH)} /T _J | | | | -6.2 | | mV/°C | |
| Drain-to-Source On Resistance | R _{DS(on)} | V _{GS} = 10 V | I _D = 50 A | | 0.52 | 0.67 | | |
| | | V _{GS} = 4.5 V | I _D = 50 A | | 0.75 | 1.0 | mΩ | |
| Forward Transconductance | 9 _{FS} | V _{DS} =15 V, I _I | ₀ = 50 A | | 270 | | S | |
| CHARGES, CAPACITANCES & GATE RE | SISTANCE | | | | | | | |
| Input Capacitance | C _{ISS} | V _{GS} = 0 V, f = 1 MHz, V _{DS} = 25 V | | | 12168 | | | |
| Output Capacitance | C _{OSS} | | | | 4538 | | pF | |
| Reverse Transfer Capacitance | C _{RSS} | | | | 79.8 | | | |
| Total Gate Charge | Q _{G(TOT)} | V_{GS} = 4.5 V, V_{DS} = 20 V; I_{D} = 50 A | | | 81 | | | |
| Total Gate Charge | Q _{G(TOT)} | V_{GS} = 10 V, V_{DS} = 20 V; I_{D} = 50 A | | | 181 | | 1 | |
| Threshold Gate Charge | Q _{G(TH)} | V _{GS} = 4.5 V, V _{DS} = 20 V; I _D = 50 A | | | 8.5 | | nC | |
| Gate-to-Source Charge | Q _{GS} | | | | 27.8 | | | |
| Gate-to-Drain Charge | Q _{GD} | | | | 23.8 | | | |
| Plateau Voltage | V _{GP} | | | | 2.7 | | V | |
| SWITCHING CHARACTERISTICS (Note 5 | 5) | | | | | | | |
| Turn-On Delay Time | t _{d(ON)} | V_{GS} = 4.5 V, V_{DS} = 20 V, I_{D} = 50 A, R_{G} = 1.0 Ω | | | 24 | | - ns | |
| Rise Time | t _r | | | | 135 | | | |
| Turn-Off Delay Time | t _{d(OFF)} | | | | 87 | | | |
| Fall Time | t _f | | | | 157 | | | |
| DRAIN-SOURCE DIODE CHARACTERIS | TICS | | | | | | | |
| Forward Diode Voltage | V _{SD} | V _{GS} = 0 V, I _S = 50 A | $T_J = 25^{\circ}C$ | | 0.7 | 1.2 | | |
| | | | T _J = 125°C | | 0.61 | | V | |
| Reverse Recovery Time | t _{RR} | V _{GS} = 0 V, dIS/dt = 100 A/µs, I _S = 50 A | | | 97.4 | | | |
| Charge Time | ta | | | | 46.5 | | ns | |
| Discharge Time | t _b | | | | 50.9 | | 1 | |
| Reverse Recovery Charge | Q _{RR} | | | | 190 | | nC | |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 4. Pulse Test: pulse width $\leq 300 \ \mu$ s, duty cycle $\leq 2\%$. 5. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS







Figure 13. Thermal Characteristics

DEVICE ORDERING INFORMATION

| Device | Marking | Package | Shipping [†] | |
|---------------------|---------|------------------------------------|-----------------------|--|
| NVMFS5C404NLT1G | 5C404L | DFN5 (Pb-Free) | 1500 / Tape & Reel | |
| NVMFS5C404NLWFT1G | 404LWF | DFN5 (Pb-Free, Wettable Flanks) | 1500 / Tape & Reel | |
| NVMFS5C404NLT3G | 5C404L | DFN5 (Pb–Free) | 5000 / Tape & Reel | |
| NVMFS5C404NLWFT3G | 404LWF | DFN5 (Pb-Free, Wettable Flanks) | 5000 / Tape & Reel | |
| NVMFS5C404NLAFT1G | 5C404L | DFN5 (Pb–Free) | 1500 / Tape & Reel | |
| NVMFS5C404NLWFAFT1G | 404LWF | DFN5 (Pb-Free, Wettable Flanks) | 1500 / Tape & Reel | |

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdi/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor, "Typical" parameters which may be provided in ON Semiconductor dates heets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights or the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor hard here, and the singes that ON Semiconductor was negligent regardles; and claim succes, and liability and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirec

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: ON Semiconductor Website: www.onsemi.com Order Literature: http://www.onsemi.com/orderlit

Phone: 421 33 790 2910 For additional inform

For additional information, please contact your local

Sales Representative