


Gas Discharge Tube – SS201N


Features

- DC Spark-over voltage: 200V
- Low Capacitance
- Micro-Gap Design
- Stable breakdown voltage
- RoHS & HF compliant
- High holdover voltage
- High insulation resistance
- Large absorbing transient current capability.



Applications

- Communication equipment
- Test equipment
- Data lines
- CATV equipment
- Power Supplies
- Telecom SLIC protection
- Telecommunications




General Characteristics Definition


- Operating temperature: -40 ~ 85°C
- Storage temperature: -40 ~ 85°C

Part Number Code

S S 201 N



Physical Dimensions



Note:

1. All dimensions are in millimeters.
2. No marking on the device.


Gas Discharge Tube – SS201N

Electrical Characteristics

Part Number	DC Spark-over Voltage @ 100V/S	Impulse Spark-over Voltage @ 1kV/ μ S	Impulse Discharge Current	Impulse Life Test	Minimum Insulation Resistance Test @ 100 Vdc	Maximum Capacitance @ 1.0 MHz	UL Certification
	(V)	(V)	(kA)	(A)	(G Ω)	(pF)	
SS201N	200 \pm 30%	\leq 750	0.5	100	1	0.5	Pending

Lead Free Reflow Soldering Recommendations


Preheat	
- Temperature Min (Tsmin)	150°C
- Temperature Max (Tsmax)	200°C
- Time (Tsmin to Tsmax)	60-180 seconds
- Average Ramp-Up Rate	1~3°C/second
Peak Temperature	260°C max.
Time within 5°C of actual Peak Temperature (tp)	40 seconds max.
Ramp-Down Rate	6 °C /second max.



Note: If the wave soldering temperatures exceed the recommended profile, devices may not meet the performance requirements.

Packaging Information

Part Number	Quantity	
	EA/Roll	EA/Box
SS201N	2000	6000



Dimension	Millimeters
P	8.0 \pm 0.1
P0	4.0 \pm 0.1
D	1.55 \pm 0.05
E	1.75 \pm 0.1
F	5.45 \pm 0.1
W	12.0 \pm 0.3
T	0.3 \pm 0.05
K	2.0 \pm 0.1