

ESD5V0B05-923

1-Line Bi-directional Diode

www.sot23.com.tw

Features

- * 40W peak pulse power (8/20 μs)
- * Protects one data or power line
- * Operating voltage:±5V
- * Ultra low clamping voltage
- * Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
 - Air discharge: ±22kV
 - Contact discharge: ±20kV
- * IEC61000-4-5 (SURGE)2.5A (8/20us)
- * RoHS Compliant

Mechanical Characteristics


- * Package: SOD-923(0402)
- * Ultra low leakage: nA level
- * Case Material: "Green" Molding Compound.
- * UL Flammability Classification Rating 94V-0
- * Moisture Sensitivity: Level 3 per J-STD-020
- * Shipping Qty :8000 /7Inch Tape & Reel


Applications

- Mobile Phones and Accessories
- * Battery Protection
- * USB VBus
- * Power Line Protection
- * Hand Held Portable Applications

Dimensions and Pin Configuration







SOD923



ESD5V0B05-923

1-Line Bi-directional Diode

www.sot23.com.tw

Absolute Maximum Ratings (Tamb=25°C unless otherwise specified)

Symbol	Value	Unit	
Ppk	40	W	
IPP	2.5	А	
VESD	±22	kV	
VESD	±20	КV	
TJ	-55 to +125	°C	
Tstg	-55 to +150	°C	
	Ppk IPP VESD TJ	Ppk 40 IPP 2.5 VESD ±22 ±20 TJ	

Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Reverse Working Voltage	Vrwm				5	V
Breakdown Voltage	Vbr	IT = 1mA -	6.5	7.5	9.5	V
Reverse Leakage Current	I _R	$V_{RWM} = 5.0V$			0.08	μA
Clamping Voltage	Vc	$I_{PP} = 1A (8 \times 20 us pulse)$			10	V
Clamping Voltage	Vc	$I_{PP} = 2.5 A (8 \times 20 us pulse)$			14	V
Junction Capacitance	CJ	VR = 0V, f = 1MHz		0.5	0.9	pF



Characteristic Curves


ESD5V0B05-923

1-Line Bi-directional Diode

www.sot23.com.tw

Fig2. ESD Pulse Waveform (according to IEC 61000-4-2) Fig1. 8/20µs Pulse Waveform 120 100% TEST Peak Value IPP tr Percent of Peak Pulse Current % 90% WAVEFORM 100 PARAMETERS Ipp - Peak Pulse Current - % of Ipp t_r=8µs t_d=20µs 80 60 40 t_d=t I_{PP}/2-10% 20 Time (ns) -tr = 0.7~1ns 0 - 30ns 5 10 15 20 25 30 0 60ns t - Time (µs)

Fig3. Power Derating Curve






ESD5V0B05-923

1-Line Bi-directional Diode

www.sot23.com.tw

Outline Drawing - SOD-923(0402)



		DIME	NSIONS		
DIM	INC	INCHES		MM	
	MIN	MAX	MIN	MAX	
Α	.037	.041	0.95	1.05	
В	.030	.033	0.75	0.85	
С	.022	.026	0.55	0.65	
D	.014	.017	0.36	0.43	
Е	.006	.010	0.15	0.25	
F	.003	.007	0.07	0.17	

Land Pattern - SOD-923(0402)

