


GPSR0730-Series

GPSR系列產品符合“實用新型貼片式功率電感器”專利，專利號：ZL 2009 2 0129705.8




實物圖：




推薦焊盤：



尺寸：(Unit:mm)



命名方式：



特性參數：

Part Number 型號	Inductance 電感量 (μH) @100KHz, 1V	DC Resistance 直流電阻 (mΩ)		Heat Rating Current 溫升電流(A)	Saturation Current 飽和電流(A)
		典型值 Typical	最大值 Max		
GPSR0730-R10M	0.10	1.5	1.7	32.5	60
GPSR0730-R22M	0.22	2.3	2.9	23	40
GPSR0730-R33M	0.33	3.2	3.9	20	30
GPSR0730-R47M	0.47	3.6	4.7	17.5	26
GPSR0730-R56M	0.56	4.3	5.7	16.5	25.5
GPSR0730-R68M	0.68	5.7	7.4	15.5	25
GPSR0730-R82M	0.82	6.7	8	13	24
GPSR0730-1R0M	1	9	10	11	22
GPSR0730-1R5M	1.5	10.5	13.7	9	18
GPSR0730-2R2M	2.2	12.5	19	8	14
GPSR0730-3R3M	3.3	20	30	6	10
GPSR0730-4R7M	4.7	28	40	5.5	10
GPSR0730-5R6M	5.6	34	45	5.5	8
GPSR0730-6R8M	6.8	40	51	4.5	8
GPSR0730-8R2M	8.2	54	68	4.5	6
GPSR0730-100M	10	60	102	3	7

典型電流重疊與溫升特性曲線

