

## 650V GaN Power Transistor (FET)


### Features

- Easy to use, compatible with standard gate drivers
- Low  $Q_{rr}$ , no free-wheeling diode required
- Excellent gate charge x  $R_{DS(on)}$  product (FOM)
- Low switching loss
- RoHS compliant and Halogen-free

Product Summary		
$V_{DSS}$	650	V
$R_{DS(on),max}$	150	m $\Omega$
$Q_{G Typ}$	21	nC
$Q_{rr Typ}$	42	nC

### Applications

- Telecom and datacom
- Industrial
- Automotive
- Servo motors



### Packaging

Part Number	Package
XGP6510B	3 Lead TO-220

### Maximum ratings, at $T_c=25^\circ\text{C}$ , unless otherwise specified

Symbol	Parameter	Limit Value	Unit
$I_D$	Continuous drain current @ $T_c=25^\circ\text{C}$	19	A
	Continuous drain current @ $T_c=100^\circ\text{C}$	14	A
$I_{DM}$	Pulsed drain current (pulse width: 10us)	110	A
$V_{DSS}$	Drain to source voltage ( $T_j = -55^\circ\text{C}$ to $150^\circ\text{C}$ )	650	V
$V_{GSS}$	Gate to source voltage	$\pm 20$	V
$P_D$	Maximum power dissipation @ $T_c=25^\circ\text{C}$	100	W
$T_c$	Operating temperature	Case	-55 to 150
$T_j$		Junction	-55 to 150
$T_s$	Storage temperature	-55 to 150	$^\circ\text{C}$
$T_{CSOLD}$	Soldering peak temperature	260	$^\circ\text{C}$


### Thermal characteristics

Symbol	Parameter	Typical	Unit
$R_{\theta JC}$	Junction-to-case	1.25	$^\circ\text{C}/\text{W}$
$R_{\theta JA}$	Junction-to-ambient	50	$^\circ\text{C}/\text{W}$

Electrical Parameters, at  $T_J=25^{\circ}\text{C}$ , unless otherwise specified


Symbol	Min	Typ	Max	Unit	Test Conditions
<b>Forward Device Characteristics</b>					
$V_{DSS-MAX}$	-	650	-	V	$V_{GS}=0V$
$BV_{DSS}$	-	1500	-	V	$V_{GS}=0V, I_{DSS}=250\mu A$
$V_{GS(th)}$	-	1.62	-	V	$V_{DS}=V_{GS}, I_D=500\mu A$
$R_{DS(on)}$	130	140	150	m $\Omega$	$V_{GS}=8V, I_D=4A, T_J=25^{\circ}\text{C}$
	-	280	-		$V_{GS}=8V, I_D=4A, T_J=150^{\circ}\text{C}$
$I_{DSS}$	-	4	6	$\mu A$	$V_{DS}=700V, V_{GS}=0V, T_J=25^{\circ}\text{C}$
	-	20	-	$\mu A$	$V_{DS}=700V, V_{GS}=0V, T_J=150^{\circ}\text{C}$
$I_{GSS}$	-	-	150	nA	$V_{GS}=20V$
	-	-	-150	nA	$V_{GS}=-20V$
$C_{ISS}$	-	1450	-	pF	$V_{GS}=0V, V_{DS}=650V, f=1\text{MHz}$
$C_{OSS}$	-	40	-	pF	
$C_{RSS}$	-	2	-	pF	
$C_{O(er)}$	-	50	-	pF	$V_{GS}=0V, V_{DS}=0 \text{ to } 650V$
$C_{O(tr)}$	-	90	-	pF	
$Q_G$	-	21	-	nC	$V_{DS}=400V, V_{GS}=0V \text{ to } 8V, I_D=10A$
$Q_{GS}$	-	4.5	-		
$Q_{GD}$	-	4	-		
$t_{D(on)}$	-	30	-	nS	$V_{DS}=400V, V_{GS}=0V \text{ to } 10V, I_D=10A, R_G=11\Omega$
$t_R$	-	10	-		
$t_{D(off)}$	-	50	-		
$t_F$	-	6	-		
<b>Reverse Device Characteristics</b>					
$V_{SD}$	-	1.9	-	V	$V_{GS}=0V, I_S=10A, T_J=25^{\circ}\text{C}$
	-	3	-		$V_{GS}=0V, I_S=10A, T_J=150^{\circ}\text{C}$
	-	1.3	-		$V_{GS}=0V, I_S=5A, T_J=25^{\circ}\text{C}$
$t_{rr}$	-	12	-	nS	$I_S=7A, V_{GS}=0V, d_i/d_t=1000A/\mu s, V_{DD}=400V$
$Q_{rr}$	-	42	-	nC	

Typical Characteristic, at  $T_c=25^\circ\text{C}$ , unless otherwise specified




**Figure 1. Typical Output Characteristics  $T_j=25^\circ\text{C}$**

Parameter:  $V_{GS}$




**Figure 2. Typical Output Characteristics  $T_j=150^\circ\text{C}$**

Parameter:  $V_{GS}$




**Figure 3. Typical Transfer Characteristics**

$V_{DS}=10\text{V}$ , Parameter:  $T_j$




**Figure 4. Normalized On-resistance**

$I_D=4\text{A}$ ,  $V_{GS}=8\text{V}$




**Figure 5. Typical Capacitance**

$V_{GS}=0\text{V}$ ,  $f=1\text{MHz}$




**Figure 6. Typical Coss Stored Energy**

Typical Characteristic, at  $T_c=25^\circ\text{C}$ , unless otherwise specified




**Figure 7. Typical Qoss**




**Figure 8. Forward Characteristic of Rev. Diode**

$I_s=f(V_{SD}), \text{Parameter } T_j$




**Figure 9. Drain-Source breakdown voltage**




**Figure 10. Typical Gate Charger**

$I_{DS}=10\text{A}, V_{DS}=400\text{V}$




**Figure 11. Power Dissipation**




**Figure 12. Current Derating**


**Test Circuits and Waveforms**




**Figure 16. Switching Time Test Circuits**




**Figure 17. Switching Time Waveform**




**Figure 18. Dynamic  $R_{DS(on)eff}$  Test Circuits**



**Figure 19. Dynamic  $R_{DS(on)eff}$  Waveform**



**Figure 20. Diode Characteristics Test Circuits**




**Figure 21. Diode Recovery Waveform**

**Mechanical**

**3 Lead TO-220 (PS) Package**

Pin 1: Gate; Pin 2: Source; Pin 3: Drain; Tab: Source



COMMON DIMENSIONS

SYMBOL	MM		
	MIN	NOM	MAX
A	4.37	4.57	4.77
A1	1.22	1.27	1.42
A2	2.49	2.69	2.89
b	0.75	0.81	0.96
b2	1.22	1.27	1.47
c	0.30	0.38	0.48
D1	8.50	8.70	8.90
D2	5.20	-	-
E	9.86	10.16	10.36
E5	7.06	-	-
e	2.54 BSC		
e1	5.08 BSC		
H1	6.10	6.30	6.50
L	13.10	13.40	13.70
L1	-	3.75	4.10
$\phi P$	3.70	3.84	3.99
Q	2.54	2.74	2.94