

# 晶创和立科技

## **GL7510F**


## MINIATURE CADMIUM SULPHIDE PHOTOCONDUCTIVE CELL




## **FEATURES**

- Miniature open frame package
- Epoxy coated
- Moisture resistant
- Spectral response similar to the human eye
- Applications include dusk-dawn lighting control

### LIGHT DEPENDENT RESISTOR





### SPECIFICATION AND PERFORMANCE

Model	Vmax	Pmax (mW)	Ambient temp(°C)	l neak l	Resistance	Dark Resistance (MΩ)	Gamm a value at 100- 10Lux	Response Time (ms)	
iviouei	(VDC)							Rise Time	Decay time
GL7510F	100	150	-30~+70	540	8-20	1	0.65	30	30

## **Measuring Conditions**

### 1. Light resistance:

Measured at 10 Lux with standard light A (2854K color temperature) and 2hr illumination at 400-600 lux prior to testing.

#### 2. Dark Resistance:

Measured 10 senconds after closed 10 lux.

#### 3. Gamma Characteristic:

Between 10 lux ande 100 lux and given by  $\gamma = Ig(R10/R100)$ 

R10、R100 Cell resistance at 10 lux and 100 lux.


The error of  $\gamma$  is  $\pm$  0.1.


### 4. Pmax:

Max. power dissipation at ambient temperature of 25  $^{\circ}\text{C}$  .

### 5. Vmax:

Max. voltage in darkness that may be applied to the cell continuously.





SHENZHEN JINGCHUANGHELI TECHNOLOGY CO., LTI Http://www.szjchl.com

Tel:+86-755-23210829 Fax:+86-755-23210825

E-mail:heli@szjchl.com