


DATASHEET

0.8mm Height Flat Top Infrared LED IR19-21C/TR8(BY)



Features

- Small double-end package
- Low forward voltage
- Good spectral matching to Si photo detector
- Pb free
- The product itself will remain within RoHS compliant version
- Compliance with EU REACH
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

Descriptions

- IR19-21C/TR8(BY) is an infrared emitting diode in miniature SMD package which is molded in a water clear plastic with flat view lens
- The device is spectrally matched with silicon photodiode and phototransistor

Applications

- PCB mounted infrared sensor
- Infrared emitting for miniature light barrier
- Floppy disk drive
- Optoelectronic switch
- Smoke detector


Device Selection Guide


Part Category	Chip Material	Lens Color		
IR	GaAlAs	Water Clear		




Chip Phototransistor with Right Angle Lens IR19-21C/TR8(BY)

Package Dimensions





- Anode
- (2) Cathode



For refiew soldering (Propose) 2 ± 0.2 0.8 ± 0.2 0.8 ± 0.2 0.9 0

Notes: 1.All dimensions are in millimeters

- 2.Tolerances unless dimensions ±0.1mm
- 3.Suggested pad dimension is just for reference only Please modify the pad dimension based on individual need

EVERLIGHT

Chip Phototransistor with Right Angle Lens IR19-21C/TR8(BY)

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Symbol Rating	
Continuous Forward Current	I _F	65	mA
Reverse Voltage	V _R	5	V
Operating Temperature	T _{opr}	-25 ~ +85	$^{\circ}\!\mathbb{C}$
Storage Temperature	T _{stg}	-40 ~ +85	$^{\circ}\!\mathbb{C}$
Soldering Temperature*1	T _{sol}	260	$^{\circ}\!\mathbb{C}$
Power Dissipation at (or below) 25° Free Air Temperature	P_d	130	mW

Notes: *1: Soldering time ≤ 5 seconds

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Condition	Min.	Тур.	Max.	Units
Radiant Intensity	le	I _F =20mA	0.5	0.9		mW/sr
Peak Wavelength	λр			940		nm
Spectral Bandwidth	Δλ			50		nm
Forward Voltage	V _F			1.2	1.5	V
View Angle	201/2			150		deg
Reverse Current	I _R	V _R =5V			10	μΑ



Typical Electro-Optical Characteristics Curves

Fig. 1 Forward Current vs.






Fig.2 Spectral Distribution₽




Wavelength λ (nm)

Fig. 3 Forward Current vs.
Forward Voltage



Ver.:2

Fig.4 Radiant Intensity vs. ↔ Forward Current ↔






Chip Phototransistor with Right Angle Lens IR19-21C/TR8(BY)

Typical Electro-Optical Characteristics Curves-

Fig. 5 Relative Radiant Intensity vs. ↔
Angular Displacement ↔



Ver.:2

Chip Phototransistor with Right Angle Lens IR19-21C/TR8(BY)



Precautions For Use

1. Over-current-proof


Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage

- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package, the LEDs should be kept at 10° C ~ 30° C and 90° RH or less.
- 2.3 The LEDs suggested be used within one year.
- 2.4 After opening the package, the devices must be stored at 10° C $\sim 30^{\circ}$ C and $\leq 60^{\circ}$ RH, and used within 168 hours (floor life). If unused LEDs remain, it should be stored in moisture proof packages.
- 2.5 If the moisture absorbent material (desiccant material) has faded or unopened bag has exceeded the shelf life or devices (out of bag) have exceeded the floor life, baking treatment is required.
- 2.6 If baking is required, refer to IPC/JEDEC J-STD-033 for bake procedure or recommend the following conditions:
 - 96 hours at 60° C ± 5° C and < 5 % RH (reeled/tubed/loose units).

3. Soldering Condition

3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times
- 3.3 When soldering, do not put stress on the LEDs during heating
- 3.4 After soldering, do not warp the circuit board

Data Sheet

Chip Phototransistor with Right Angle Lens IR19-21C/TR8(BY)




4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.


5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.






Package Dimensions



Note: The tolerances unless mentioned are ±0.1mm, Unit: mm

Carrier Taping Dimensions: (Quantity: 3000PCS/Reel)




Note: The tolerances unless mentioned are ±0.1mm, Unit: mm

Chip Phototransistor with Right Angle Lens IR19-21C/TR8(BY)



Label Form Specification



CPN: Customer's Production Number

P/N: Production Number

LOT No: Lot Number QTY: Packing Quantity HUE: Peak Wavelength

CAT: Ranks

REF: Reference MSL-X: MSL Level

Made In: Manufacture place

DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

EVERLIGHT ELECTRONICS CO., LTD.

Office: No. 6-8, Zhonghua Rd., Shulin Dist.,

New Taipei City 23860, Taiwan

Tel: 886-2-2685-6688 Fax: 886-2685-2699 , 6897

http://www.everlight.com

www.everlight.com