

# N-Channel MOSFET

## **Applications:**

- Adaptor
- Charger
- .SMPS

# Lead Free Package and Finish


V <sub>DSS</sub>	R <sub>DS(ON)</sub> (Typ.)	I <sub>D</sub>
60V	$3 m \Omega$	230A

### Features:

- RoHS Compliant
- Low ON Resistance
- Low Gate Charge
- Peak Current vs Pulse Width Curve
- Inductive Switching Curves

**Ordering Information** 

<u> </u>		
PART NUMBER	PACKAGE	BRAND
FTP03N06NA	TO-220	IPS



# **Absolute Maximum Ratings** $T_C=25^{\circ}C$ unless otherwise specified

Symbol	Parameter	FTP03N06NA	Units
V <sub>DSS</sub>	Drain-to-Source Voltage	60	V
I <sub>D</sub>	Continuous Drain Current	230	Α
	Continuous Drain Current T <sub>C</sub> =100°C	145	А
I <sub>DM</sub>	Pulsed Drain Current (NOTE *1)	920	А
П	Power Dissipation	284	W
$P_D$	Derating Factor above 25℃	2.272	W/℃
V <sub>GS</sub>	Gate-to-Source Voltage	±20	V
E <sub>AS</sub>	Single Pulse Avalanche Energy(NOTE *2)	1024	mJ
T <sub>L</sub>	Maximum Temperature for Soldering	300	
T <sub>J</sub> and T <sub>STG</sub>	Operating Junction and Storage Temperature Range	150,-55 to150	${\mathbb C}$

### **Thermal Resistance**

Symbol	Parameter	Max.	Units	Test Conditions
D	Junction-to-Case	0.44		Water cooled heatsink, PD adjusted for a
$R_{\theta JC}$	Junction-to-Case	0.44	$^{\circ}$ C/W	peak junction temperature of +150℃.
$R_{\theta JA}$	Junction-to-Ambient	62.5		1 cubic foot chamber, free air.

**OFF Characteristics** T<sub>C</sub>=25 °C unless otherwise specified

Te-20 e difference opposition						
Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
BV <sub>DSS</sub>	Drain-to-Source Breakdown Voltage	60			V	$V_{GS}$ =0V, $I_D$ =250 $\mu$ A
	Dainta Constant and Constant			1		$V_{DS}$ =60V, $V_{GS}$ =0V $T_{J}$ =25 $^{\circ}$ C
I <sub>DSS</sub>	Drain-to-Source Leakage Current			100	μΑ	$V_{DS}$ =48V, $V_{GS}$ =0V $T_{J}$ =125 $^{\circ}$ C
I <sub>GSS</sub>	Gate-to-Source Forward Leakage			+100	nΛ	V <sub>GS</sub> =+20V
	Gate-to-Source Reverse Leakage			-100	nA -	V <sub>GS</sub> = -20V

**ON Characteristics**  $T_J=25^{\circ}\mathbb{C}$  unless otherwise specified

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
R <sub>DS(ON)</sub>	StaticDrain-to-Source On-Resistance		3.0	3.6	mΩ	$V_{GS}$ =10V, $I_D$ =95A
$V_{GS(TH)}$	Gate Threshold Voltage	2		4	V	$V_{DS}=V_{GS}$ , $I_{D}=250\mu A$
Pulse width ≤300µs; duty cycle≤ 2%						

**Dynamic Characteristics** Essentially independent of operating temperature

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
R <sub>g</sub>	Gate resistance		1.3		Ω	$V_{GS}$ = 0V, $V_{DS}$ = 25V f =1.0MHz
C <sub>iss</sub>	Input Capacitance		5681		pF	$V_{GS}$ = 0V, $V_{DS}$ = 25V f =1.0MHz
C <sub>oss</sub>	Output Capacitance		734.8			
$C_{rss}$	Reverse Transfer Capacitance		371.5			
Q <sub>g</sub> (10V)	Total Gate Charge		98.4			1 4450 \/ 40\/
$Q_{gs}$	Gate-to-Source Charge		29		nC	$I_D=115A, V_{DD}=48V$ $V_{GS}=10V$
$Q_{gd}$	Gate-to-Drain ("Miller") Charge		33.2			

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
t <sub>d(ON)</sub>	Turn-on Delay Time		41.9			$V_{DD}$ =30V, $I_{D}$ =115A, $V_{G}$ =10V $R_{G}$ =6 $\Omega$
t <sub>rise</sub>	Rise Time		47			
t <sub>d(OFF)</sub>	Turn-Off Delay Time		70.9		ns	
t <sub>fall</sub>	Fall Time		29.3			



## Source-Drain Diode Characteristics Tc=25℃ unless otherwise specified

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
I <sub>S</sub>	Continuous Source Current			220	_	
	(Body Diode)			230	Α	T 25°
I <sub>SM</sub>	Maximum Pulsed Current			920	Α	T <sub>C</sub> =25℃
	(Body Diode)					
V <sub>SD</sub>	Diode Forward Voltage			1.5	V	I <sub>SD</sub> =95A, V <sub>GS</sub> =0V
t <sub>rr</sub>	Reverse Recovery Time		38.1		ns	I <sub>F</sub> = 115A
Q <sub>rr</sub>	Reverse Recovery Charge		51.9		nC	di/dt=100A/us
Pulse width ≤300µs; duty cycle ≤ 2%						

### Notes:


<sup>\*1.</sup> Repetitive rating; pulse width limited by maximum junction temperature.

<sup>\*2.</sup> L=0.5mH,  $I_D$ =64A, Start  $T_J$ =25  $^{\circ}$ C



#### **Characteristics Curve:**

# Figure 1.Maximum Effective Thermal Impedance, Junction-to-Case



T , Rectangular Pulse Duration [sec]

Figure 3. Typical Output Characteristics




Figure 5. Typical Body Diode Transfer Characteristics




Figure 2 Typical Threshold Voltage vs Junction Temperature




Figure 4. Typical Transfer Characteristics




Figure 6. Typical on Resistance VS Drain Current






Figure 7. Capacitance VS Drain-to-Source Voltage




Figure 9. Breakdown Voltage VS Temperature




Figure 11. Resistance vs Gate-to-Source Voltage




Figure 8. Gate Charge VS Gate-to-Source Voltage




Figure 10. on-Resistance VS Temperature





Figure 12. Safe Operating Area





### **Test Circuits and Waveforms**

Figure 13. Gate Charge Test Circuit




Figure 14. Gate Charge Waveforms





Figure 15. Resistive Switching Test Circuit

Figure 16. Resistive Switching Waveforms










Figure 17. Diode Reverse Recovery Test Circuit




Figure 18. Diode Reverse Recovery Waveform






Figure19.Unclamped Inductive Switching Test Circuit

Figure 20. Unclamped Inductive Switching Waveform







#### **Disclaimers:**

InPower Semiconductor Co., Ltd (IPS) reserves the right to make changes without notice in order to improve reliability, function or design and to discontinue any product or service without notice. Customers should obtain the latest relevant information before orders and should verify that such information is current and complete. All products are sold subject to IPS's terms and conditions supplied at the time of order acknowledgement.

InPower Semiconductor Co., Ltd warrants performance of its hardware products to the specifications at the time of sale, Testing reliability and quality control are used to the extent IPS deems necessary to support this warrantee. Except where agreed upon by contractual agreement, testing of all parameters of each product is not necessarily performed.

InPower Semiconductor Co., Ltd does not assume any liability arising from the use of any product or circuit designs described herein. Customers are responsible for their products and applications using IPS's components. To minimize risk, customers must provide adequate design and operating safeguards.

InPower Semiconductor Co., Ltd does not warrant or convey any license either expressed or implied under its patent rights, nor the rights of others. Reproduction of information in IPS's data sheets or data books is permissible only if reproduction is without modification or alteration. Reproduction of this information with any alteration is an unfair and deceptive business practice. InPower Semiconductor Co., Ltd is not responsible or liable for such altered documentation.

Resale of IPS's products with statements different from or beyond the parameters stated by InPower Semiconductor Co., Ltd for that product or service voids all express or implied warrantees for the associated IPS's product or service and is unfair and deceptive business practice. InPower Semiconductor Co., Ltd is not responsible or liable for any such statements.

### **Life Support Policy:**

InPower Semiconductor Co., Ltd's products are not authorized for use as critical components in life support devices or systems without the expressed written approval of InPower Semiconductor Co., Ltd.

#### As used herein:

- 1. Life support devices or systems are devices or systems which:
  - a. are intended for surgical implant into the human body,
  - b. support or sustain life,
  - c. whose failure to perform when properly used in accordance with instructions for used provided in the labeling, can be reasonably expected to result in significant injury to the user.
- A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.