

CT304D 3Q TRIACs

MAIN CHARACTERISTICS


| | | |
|-------------------|---------------|--------------|
| $I_{T(RMS)}$ | | 4A |
| V_{DRM}/V_{RRM} | CT304D-600T/S | 600V |
| | CT304D-800T/S | 800V |
| V_{TM} | | 1.55V |

FEATURES


- NPNPN 5-layer Structure TRIACs
- Mesa Glass Passivated Technology
- Multi Layers Metal Electrodes
- High Junction Temperature
- Good Commutation Performance
- High dV/dt and dI/dt

APPLICATIONS

- Heater Control
- Motor Speed Controller
- Mixer



MARKING



CT304D:Series Code
 600S:Depends on V_{DRM}
 and I_{GT}
 XXX:Internal Code

ABSOLUTE RATINGS ($T_a=25^\circ\text{C}$ unless otherwise noted)

| Symbol | Parameter | Test condition | Value | Unit | |
|-------------------|--|--|---------------|----------------------|------------------------|
| V_{DRM}/V_{RRM} | Repetitive peak off-state voltage | $T_j=25^\circ\text{C}$ | CT304D-600T/S | 600 | V |
| | | | CT304D-800T/S | 800 | V |
| $I_{T(RMS)}$ | RMS on-state current | TO-252-2LK ($T_C \leq 110^\circ\text{C}$) , Fig. 1,2 | 4 | A | |
| I_{TSM} | Non repetitive surge peak on-state current | Full sine wave , $T_j(\text{init})=25^\circ\text{C}$, $t_p=20\text{ms}$; Fig. 3,5 | 40 | A | |
| I^2t | I^2t value | $t_p=10\text{ms}$ | 8 | A^2s | |
| dI_T/dt | Critical rate of rise of on-state current | $I_G=2 \cdot I_{GT}$, $t_r \leq 10\text{ns}$, $F=120\text{Hz}$, $T_j=125^\circ\text{C}$ | I - II - III | 50 | $\text{A}/\mu\text{s}$ |
| | | | IV | n/a | |
| I_{GM} | Peak gate current | $t_p=20\mu\text{s}$, $T_j=125^\circ\text{C}$ | 4 | A | |
| $P_{G(AV)}$ | Average gate power | $T_j=125^\circ\text{C}$ | 1 | W | |
| T_{STG} | Storage temperature | | -40~+150 | $^\circ\text{C}$ | |
| T_j | Operating junction temperature | | -40~+125 | | |


ELECTRICAL CHARACTERISTICS (T_a=25°C unless otherwise specified)

| Symbol | Parameter | Test condition | Value | | Unit | |
|-------------------------------------|------------------------------------|---|--------------|-----|------|------|
| | | | T | S | | |
| I _{GT} | Gate trigger current | V _D =12V, I _T =1A, T _j =25°C, Fig. 6 | I - II - III | ≤5 | ≤10 | mA |
| | | | IV | n/a | n/a | |
| V _{GT} | Gate trigger voltage | I - II - III | ≤1.3 | | V | |
| V _{GD} | Non-triggering gate voltage | V _D =V _{DRM} , T _j =125°C | ≥0.2 | | V | |
| I _H | Holding current | V _D =12V, I _{GT} =0.1A, T _j =25°C, Fig. 6 | I - II - III | ≤10 | ≤15 | mA |
| I _L | Latching current | I - III | | ≤10 | ≤25 | mA |
| | | | II | ≤15 | ≤30 | mA |
| dV _D /dt | Critical rate of rise of off-state | V _D =67%V _{DRM} , Gate Open T _j =125°C | | ≥20 | ≥40 | V/μs |
| V _{TM} | On-state Voltage | I _{TM} =6A, tp=380μs, Fig. 4 | ≤1.55 | | V | |
| I _{DRM} / I _{RRM} | Repetitive peak off-state current | V _D =V _{DRM} /V _{RRM} , T _j =25°C | | ≤5 | ≤5 | μA |
| | | V _D =V _{DRM} /V _{RRM} , T _j =125°C | | ≤1 | ≤1 | mA |

THERMAL RESISTANCES

| Symbol | Parameter | Value | Unit |
|-----------------------|-----------------------|------------|----------|
| R _{th} (j-c) | Junction to case (AC) | TO-252-2LK | 2.6 °C/W |
| R _{th} (j-a) | Junction to ambient | TO-252-2LK | 70 °C/W |

PART NUMBER



CHARACTERISTICS CURVES

FIG.1: Maximum power dissipation versus RMS on-state current (full cycle)




FIG.2: RMS on-state current versus case temperature (full cycle)




FIG.3: Surge peak on-state current versus number of cycles




FIG.4: On-state characteristics (maximum values)




FIG.5: Non-repetitive surge peak on-state current for a sinusoidal pulse with width $t_p < 10\text{ms}$






FIG.6: Relative variations of gate trigger current, holding current and latching current versus junction temperature (typical values)



TO-252-2LK PACKAGE OUTLINE DIMENSIONS



| Symbol | Dimensions In Millimeters | |
|--------|---------------------------|--------|
| | Min. | Max. |
| A | 2.100 | 2.500 |
| A1 | 0.000 | 0.127 |
| B | 1.070 | 1.470 |
| b | 0.710 | 0.810 |
| C | 0.700 | 0.900 |
| D | 3.400 | 3.800 |
| e | 2.250 | 2.350 |
| e1 | 2.250 | 2.350 |
| L | 10.000 | 10.400 |
| L1 | 2.600 | 3.000 |
| L2 | 1.400 | 1.700 |
| L3 | 0.600 | 1.000 |