

TO-262K Plastic-Encapsulate Thyristors

CT316R 3Q TRIACs

MAIN CHARACTERISTICS


| | | |
|-------------------|-----------------|--------------|
| $I_{T(RMS)}$ | | 16A |
| V_{DRM}/V_{RRM} | CT316R-600S/C/B | 600V |
| | CT316R-800S/C/B | 800V |
| V_{TM} | | 1.55V |

FEATURES


- NPNPN 5-layer Structure TRIACs
- Mesa Glass Passivated Technology
- Multi Layers Metal Electrodes
- High Junction Temperature
- Good Commutation Performance
- High dV/dt and dI/dt

APPLICATIONS

- Heater Control
- Motor Speed Controller
- Mixer



MARKING



CT316R:Series Code
600S:Depends on V_{DRM}
and I_{GT}
XXX:Internal Code

ABSOLUTE RATINGS ($T_a=25^\circ\text{C}$ unless otherwise noted)

| Symbol | Parameter | Test condition | Value | Unit | |
|-------------------|--|--|-----------------|----------------------|------------------------|
| V_{DRM}/V_{RRM} | Repetitive peak off-state voltage | $T_j=25^\circ\text{C}$ | CT316R-600S/C/B | 600 | V |
| | | | CT316R-800S/C/B | 800 | V |
| $I_{T(RMS)}$ | RMS on-state current | TO-262K($T_c \leq 100^\circ\text{C}$), Fig. 1,2 | 16 | A | |
| I_{TSM} | Non repetitive surge peak on-state current | Full sine wave , $T_j(\text{init})=25^\circ\text{C}$, $t_p=20\text{ms}$; Fig. 3,5 | 160 | A | |
| I^2t | I^2t value | $t_p=10\text{ms}$ | 140 | A^2s | |
| dI_T/dt | Critical rate of rise of on-state current | $I_G=2 \cdot I_{GT}$, $t_r \leq 10\text{ns}$, $F=120\text{Hz}$, $T_j=125^\circ\text{C}$ | I - II - III | 50 | $\text{A}/\mu\text{s}$ |
| | | | IV | n/a | |
| I_{GM} | Peak gate current | $t_p=20\mu\text{s}$, $T_j=125^\circ\text{C}$ | 4 | A | |
| $P_{G(AV)}$ | Average gate power | $T_j=125^\circ\text{C}$ | 1 | W | |
| T_{STG} | Storage temperature | | -40~+150 | $^\circ\text{C}$ | |
| T_j | Operating junction temperature | | -40~+125 | | |


ELECTRICAL CHARACTERISTICS (T_a=25°C unless otherwise specified)

| Symbol | Parameter | Test condition | Value | | | Unit | |
|-------------------------------------|------------------------------------|---|--------------|-------|------|-------|------|
| | | | S | C | B | | |
| I _{GT} | Gate trigger current | V _D =12V, R _L =33Ω, T _j =25°C, Fig. 6 | I - II - III | ≤10 | ≤35 | ≤50 | mA |
| | | | IV | n/a | n/a | n/a | |
| V _{GT} | Gate trigger voltage | T _j =25°C, Fig. 6 | I - II - III | ≤1.3 | | V | |
| V _{GD} | Non-triggering gate voltage | V _D =V _{DRM} , T _j =125°C | | ≥0.2 | | V | |
| I _H | Holding current | I _T =500mA, Fig. 6 | | ≤15 | ≤30 | ≤50 | mA |
| I _L | Latching current | I _G =1.2I _{GT} Fig. 6 | I - III | ≤25 | ≤50 | ≤70 | mA |
| | | | II | ≤30 | ≤60 | ≤80 | mA |
| dV _D /dt | Critical rate of rise of off-state | V _D =67%V _{DRM} , Gate Open T _j =125°C | | ≥40 | ≥500 | ≥1000 | V/μs |
| V _{TM} | On-state Voltage | I _{TM} =23A, tp=380μs, Fig. 4 | | ≤1.55 | | V | |
| I _{DRM} / I _{RPM} | Repetitive peak off-state current | V _D =V _{DRM} /V _{RPM} , T _j =25°C | | ≤5 | ≤5 | ≤5 | μA |
| | | V _D =V _{DRM} /V _{RPM} , T _j =125°C | | ≤1 | ≤1 | ≤1 | mA |

THERMAL RESISTANCES

| Symbol | Parameter | Value | Unit |
|-----------------------|-----------------------|---------|----------|
| R _{th} (j-c) | Junction to case (AC) | TO-262K | 1.2 °C/W |
| R _{th} (j-a) | Junction to ambient | TO-262K | 45 °C/W |

PART NUMBER



CHARACTERISTICS CURVES

FIG.1: Maximum power dissipation versus RMS on-state current (full cycle)




FIG.2: RMS on-state current versus case temperature (full cycle)




FIG.3: Surge peak on-state current versus number of cycles




FIG.4: On-state characteristics (maximum values)




FIG.5: Non-repetitive surge peak on-state current for a sinusoidal pulse with width $t_p < 10\text{ms}$






FIG.6: Relative variations of gate trigger current, holding current and latching current versus junction temperature (typical values)



TO-262K PACKAGE OUTLINE DIMENSIONS



| DIM. | Unit(mm) | | Unit(inch) | |
|------|----------|-------|------------|-------|
| | Min | Max | Min | Max |
| A | 9.7 | 10.4 | 0.381 | 0.409 |
| B | 1.31 | 1.62 | 0.051 | 0.063 |
| C | 3.5 | 3.9 | 0.137 | 0.153 |
| D | 0.7 | 0.92 | 0.027 | 0.036 |
| F | 9.95 | 10.35 | 0.391 | 0.407 |
| G | 12.95 | 13.9 | 0.509 | 0.547 |
| H | 2.4 | 2.7 | 0.094 | 0.106 |
| I | 4.38 | 4.65 | 0.172 | 0.183 |
| J | 1.15 | 1.36 | 0.045 | 0.053 |
| L | 2.35 | 2.85 | 0.092 | 0.112 |
| M | 0.32 | 0.58 | 0.012 | 0.022 |
| N | 1.18 | 1.42 | 0.046 | 0.055 |