



P-Channel NexFET™ Power MOSFET

Check for Samples: CSD25213W10

FEATURES

- Ultra Low Qg and Qgd
- Small Footprint 1mm x 1mm
- Low Profile 0.62mm Height
- Pb Free
- Gate-Source Voltage Clamp
- Gate ESD Protection
- RoHS Compliant
- Halogen Free


APPLICATIONS


- Battery Management
- Load Switch
- Battery Protection

DESCRIPTION

The device has been designed to deliver the lowest on resistance and gate charge in the smallest outline possible with excellent thermal characteristics in an ultra low profile.

Top View





PRODUCT SUMMARY

V_{DS}	Drain to Source Voltage	-20		V	
Q_g	Gate Charge Total (4.5V) 2.2				
Q_{gd}	Gate Charge Gate to Drain 0.14				
R _{DS(on)}	Drain to Source On	Source On $V_{GS} = -2.5V$ 5-		mΩ	
	Resistance	$V_{GS} = -4.5V$	39	mΩ	
$V_{GS(th)}$	Threshold Voltage	-0.85	1	V	


ORDERING INFORMATION

Device Package		Media	Qty	Ship
CSD25213W10	1 x 1 Wafer Level Package	7-inch reel	3000	Tape and Reel

ABSOLUTE MAXIMUM RATINGS

T _A = 25°C	unless otherwise stated	VALUE	UNIT
V_{DS}	Drain to Source Voltage	-20	٧
V _{GS}	Gate to Source Voltage	-6.0	V
I _D	Continuous Drain Current, $T_A = 25^{\circ}C^{(1)}$	-1.6	Α
I_{DM}	Pulsed Drain Current, T _A = 25°C ⁽²⁾	-16	Α
I _G	Continuous Gate Clamp Current ⁽³⁾	-5	mA
P_D	Power Dissipation ⁽¹⁾	1	W
T _J , T _{STG}	Operating Junction and Storage Temperature Range	-55 to 150	°C

- (1) $R_{\theta JA} = 75^{\circ}\text{C/W}$ on 1in^2 Cu (2 oz.) on 0.060" thick FR4 PCB.
- (2) Pulse width ≤300µs, duty cycle ≤2%
- (3) Limited by gate resistance.





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



SLPS443 - JUNE 2013 www.ti.com



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

ELECTRICAL CHARACTERISTICS

 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Static Ch	aracteristics					
BV _{DSS}	Drain to Source Voltage	$V_{GS} = 0V, I_D = -250\mu A$	-20			V
BV _{GSS}	Gate to Source Voltage;	$V_{DS} = 0V, I_{G} = -250\mu A$	-6.0			V
I _{DSS}	Drain to Source Leakage Current	V _{GS} = 0V, V _{DS} = -10V			-1	μΑ
I _{GSS}	Gate to Source Leakage Current	$V_{DS} = 0V$, $V_{GS} = -6V$			-100	nA
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$	-0.60	-0.85	-1.10	V
	Drain to Source On Resistance	$V_{GS} = -2.5V, I_D = -1A$		54	67	mΩ
R _{DS(on)}	Drain to Source On Resistance	$V_{GS} = -4.5V, I_D = -1A$		39	47	mΩ
9 _{fs}	Transconductance	$V_{DS} = -10V, I_{D} = -1A$		6.2		S
Dynamic	Characteristics				•	
C _{ISS}	Input Capacitance			368	478	pF
Coss	Output Capacitance	$V_{GS} = 0V, V_{DS} = -10V, f = 10kHz$		148	192	pF
C _{RSS}	Reverse Transfer Capacitance			7.8	10.1	pF
R _G	Series Gate Resistance			20		Ω
R _C	Series Clamp Resistance			5000		Ω
Qg	Gate Charge Total (-4.5V)			2.2	2.9	nC
Q _{gd}	Gate Charge Gate to Drain	101/ 1 11		0.14		nC
Q _{gs}	Gate Charge Gate to Source	$V_{DS} = -10V, I_{D} = -1A$		0.74		nC
Q _{g(th)}	Gate Charge at Vth			0.43		nC
Q _{OSS}	Output Charge	$V_{DS} = -10V, V_{GS} = 0V$		2.5		nC
t _{d(on)}	Turn On Delay Time			510		ns
t _r	Rise Time	$V_{DS} = -10V, V_{GS} = -2.5V, I_{D} = -1A$		520		ns
t _{d(off)}	Turn Off Delay Time	$R_G = 10\Omega$		1000		ns
t _f	Fall Time			970		ns
Diode Ch	aracteristics					
V _{SD}	Diode Forward Voltage	$I_S = -1A$, $V_{GS} = 0V$		-0.77	-1	V
Q _{rr}	Reverse Recovery Charge	$V_{DS} = -10V, I_F = -1A,$ di/dt = 200A/ μ s		4.0		nC
t _{rr}	Reverse Recovery Time	$V_{DS} = -10V, I_F = -1A,$ di/dt = 200A/µs		11		ns

THERMAL CHARACTERISTICS


 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$

	PARAMETER	MIN	TYP	MAX	UNIT
D	Junction to Ambient Thermal Resistance ⁽¹⁾		75		°C/W
$R_{\theta JA}$	Junction to Ambient Thermal Resistance ⁽²⁾		265		°C/W


- (1) Device mounted on FR4 material with 1-inch² (6.45-cm²), 2-oz. (0.071-mm thick) Cu.
 (2) Device mounted on FR4 material with minimum Cu mounting area.

Product Folder Links: CSD25213W10





Max $R_{\theta JA} = 90^{\circ}C/W$ when mounted on 1inch² of 2 oz. Cu.



Max $R_{\theta JA} = 333^{\circ} C/W$ when mounted on minimum pad area of 2 oz. Cu.

TYPICAL MOSFET CHARACTERISTICS

 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$




Figure 1. Transient Thermal Impedance

Product Folder Links: CSD25213W10

1.1

1

0.9

0.8

0.7

0.6

-V_{GS(th)} - Threshold Voltage (V)



SLPS443 - JUNE 2013 www.ti.com

TYPICAL MOSFET CHARACTERISTICS (continued)

(T_A = 25°C unless otherwise stated)




Figure 2. Saturation Characteristics




Figure 3. Transfer Characteristics





Figure 4. Gate Charge

 $I_{D} = -250uA$



0.5 -75 T_C - Case Temperature (°C) Figure 6. Threshold Voltage vs. Temperature

75

125

175

25




Figure 7. On-State Resistance vs. Gate-to-Source Voltage

-25



TYPICAL MOSFET CHARACTERISTICS (continued)

 $(T_A = 25$ °C unless otherwise stated)




Figure 8. Normalized On-State Resistance vs. Temperature




Figure 9. Typical Diode Forward Voltage




Figure 10. Maximum Safe Operating Area




Figure 11. Single Pulse Unclamped Inductive Switching




Figure 12. Maximum Drain Current vs. Temperature

Copyright © 2013, Texas Instruments Incorporated


Product Folder Links: CSD25213W10

SLPS443 - JUNE 2013 www.ti.com

NSTRUMENTS

MECHANICAL DATA

CSD25213W10 Package Dimensions




NOTE: All dimensions are in mm (unless otherwise specified)

Pin Configuration Table

3.1			
POSITION	DESIGNATION		
A1	Gate		
B1	Drain		
A2, B2	Source		


Land Pattern Recommendation





NOTE: All dimensions are in mm (unless otherwise specified)



Tape and Reel Information







M0153-01

- (1) All dimensions are in mm (unless otherwise specified)
- (2) Pin 1 will be oriented in the top left quadrant of the tape enclosure (closest to the carrier tape sprocket holes).



PACKAGE OPTION ADDENDUM

17-Jul-2013

PACKAGING INFORMATION

Orderable Device	Status	Package Type	_	Pins	•	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)		(3)		(4/5)	
CSD25213W10	ACTIVE	DSBGA	YZB	4	3000	Green (RoHS & no Sb/Br)	SNAGCU	Level-1-260C-UNLIM	-55 to 150	213	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive **Amplifiers** amplifier.ti.com Communications and Telecom www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic Security www.ti.com/security logic.ti.com

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors www.ti.com/omap TI E2E Community e2e.ti.com

Wireless Connectivity www.ti.com/wirelessconnectivity